

THOUSANDS OF APPLICATIONS.
HUNDREDS OF LABELS.
ONE LABEL PRINTER.



BMP® 71 LABEL PRINTER



THE ONE WAY TO

BMP®71 LABEL PRINTER

The best features and functionalities of Brady's portable label printers are now combined into one easy-to-use, top-of-the-line portable thermal transfer printer – Brady's NEW BMP®71 printer. Whether you need ¼" self-laminating wire marker labels or 2" wide vinyl pipe marker labels, you only need ONE label maker - the BMP®71 printer can do it all!

SAVE TIME WITH FOOLPROOF LABEL DESIGN AND HIGH SPEED PRINT

The BMP71 printer is designed to help you get your job done quickly and efficiently – and that means making labels fast. At 1.5" per second, the BMP71 printer has the fastest print speed on the portable printer market.

But that's not all. With built-in design wizards, material-recognition technology and storage space for over 100,000 label files, this printer can cut your label design time in half.

Label Design Wizards Available For:

- Electrical
- Voice/Data Comm
- Safety/General ID



CUT MATERIAL WASTE - PREVIEW LABELS BEFORE YOU PRINT!

With a large, full color graphical screen, the BMP71 printer shows you exactly what your label will look like as you're creating it – so there's no guesswork. You can stop wasting label material on "test labels" and start saving time and money by creating a label once – knowing it's correct before you even hit "Print."

The display includes:

- Label material and ribbon part number
- Label color and size (including the amount of remaining material)
- Font size, bold and other type functions
- Application templates
- Multi-area print areas
- Remaining battery charge



FASTER, EASIER LABEL PRINTING



ENHANCE YOUR LABELS WITH ADVANCED GRAPHICS AND SYMBOLS

With hundreds of symbols and graphics, the BMP71 printer can transform your labels from basic text messages to highly effective communication vehicles.

For lean enterprises, Brady's MarkWare™ software provides additional graphics and templates for signs, labels, pipe markers and tags - perfect for 5S, TPM and lean visuals.

EASY WAY TO CREATE LABELS ON YOUR PC

Brady's LabelMark™ software lets you easily create labels for asset id, component marking, voice / data comm labeling, wire markers and more. LabelMark software is completely integrated with Microsoft Office, AutoCAD applications and more.

Coming soon ---- Create labels on your PC, download them to the BMP71 printer and print with the new LabelMark v.5.1 software. Edit your files on the BMP®71 Label Printer and transfer them back into LabelMark software.


Other Features Include:

- | | | | |
|----------------------|------------------|--------------------|-------------------------------|
| ■ 100's Of Symbols | ■ Frame | ■ Expand/Condense | ■ Multiple Areas On One Label |
| ■ Reverse Print | ■ Mirror Print | ■ Time/Date Stamps | ■ Barcodes |
| ■ Multiple Font Size | ■ Auto Font Size | ■ Underline | ■ Sequences |
| ■ Subscripts | ■ Vertical | ■ Italics/Bold | |



WATCH A DEMO VIDEO AT:

www.BradyID.com/bmp71
www.BradyCanada.ca/bmp71



ONE SOURCE FOR LABEL MATERIALS

The BMP®71 Label Printer can print on over 400 label parts - so whatever label size or color you need, we've got you covered. Add all of the materials from the TLS 2200® Thermal Transfer Printer and the HandiMark® Portable Label Maker, and your label options are endless!

General Industrial, Lean & Safety

Indoor/outdoor pliable vinyl conforms to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins, and equipment. Aggressive permanent adhesive; labels offer excellent resistance to oils, detergents, dirt, grime, and many solvents.




Figure 8



Indoor/Outdoor Grade Vinyl Tape

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 8	M71C-500-595-BK	1 Roll (cont.)	B-595	Black	0.50	(12.70)	50 ft.	(15.24 m)	M71-R4400-WT	\$43.88
Fig. 8	M71C-500-595-BL	1 Roll (cont.)	B-595	Blue	0.50	(12.70)	50 ft.	(15.24 m)	M71-R4400-WT	\$43.88
Fig. 8	M71C-500-595-BR	1 Roll (cont.)	B-595	Brown	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-CL	1 Roll (cont.)	B-595	Clear	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-GD	1 Roll (cont.)	B-595	Gold	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-GN	1 Roll (cont.)	B-595	Green	0.50	(12.70)	50 ft.	(15.24 m)	M71-R4400-WT	\$43.88
Fig. 8	M71C-500-595-GY	1 Roll (cont.)	B-595	Grey	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-LB	1 Roll (cont.)	B-595	Light Blue	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-OC	1 Roll (cont.)	B-595	Ochre	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-OR	1 Roll (cont.)	B-595	Orange	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-PK	1 Roll (cont.)	B-595	Pink	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-PL	1 Roll (cont.)	B-595	Purple	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-RD	1 Roll (cont.)	B-595	Red	0.50	(12.70)	50 ft.	(15.24 m)	M71-R4400-WT	\$43.88
Fig. 8	M71C-500-595-SB	1 Roll (cont.)	B-595	Sky Blue	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-TN	1 Roll (cont.)	B-595	Tan	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-WT	1 Roll (cont.)	B-595	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-500-595-YL	1 Roll (cont.)	B-595	Yellow	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$43.88
Fig. 8	M71C-1000-595-BK	1 Roll (cont.)	B-595	Black	1.00	(25.40)	50 ft.	(15.24 m)	M71-R4400-WT	\$61.21
Fig. 8	M71C-1000-595-BL	1 Roll (cont.)	B-595	Blue	1.00	(25.40)	50 ft.	(15.24 m)	M71-R4400-WT	\$61.21
Fig. 8	M71C-1000-595-BR	1 Roll (cont.)	B-595	Brown	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-CL	1 Roll (cont.)	B-595	Clear	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-GD	1 Roll (cont.)	B-595	Gold	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-GN	1 Roll (cont.)	B-595	Green	1.00	(25.40)	50 ft.	(15.24 m)	M71-R4400-WT	\$61.21
Fig. 8	M71C-1000-595-GY	1 Roll (cont.)	B-595	Grey	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-LB	1 Roll (cont.)	B-595	Light Blue	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-OC	1 Roll (cont.)	B-595	Ochre	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-OR	1 Roll (cont.)	B-595	Orange	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-PK	1 Roll (cont.)	B-595	Pink	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-PL	1 Roll (cont.)	B-595	Purple	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-RD	1 Roll (cont.)	B-595	Red	1.00	(25.40)	50 ft.	(15.24 m)	M71-R4400-WT	\$61.21
Fig. 8	M71C-1000-595-SB	1 Roll (cont.)	B-595	Sky Blue	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-TN	1 Roll (cont.)	B-595	Tan	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-WT	1 Roll (cont.)	B-595	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-1000-595-YL	1 Roll (cont.)	B-595	Yellow	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$61.21
Fig. 8	M71C-2000-595-BK	1 Roll (cont.)	B-595	Black	2.00	(50.80)	50 ft.	(15.24 m)	M71-R4400-WT	\$91.85
Fig. 8	M71C-2000-595-BL	1 Roll (cont.)	B-595	Blue	2.00	(50.80)	50 ft.	(15.24 m)	M71-R4400-WT	\$91.85
Fig. 8	M71C-2000-595-BR	1 Roll (cont.)	B-595	Brown	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-CL	1 Roll (cont.)	B-595	Clear	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-GD	1 Roll (cont.)	B-595	Gold	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-GN	1 Roll (cont.)	B-595	Green	2.00	(50.80)	50 ft.	(15.24 m)	M71-R4400-WT	\$91.85
Fig. 8	M71C-2000-595-GY	1 Roll (cont.)	B-595	Grey	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-LB	1 Roll (cont.)	B-595	Light Blue	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-OC	1 Roll (cont.)	B-595	Ochre	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-OR	1 Roll (cont.)	B-595	Orange	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-PK	1 Roll (cont.)	B-595	Pink	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-PL	1 Roll (cont.)	B-595	Purple	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-RD	1 Roll (cont.)	B-595	Red	2.00	(50.80)	50 ft.	(15.24 m)	M71-R4400-WT	\$91.85
Fig. 8	M71C-2000-595-SB	1 Roll (cont.)	B-595	Sky Blue	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-TN	1 Roll (cont.)	B-595	Tan	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-WT	1 Roll (cont.)	B-595	White	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85
Fig. 8	M71C-2000-595-YL	1 Roll (cont.)	B-595	Yellow	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$91.85

* See all ribbon colors on page 14.

General Industrial, Lean & Safety (Continued)

Pre-Printed Die Cut Labels




Figure 4




Figure 8




Figure 27




Figure 28




Figure 30

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 28	M71-30-423-TEST	250	B-423	White	1.50	(38.10)	0.75	(19.05)	M71-R6000	\$35.79
Fig. 27	M71-30-428-CALI	250	B-428	White	1.50	(38.10)	0.75	(19.05)	M71-R4300	\$57.06
Fig. 30	M71-35-428-PROP	250	B-428	White	1.63	(41.40)	0.75	(19.05)	M71-R4300	\$57.06
Fig. 4	M71-38-483-CAUT	100	B-483	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$53.67
Fig. 4	M71-38-483-DANG	100	B-483	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$53.67
Fig. 4	M71-38-483-NOTI	100	B-483	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$53.67
Fig. 4	M71-38-483-WARN	100	B-483	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$53.67

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 8	M71C-500-428	1 Roll (cont.)	B-428	Silver	0.50	(12.70)	50 ft.	(15.24 m)	M71-R4300	\$59.50
Fig. 8	M71C-1000-529	1 Roll (cont.)	B-529	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$47.89
Fig. 8	M71C-2000-529	1 Roll (cont.)	B-529	White	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$66.54

Control Panel/Raised Panel

Customized legend plates with less hassle and time than engraved plates. Brady Raised Panel Labels are RoHS compliant and UL approved. Aggressive adhesive and solvent resistant.




Figure 4




Figure 25



Pre-Printed Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 4	M71EP-171-593	200	B-593	White	1.06	(26.92)	0.49	(12.45)	M71-R6000	\$99.95
Fig. 4	M71EP-171-593-BK	200	B-593	Black	1.06	(26.92)	0.49	(12.45)	M71-R4400-WT	\$99.95
Fig. 4	M71EP-171-593-GN	200	B-593	Green	1.06	(26.92)	0.49	(12.45)	M71-R4400-WT	\$99.95
Fig. 4	M71EP-171-593-RD	200	B-593	Red	1.06	(26.92)	0.49	(12.45)	M71-R4400-WT	\$99.95
Fig. 4	M71EP-171-593-SL	200	B-593	Silver	1.06	(26.92)	0.49	(12.45)	M71-R6000	\$99.95
Fig. 4	M71EP-171-593-YL	200	B-593	Yellow	1.06	(26.92)	0.49	(12.45)	M71-R6000	\$99.95
Fig. 25	M71EP-167-593	100	B-593	White	1.20	(30.48)	1.50	(38.10)	M71-R6000	\$89.95
Fig. 25	M71EP-167-593-BK	100	B-593	Black	1.20	(30.48)	1.50	(38.10)	M71-R4400-WT	\$89.95
Fig. 25	M71EP-167-593-GN	100	B-593	Green	1.20	(30.48)	1.50	(38.10)	M71-R4400-WT	\$89.95
Fig. 25	M71EP-167-593-RD	100	B-593	Red	1.20	(30.48)	1.50	(38.10)	M71-R4400-WT	\$89.95
Fig. 25	M71EP-167-593-YL	100	B-593	Yellow	1.20	(30.48)	1.50	(38.10)	M71-R6000	\$89.95
Fig. 25	M71EP-168-593	100	B-593	White	1.20	(30.48)	1.90	(48.26)	M71-R6000	\$99.95
Fig. 25	M71EP-168-593-BK	100	B-593	Black	1.20	(30.48)	1.90	(48.26)	M71-R4400-WT	\$99.95
Fig. 25	M71EP-168-593-GN	100	B-593	Green	1.20	(30.48)	1.90	(48.26)	M71-R4400-WT	\$99.95
Fig. 25	M71EP-168-593-RD	100	B-593	Red	1.20	(30.48)	1.90	(48.26)	M71-R4400-WT	\$99.95
Fig. 25	M71EP-168-593-YL	100	B-593	Yellow	1.20	(30.48)	1.90	(48.26)	M71-R6000	\$99.95
Fig. 25	M71EP-169-593	100	B-593	White	1.80	(45.72)	1.80	(45.72)	M71-R6000	\$105.95
Fig. 25	M71EP-169-593-BK	100	B-593	Black	1.80	(45.72)	1.80	(45.72)	M71-R4400-WT	\$105.95
Fig. 25	M71EP-169-593-GN	100	B-593	Green	1.80	(45.72)	1.80	(45.72)	M71-R4400-WT	\$105.95
Fig. 25	M71EP-169-593-RD	100	B-593	Red	1.80	(45.72)	1.80	(45.72)	M71-R4400-WT	\$105.95
Fig. 25	M71EP-169-593-YL	100	B-593	Yellow	1.80	(45.72)	1.80	(45.72)	M71-R6000	\$105.95
Fig. 4	M71EP-173-593	100	B-593	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$75.95
Fig. 4	M71EP-173-593-BK	100	B-593	Black	2.00	(50.80)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-173-593-GN	100	B-593	Green	2.00	(50.80)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-173-593-RD	100	B-593	Red	2.00	(50.80)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-173-593-SL	100	B-593	Silver	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$75.95
Fig. 4	M71EP-173-593-YL	100	B-593	Yellow	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$75.95
Fig. 4	M71EP-176-593	50	B-593	White	3.00	(76.20)	1.00	(25.40)	M71-R6000	\$59.95
Fig. 4	M71EP-176-593-BK	50	B-593	Black	3.00	(76.20)	1.00	(25.40)	M71-R4400-WT	\$59.95
Fig. 4	M71EP-176-593-GN	50	B-593	Green	3.00	(76.20)	1.00	(25.40)	M71-R4400-WT	\$59.95
Fig. 4	M71EP-176-593-RD	50	B-593	Red	3.00	(76.20)	1.00	(25.40)	M71-R4400-WT	\$59.95
Fig. 4	M71EP-176-593-YL	50	B-593	Yellow	3.00	(76.20)	1.00	(25.40)	M71-R6000	\$59.95
Fig. 4	M71EP-174-593	50	B-593	White	4.00	(101.60)	1.00	(25.40)	M71-R6000	\$75.95
Fig. 4	M71EP-174-593-BK	50	B-593	Black	4.00	(101.60)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-174-593-GN	50	B-593	Green	4.00	(101.60)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-174-593-RD	50	B-593	Red	4.00	(101.60)	1.00	(25.40)	M71-R4400-WT	\$75.95
Fig. 4	M71EP-174-593-SL	50	B-593	Silver	4.00	(101.60)	1.00	(25.40)	M71-R6000	\$75.95
Fig. 4	M71EP-174-593-YL	50	B-593	Yellow	4.00	(101.60)	1.00	(25.40)	M71-R6000	\$75.95

* See all ribbon colors on page 14.

General Labels/Rating Plates

Choose from several materials with aggressive adhesives for use in commercial/industrial applications.




Figure 4




Figure 8




Figure 14



Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 4	M71-68-430	750	B-430	Clear	0.24	(6.00)	0.15	(3.81)	M71-R6000	\$30.18
Fig. 4	M71-71-430	750	B-430	Clear	0.35	(8.89)	0.20	(5.08)	M71-R6000	\$30.18
Fig. 14	M71-80-488	250	B-488	White	0.75	(19.05)	0.90	(22.86)	M71-R4300	\$25.30
Fig. 4	M71-97-488	250	B-488	White	0.90	(22.86)	0.90	(22.86)	M71-R4300	\$27.00
Fig. 4	M71-16-430	500	B-430	Clear	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$43.13
Fig. 4	M71-17-430	500	B-430	Clear	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$43.13
Fig. 4	M71-16-483	500	B-483	White	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$47.77
Fig. 4	M71-17-483	500	B-483	White	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$48.75
Fig. 4	M71-19-483	250	B-483	White	1.00	(25.40)	1.00	(25.40)	M71-R6000	\$34.33
Fig. 4	M71-17-486	500	B-486	Silver	1.00	(25.40)	0.50	(12.70)	M71-R4300	\$55.95
Fig. 4	M71-45-430	500	B-430	Clear	1.05	(38.10)	0.38	(9.53)	M71-R6000	\$45.08
Fig. 4	M71-65-483	250	B-483	White	1.38	(34.93)	1.00	(25.40)	M71-R6000	\$30.42
Fig. 4	M71-29-459	500	B-459	White	1.50	(38.10)	0.50	(12.70)	M71-R6000	\$43.85
Fig. 4	M71-30-459	250	B-459	White	1.50	(38.10)	0.75	(19.05)	M71-R6000	\$38.36
Fig. 4	M71-29-483	500	B-483	White	1.50	(38.10)	0.50	(12.70)	M71-R6000	\$54.12
Fig. 4	M71-30-483	250	B-483	White	1.50	(38.10)	0.75	(19.05)	M71-R6000	\$46.53
Fig. 4	M71-31-483	250	B-483	White	1.50	(38.10)	1.00	(25.40)	M71-R6000	\$38.85
Fig. 4	M71-29-486	500	B-486	Silver	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$64.38
Fig. 4	M71-30-486	250	B-486	Silver	1.50	(38.10)	0.75	(19.05)	M71-R4300	\$52.77
Fig. 4	M71-29-489	500	B-489	White	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$53.26
Fig. 4	M71-32-489	250	B-489	White	1.50	(38.10)	1.50	(38.10)	M71-R4300	\$54.37
Fig. 4	M71-81-488	750	B-488	White	1.90	(48.26)	0.25	(6.35)	M71-R4300	\$61.45
Fig. 4	M71-20-459	100	B-459	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$23.45
Fig. 4	M71-61-483	100	B-483	White	2.00	(50.80)	0.50	(12.70)	M71-R6000	\$17.46
Fig. 4	M71-20-483	100	B-483	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$26.52
Fig. 4	M71-20-486	100	B-486	Silver	2.00	(50.80)	1.00	(25.40)	M71-R4300	\$34.33
Fig. 4	M71-37-483	100	B-483	White	3.00	(76.20)	1.90	(48.26)	M71-R6000	\$38.85
Fig. 4	M71-37-486	100	B-486	Silver	3.00	(76.20)	1.90	(48.26)	M71-R4300	\$49.49
Fig. 4	M71-23-483	100	B-483	White	4.00	(101.60)	1.00	(25.40)	M71-R6000	\$40.19
Fig. 4	M71-38-483	100	B-483	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$46.67
Fig. 4	M71-38-489	100	B-489	White	4.00	(101.60)	1.90	(48.26)	M71-R4300	\$46.67

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 8	M71C-375-430	1 Roll (cont.)	B-430	Clear	0.38	(9.53)	50 ft.	(15.24 m)	M71-R6000	\$50.46
Fig. 8	M71C-500-430	1 Roll (cont.)	B-430	Clear	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$50.46
Fig. 8	M71C-500-483	1 Roll (cont.)	B-483	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$56.94
Fig. 8	M71C-1000-430	1 Roll (cont.)	B-430	Clear	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$69.64
Fig. 8	M71C-1000-483	1 Roll (cont.)	B-483	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$78.80
Fig. 8	M71C-1900-430	1 Roll (cont.)	B-430	Clear	1.90	(48.26)	50 ft.	(15.24 m)	M71-R6000	\$104.22
Fig. 8	M71C-1900-483	1 Roll (cont.)	B-483	White	1.90	(48.26)	50 ft.	(15.24 m)	M71-R6000	\$117.40

* See all ribbon colors on page 14.



REQUEST A SAMPLE PACK AT:
www.BradyID.com/bmp71
www.BradyCanada.ca/bmp71



Circuit Board & Component ID

Various sizes and label types for marking relays, solenoids, switches, drive motors, and other components.




Figure 4




Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 8	M71C-500-423	1 Roll (cont.)	B-423	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$45.82

Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 4	M71-1-423	750	B-423	White	0.25	(6.35)	0.25	(6.35)	M71-R6000	\$25.30
Fig. 4	M71-3-423	500	B-423	White	0.38	(9.53)	0.38	(9.53)	M71-R6000	\$26.39
Fig. 4	M71-3-457	500	B-457	White	0.38	(9.53)	0.38	(9.53)	M71-R6000	\$92.48
Fig. 4	M71-4-423	500	B-423	White	0.40	(10.16)	0.40	(10.16)	M71-R6000	\$27.62
Fig. 4	M71-5-423	750	B-423	White	0.50	(12.70)	0.20	(5.08)	M71-R6000	\$35.79
Fig. 4	M71-6-423	750	B-423	White	0.50	(12.70)	0.28	(6.99)	M71-R6000	\$37.64
Fig. 4	BM71-7-423*	5000	B-423	White	0.50	(12.70)	0.50	(12.70)	M71-R6000	\$277.72
Fig. 4	M71-7-423	500	B-423	White	0.50	(12.70)	0.50	(12.70)	M71-R6000	\$33.11
Fig. 4	M71-6-473	750	B-473	White	0.50	(12.70)	0.28	(6.99)	M71-R6000	\$47.88
Fig. 4	M71-9-423	750	B-423	White	0.65	(16.51)	0.20	(5.08)	M71-R6000	\$39.71
Fig. 4	M71-9-426	750	B-426	Amber	0.65	(16.51)	0.20	(5.08)	M71-R4300	\$135.86
Fig. 4	M71-9-473	750	B-473	White	0.65	(16.51)	0.20	(5.08)	M71-R6000	\$49.73
Fig. 4	M71-10-457	750	B-457	White	0.75	(19.05)	0.25	(6.35)	M71-R6000	\$140.13
Fig. 4	M71-10-473	750	B-473	White	0.75	(19.05)	0.25	(6.35)	M71-R6000	\$51.19
Fig. 4	M71-10-423	750	B-423	White	0.75	(19.05)	0.25	(6.35)	M71-R6000	\$40.93
Fig. 4	M71-13-423	750	B-423	White	0.90	(22.86)	0.25	(6.35)	M71-R6000	\$43.62
Fig. 4	M71-13-426	750	B-426	Amber	0.90	(22.86)	0.25	(6.35)	M71-R4300	\$135.86
Fig. 4	M71-14-423	750	B-423	White	1.00	(25.40)	0.19	(4.75)	M71-R6000	\$46.29
Fig. 4	M71-15-423	750	B-423	White	1.00	(25.40)	0.28	(6.99)	M71-R6000	\$47.64
Fig. 4	BM71-16-423*	5000	B-423	White	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$275.00
Fig. 4	M71-16-423	500	B-423	White	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$39.21
Fig. 4	BM71-17-423*	5000	B-423	White	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$266.93
Fig. 4	M71-17-423	500	B-423	White	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$39.21
Fig. 4	BM71-19-423*	2500	B-423	White	1.00	(25.40)	1.00	(25.40)	M71-R6000	\$193.89
Fig. 4	M71-19-423	250	B-423	White	1.00	(25.40)	1.00	(25.40)	M71-R6000	\$27.73
Fig. 4	M71-16-426	500	B-426	Amber	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$151.97
Fig. 4	M71-17-426	500	B-426	Amber	1.00	(25.40)	0.50	(12.70)	M71-R4300	\$155.89
Fig. 4	M71-15-428	750	B-428	Silver	1.00	(25.40)	0.28	(6.99)	M71-R4300	\$62.55
Fig. 4	BM71-17-428*	5000	B-428	Silver	1.00	(25.40)	0.50	(12.70)	M71-R4300	\$357.59
Fig. 4	M71-17-428	500	B-428	Silver	1.00	(25.40)	0.50	(12.70)	M71-R4300	\$51.07
Fig. 4	M71-16-457	500	B-457	White	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$151.97
Fig. 4	M71-16-473	500	B-473	White	1.00	(25.40)	0.38	(9.53)	M71-R6000	\$49.12
Fig. 4	M71-17-473	500	B-473	White	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$49.12
Fig. 4	M71-24-423-BK	500	B-423	Black	1.13	(28.70)	0.50	(12.70)	M71-R6000	\$38.12
Fig. 4	M71-25-423	750	B-423	White	1.25	(31.75)	0.25	(6.35)	M71-R6000	\$50.22
Fig. 4	M71-27-423	750	B-423	White	1.50	(38.10)	0.13	(3.18)	M71-R6000	\$51.31
Fig. 4	M71-28-423	750	B-423	White	1.50	(38.10)	0.25	(6.35)	M71-R6000	\$57.17
Fig. 4	BM71-29-423*	5000	B-423	White	1.50	(38.10)	0.50	(12.70)	M71-R6000	\$306.90
Fig. 4	M71-29-423	500	B-423	White	1.50	(38.10)	0.50	(12.70)	M71-R6000	\$43.85
Fig. 4	M71-31-423	250	B-423	White	1.50	(38.10)	1.00	(25.40)	M71-R6000	\$31.52
Fig. 4	M71-32-423	250	B-423	White	1.50	(38.10)	1.50	(38.10)	M71-R6000	\$44.84
Fig. 4	M71-28-426	750	B-426	Amber	1.50	(38.10)	0.25	(6.35)	M71-R4300	\$178.50
Fig. 4	M71-29-428	500	B-428	Silver	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$58.76
Fig. 4	M71-28-473	750	B-473	White	1.50	(38.10)	0.25	(6.35)	M71-R6000	\$71.35
Fig. 4	M71-2-423	100	B-423	White	2.00	(50.80)	0.25	(6.35)	M71-R6000	\$16.97
Fig. 4	BM71-20-423*	1000	B-423	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$154.80
Fig. 4	M71-20-423	100	B-423	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$22.10
Fig. 4	BM71-20-424*	1000	B-424	White	2.00	(50.80)	1.00	(25.40)	M71-R4300	\$118.26
Fig. 4	M71-20-424	100	B-424	White	2.00	(50.80)	1.00	(25.40)	M71-R4300	\$16.87
Fig. 4	BM71-20-428*	1000	B-428	Silver	2.00	(50.80)	1.00	(25.40)	M71-R4300	\$218.80
Fig. 4	M71-20-428	100	B-428	Silver	2.00	(50.80)	1.00	(25.40)	M71-R4300	\$31.28
Fig. 4	M71-26-423	100	B-423	White	2.75	(69.85)	1.25	(31.75)	M71-R6000	\$32.12
Fig. 4	M71-26-428	100	B-428	White	2.75	(69.85)	1.25	(31.75)	M71-R4300	\$45.08
Fig. 4	M71-22-423	100	B-423	White	3.00	(76.20)	1.00	(25.40)	M71-R6000	\$26.64
Fig. 4	M71-37-423	100	B-423	White	3.00	(76.20)	1.90	(48.26)	M71-R6000	\$32.12
Fig. 4	M71-22-428	100	B-428	Silver	3.00	(76.20)	1.00	(25.40)	M71-R4300	\$37.51
Fig. 4	M71-23-423	100	B-423	White	4.00	(101.60)	1.00	(25.40)	M71-R6000	\$32.12
Fig. 4	M71-38-423	100	B-423	White	4.00	(101.60)	1.90	(48.26)	M71-R6000	\$38.36
Fig. 4	M71-38-428	100	B-428	White	4.00	(101.60)	1.90	(48.26)	M71-R4300	\$49.97

* "B" indicates bulk roll.

* See all ribbon colors on page 14.

Wire And Cable Markers

Durable vinyl cloth wrap around wire and cable markers. Firm adhesive can be removed cleanly and reapplied.




Figure 4




Figure 5




Figure 6




Figure 7




Figure 8




Figure 12

Wrap Around Wire ID Labels

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	A Inch	(mm)	B Inch	(mm)	C Inch	(mm)	Recommened Ribbon	Price
Fig. 6	M71-21-499	100	B-499	White	Cables	1.00	(25.40)	2.50	(63.50)	–	–	M71-R4300	\$36.17
Fig. 6	M71-21-498	100	B-498	White	Cables	1.00	(25.40)	2.50	(63.50)	–	–	M71-R6200	\$30.67
Fig. 6	M71-33-498	100	B-498	White	Cables	1.50	(38.10)	4.00	(101.60)	–	–	M71-R6200	\$49.49
Fig. 6	M71-10-498	750	B-498	White	16-10	0.25	(6.35)	0.75	(19.05)	–	–	M71-R6200	\$47.88
Fig. 12	M71-7-499	500	B-499	White	16-10	0.50	(12.70)	0.50	(12.70)	–	–	M71-R4300	\$46.91
Fig. 12	M71-7-498	500	B-498	White	16-10	0.50	(12.70)	0.50	(12.70)	–	–	M71-R6200	\$45.94
Fig. 6	BM71-11-499*	5000	B-499	White	16-10	0.50	(12.70)	0.75	(19.05)	–	–	M71-R4300	\$299.94
Fig. 6	M71-11-499	500	B-499	White	16-10	0.50	(12.70)	0.75	(19.05)	–	–	M71-R4300	\$42.76
Fig. 6	BM71-11-498*	5000	B-498	White	16-10	0.50	(12.70)	0.75	(19.05)	–	–	M71-R6200	\$292.73
Fig. 6	M71-11-498	500	B-498	White	16-10	0.50	(12.70)	0.75	(19.05)	–	–	M71-R6200	\$41.79
Fig. 6	M71-16-499	500	B-499	White	12-10	0.38	(9.53)	1.00	(25.40)	–	–	M71-R4300	\$51.31
Fig. 6	M71-16-498	500	B-498	White	12-10	0.38	(9.53)	1.00	(25.40)	–	–	M71-R6200	\$50.22
Fig. 6	M71-18-499	250	B-499	White	12-10	0.75	(19.05)	1.00	(25.40)	–	–	M71-R4300	\$35.31
Fig. 6	BM71-18-498*	2500	B-498	White	12-10	0.75	(19.05)	1.00	(25.40)	–	–	M71-R6200	\$234.94
Fig. 6	M71-18-498	250	B-498	White	12-10	0.75	(19.05)	1.00	(25.40)	–	–	M71-R6200	\$34.57
Fig. 12	M71-17-498	500	B-498	White	12-10	1.00	(25.40)	0.50	(12.70)	–	–	M71-R6200	\$52.77
Fig. 12	M71-19-499	250	B-499	White	12-10	1.00	(25.40)	1.00	(25.40)	–	–	M71-R4300	\$38.36
Fig. 12	BM71-19-498*	2500	B-498	White	12-10	1.00	(25.40)	1.00	(25.40)	–	–	M71-R6200	\$254.84
Fig. 12	M71-19-498	250	B-498	White	12-10	1.00	(25.40)	1.00	(25.40)	–	–	M71-R6200	\$37.51
Fig. 4	M71-78-499	250	B-499	White	12-10	1.90	(48.26)	1.00	(25.40)	–	–	M71-R4300	\$61.45
Fig. 6	M71-28-499	750	B-499	White	10-4	0.25	(6.35)	1.50	(38.10)	–	–	M71-R4300	\$49.97
Fig. 6	M71-29-499	500	B-499	White	10-4	0.50	(12.70)	1.50	(38.10)	–	–	M71-R4300	\$47.64
Fig. 6	BM71-29-498*	5000	B-498	White	10-4	0.50	(12.70)	1.50	(38.10)	–	–	M71-R6200	\$317.04
Fig. 6	M71-29-498	500	B-498	White	10-4	0.50	(12.70)	1.50	(38.10)	–	–	M71-R6200	\$46.67
Fig. 6	M71-30-499	250	B-499	White	10-4	0.75	(19.05)	1.50	(38.10)	–	–	M71-R4300	\$42.16
Fig. 6	M71-30-498	250	B-498	White	10-4	0.75	(19.05)	1.50	(38.10)	–	–	M71-R6200	\$41.06
Fig. 6	M71-31-499	250	B-499	White	10-4	1.00	(25.40)	1.50	(38.10)	–	–	M71-R4300	\$48.87
Fig. 6	M71-31-498	250	B-498	White	10-4	1.00	(25.40)	1.50	(38.10)	–	–	M71-R6200	\$47.64
Fig. 12	M71-32-498	250	B-498	White	10-4	1.50	(38.10)	1.50	(38.10)	–	–	M71-R6200	\$59.00
Fig. 5	M71C-240-498	1 Roll (cont.)	B-498	White	–	0.24	(6.09)	30 ft.	(9.10 m)	–	–	M71-R6200	\$39.58
Fig. 8	BM71C-240-498*	1 Roll (cont.)	B-498	White	–	0.24	(5.80)	275 ft.	(83.82 m)	–	–	M71-R6200	\$254.44
Fig. 5	M71C-318-498	1 Roll (cont.)	B-498	White	–	0.32	(8.07)	30 ft.	(9.10 m)	–	–	M71-R6200	\$40.68
Fig. 5	BM71C-318-498*	1 Roll (cont.)	B-498	White	–	0.32	(8.07)	275 ft.	(83.82 m)	–	–	M71-R6200	\$260.95
Fig. 5	M71C-375-498	1 Roll (cont.)	B-498	White	–	0.38	(9.53)	30 ft.	(9.10 m)	–	–	M71-R6200	\$41.30
Fig. 5	BM71C-375-498*	1 Roll (cont.)	B-498	White	–	0.38	(9.53)	275 ft.	(83.82 m)	–	–	M71-R6200	\$265.07
Fig. 8	M71C-500-499	1 Roll (cont.)	B-499	White	–	0.50	(12.70)	30 ft.	(9.10 m)	–	–	M71-R4300	\$29.62
Fig. 8	M71C-500-498	1 Roll (cont.)	B-498	White	–	0.50	(12.70)	30 ft.	(9.10 m)	–	–	M71-R6200	\$29.62
Fig. 4	M71-84-499	500	B-499	White	–	0.90	(22.86)	0.50	(12.70)	–	–	M71-R4300	\$44.10
Fig. 4	M71-17-489	500	B-489	White	–	1.00	(25.40)	0.50	(12.70)	–	–	M71-R4300	\$47.77
Fig. 8	M71C-1000-499	1 Roll (cont.)	B-499	White	–	1.00	(25.40)	30 ft.	(9.10 m)	–	–	M71-R4300	\$41.31
Fig. 8	M71C-1000-498	1 Roll (cont.)	B-498	White	–	1.00	(25.40)	30 ft.	(9.10 m)	–	–	M71-R6200	\$41.31
Fig. 4	M71-29-437	500	B-437	White	–	1.50	(38.10)	0.50	(12.70)	–	–	M71-R4300	\$67.16
Fig. 4	M71-81-499	750	B-499	White	–	1.90	(48.26)	0.25	(6.35)	–	–	M71-R4300	\$58.52
Fig. 8	M71C-1900-499	1 Roll (cont.)	B-499	White	–	1.90	(48.30)	30 ft.	(9.10 m)	–	–	M71-R4300	\$62.00
Fig. 8	M71C-1900-498	1 Roll (cont.)	B-498	White	–	1.90	(48.30)	30 ft.	(9.10 m)	–	–	M71-R6200	\$62.00

Fiber Optic Flags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	(mm)	B Inch	(mm)	Recommened Ribbon	Price
Fig. 23	M71FP-1-425	250	B-425	White	1.18	(30.00)	0.79	(20.00)	M71-R4300	\$22.60
Fig. 24	M71FT-1-425	250	B-425	White	1.18	(30.00)	0.79	(20.00)	M71-R4300	\$22.60
Fig. 23	M71FP-2-425	100	B-425	White	1.75	(44.45)	1.00	(25.40)	M71-R4300	\$22.60




Figure 23




Figure 24

* "B" indicates bulk roll.

** Flame retardant material.

* See all ribbon colors on page 14.

Self Laminating Wire Markers

Protected printing area offers superior chemical and abrasion resistance. Features a non-printed clear area that wraps around and overlaminates the printed text.




Figure 4




Figure 7




Figure 19



Self-Laminating Labels

Diagram	Part Number	Labels/ Roll	Material	Color	Approx. Wire Gauge	A Inch (mm)		B Inch (mm)		C Inch (mm)		Reccommended Ribbon	Price
Fig. 7	BM71-21-427*	1000	B-427	White	Cables	1.00	(25.40)	2.50	(63.50)	0.75	(19.05)	M71-R4300	\$178.85
Fig. 7	M71-21-427	100	B-427	White	Cables	1.00	(25.40)	2.50	(63.50)	0.75	(19.05)	M71-R4300	\$25.54
Fig. 7	M71-21-427-YL	100	B-427	Yellow	Cables	1.00	(25.40)	2.50	(63.50)	0.75	(19.05)	M71-R4300	\$32.01
Fig. 19	BM71-64-427*	1000	B-427	White	Cables	1.00	(25.40)	3.38	(85.73)	1.13	(28.58)	M71-R4300	\$109.51
Fig. 19	M71-64-427	100	B-427	White	Cables	1.00	(25.40)	3.38	(85.73)	1.13	(28.58)	M71-R4300	\$15.64
Fig. 7	BM71-23-427*	1000	B-427	White	Cables	1.00	(25.40)	4.00	(101.60)	1.00	(25.40)	M71-R4300	\$213.56
Fig. 7	M71-23-427	100	B-427	White	Cables	1.00	(25.40)	4.00	(101.60)	1.00	(25.40)	M71-R4300	\$30.42
Fig. 7	BM71-109-427*	500	B-427	White	Cables	1.50	(38.10)	4.00	(101.60)	1.50	(38.10)	M71-R4300	\$144.03
Fig. 7	BM71-33-427*	500	B-427	White	Cables	1.50	(38.10)	4.00	(101.60)	1.00	(25.40)	M71-R4300	\$144.03
Fig. 7	M71-109-427	100	B-427	White	Cables	1.50	(38.10)	4.00	(101.60)	1.50	(38.10)	M71-R4300	\$41.17
Fig. 7	M71-33-427	100	B-427	White	Cables	1.50	(38.10)	4.00	(101.60)	1.00	(25.40)	M71-R4300	\$41.17
Fig. 7	M71-33-427-YL	100	B-427	Yellow	Cables	1.50	(38.10)	4.00	(101.60)	1.00	(25.40)	M71-R4300	\$51.56
Fig. 7	BM71-34-427*	500	B-427	White	Cables	1.50	(38.10)	6.00	(152.40)	1.50	(38.10)	M71-R4300	\$238.48
Fig. 7	M71-34-427	50	B-427	White	Cables	1.50	(38.10)	6.00	(152.40)	1.50	(38.10)	M71-R4300	\$34.09
Fig. 7	M71-66-427	100	B-427	White	Cables	1.94	(49.23)	3.15	(80.00)	1.00	(25.40)	M71-R4300	\$41.17
Fig. 7	M71-10-427	750	B-427	White	16-10	0.25	(6.35)	0.75	(19.05)	0.38	(9.53)	M71-R4300	\$32.62
Fig. 7	BM71-11-427*	5000	B-427	White	16-10	0.50	(12.70)	0.75	(19.05)	0.38	(9.53)	M71-R4300	\$242.88
Fig. 7	M71-11-427	500	B-427	White	16-10	0.50	(12.70)	0.75	(19.05)	0.38	(9.53)	M71-R4300	\$34.69
Fig. 7	M71-96-427	250	B-427	White	16-10	1.00	(25.40)	0.75	(19.05)	0.38	(9.53)	M71-R4300	\$23.69
Fig. 7	BM71-17-427*	5000	B-427	White	12-10	0.50	(12.70)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$259.75
Fig. 7	M71-17-427	500	B-427	White	12-10	0.50	(12.70)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$37.14
Fig. 7	BM71-19-427*	2500	B-427	White	12-10	1.00	(25.40)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$233.11
Fig. 7	M71-19-427	250	B-427	White	12-10	1.00	(25.40)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$33.36
Fig. 7	M71-19-427-YL	250	B-427	Yellow	12-10	1.00	(25.40)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$36.77
Fig. 7	M71-104-427	250	B-427	White	12-10	1.50	(38.10)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$42.76
Fig. 7	M71-28-427	750	B-427	White	10-4	0.25	(6.35)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$41.54
Fig. 7	BM71-29-427*	5000	B-427	White	10-4	0.50	(12.70)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$317.64
Fig. 7	M71-29-427	500	B-427	White	10-4	0.50	(12.70)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$45.45
Fig. 7	BM71-18-427*	2500	B-427	White	10-4	0.75	(19.05)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$212.70
Fig. 7	M71-18-427	250	B-427	White	10-4	0.75	(19.05)	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$30.31
Fig. 7	BM71-30-427*	2500	B-427	White	10-4	0.75	(19.05)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$236.65
Fig. 7	M71-30-427	250	B-427	White	10-4	0.75	(19.05)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$33.85
Fig. 7	M71-30-427-BL	250	B-427	Blue	10-4	0.75	(19.05)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$42.28
Fig. 7	M71-30-427-PL	250	B-427	Purple	10-4	0.75	(19.05)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$42.28
Fig. 7	M71-30-427-RD	250	B-427	Red	10-4	0.75	(19.05)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$42.28
Fig. 7	M71-103-427	250	B-427	White	10-4	1.00	(25.40)	1.25	(31.75)	0.50	(12.70)	M71-R4300	\$39.34
Fig. 7	BM71-31-427*	2500	B-427	White	10-4	1.00	(25.40)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$299.94
Fig. 7	M71-31-427	250	B-427	White	10-4	1.00	(25.40)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$42.76
Fig. 7	M71-31-427-GN	250	B-427	Green	10-4	1.00	(25.40)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$54.50
Fig. 7	M71-31-427-RD	250	B-427	Red	10-4	1.00	(25.40)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$54.50
Fig. 7	M71-31-427-YL	250	B-427	Yellow	10-4	1.00	(25.40)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$54.50
Fig. 4	M71-30-427-AW	250	B-427	White	10-4	1.50	(38.10)	0.75	(19.05)	—	—	M71-R4300	\$33.85
Fig. 7	BM71-32-427*	1000	B-427	White	10-4	1.50	(38.10)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$123.39
Fig. 7	M71-32-427	250	B-427	White	10-4	1.50	(38.10)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$44.22
Fig. 7	M71-32-427-YL	250	B-427	Yellow	10-4	1.50	(38.10)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$54.86
Fig. 7	M71-88-427	250	B-427	White	10-4	1.75	(44.45)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$57.79
Fig. 7	BM71-107-427*	1000	B-427	White	10-4	2.00	(50.80)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$359.19
Fig. 7	M71-107-427	100	B-427	White	10-4	2.00	(50.80)	1.50	(38.10)	0.50	(12.70)	M71-R4300	\$52.91

* "B" indicates bulk roll.

* See all ribbon colors on page 14.

PermaSleeves™ Wire Markers

These full circle heat-shrink sleeves are the ultimate in marker durability, permanence and aesthetic appearance. Fast shrink rate saves time and costs during installation.



Figure 8




Figure 20



PermaSleeve Markers (Shrink Ratio 3-to-1)

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	Label Dimensions			Recommended Ribbon	Price
A Inch (mm)	B Inch (mm)									
Fig. 8	BM71C-94-342*	1 Roll (cont.)	B-342	White	28-18	0.18 (4.62)	50 ft. (15.24 m)		M71-R4300	\$186.00
Fig. 20	M71-94-1-342	100	B-342	White	28-18	1.02 (25.78)	0.18 (4.62)		M71-R4300	\$42.64
Fig. 20	M71-94-1-342YL	100	B-342	Yellow	28-18	1.02 (25.78)	0.18 (4.62)		M71-R4300	\$43.00
Fig. 20	BM71-94-175-342*	2500	B-342	White	28-18	1.77 (44.83)	0.18 (4.62)		M71-R4300	\$1,011.93
Fig. 20	BM71-94-175-342YL*	2500	B-342	Yellow	28-18	1.77 (44.83)	0.18 (4.62)		M71-R4300	\$1,011.93
Fig. 20	M71-94-175-342	100	B-342	White	28-18	1.77 (44.83)	0.18 (4.62)		M71-R4300	\$57.90
Fig. 20	M71-94-175-342YL	100	B-342	Yellow	28-18	1.77 (44.83)	0.18 (4.62)		M71-R4300	\$57.90
Fig. 8	BM71C-125-342*	1 Roll (cont.)	B-342	White	22-16	0.24 (5.96)	50 ft. (15.24 m)		M71-R4300	\$198.00
Fig. 20	BM71-125-1-342*	1000	B-342	White	22-16	1.02 (25.78)	0.24 (5.96)		M71-R4300	\$315.81
Fig. 20	M71-125-1-342	100	B-342	White	22-16	1.02 (25.78)	0.24 (5.96)		M71-R4300	\$45.20
Fig. 20	M71-125-1-342YL	100	B-342	Yellow	22-16	1.02 (25.78)	0.24 (5.96)		M71-R4300	\$45.20
Fig. 20	BM71-125-175-342*	1000	B-342	White	22-16	1.77 (44.83)	0.24 (5.96)		M71-R4300	\$424.30
Fig. 20	BM71-125-175-342YL*	1000	B-342	Yellow	22-16	1.77 (44.83)	0.24 (5.96)		M71-R4300	\$424.30
Fig. 20	M71-125-175-342	100	B-342	White	22-16	1.77 (44.83)	0.24 (5.96)		M71-R4300	\$60.71
Fig. 20	M71-125-175-342YL	100	B-342	Yellow	22-16	1.77 (44.83)	0.24 (5.96)		M71-R4300	\$60.71
Fig. 8	BM71C-187-342*	1 Roll (cont.)	B-342	White	18-12	0.34 (8.50)	50 ft. (15.24 m)		M71-R4300	\$210.00
Fig. 20	BM71-187-1-342*	100	B-342	White	18-12	1.02 (25.78)	0.34 (8.50)		M71-R4300	\$352.33
Fig. 20	BM71-187-1-342YL*	1000	B-342	Yellow	18-12	1.02 (25.78)	0.34 (8.50)		M71-R4300	\$352.33
Fig. 20	M71-187-1-342	100	B-342	White	18-12	1.02 (25.78)	0.34 (8.50)		M71-R4300	\$50.33
Fig. 20	M71-187-1-342YL	100	B-342	Yellow	18-12	1.02 (25.78)	0.34 (8.50)		M71-R4300	\$50.33
Fig. 20	BM71-187-175-342*	1000	B-342	White	18-12	1.77 (44.83)	0.34 (8.50)		M71-R4300	\$458.63
Fig. 20	BM71-187-175-342YL*	1000	B-342	Yellow	18-12	1.77 (44.83)	0.34 (8.50)		M71-R4300	\$458.63
Fig. 20	M71-187-175-342	100	B-342	White	18-12	1.77 (44.83)	0.34 (8.50)		M71-R4300	\$67.43
Fig. 20	M71-187-175-342YL	100	B-342	Yellow	18-12	1.77 (44.83)	0.34 (8.50)		M71-R4300	\$67.43
Fig. 8	BM71C-250-342*	1 Roll (cont.)	B-342	White	16-10	0.44 (11.15)	50 ft. (15.24 m)		M71-R4300	\$270.00
Fig. 20	BM71-250-1-342*	1000	B-342	White	16-10	1.02 (25.78)	0.44 (11.15)		M71-R4300	\$426.26
Fig. 20	M71-250-1-342	100	B-342	White	16-10	1.02 (25.78)	0.44 (11.15)		M71-R4300	\$60.97
Fig. 20	M71-250-1-342YL	100	B-342	Yellow	16-10	1.02 (25.78)	0.44 (11.15)		M71-R4300	\$60.97
Fig. 20	BM71-250-175-342*	1000	B-342	White	16-10	1.77 (44.83)	0.44 (11.15)		M71-R4300	\$573.84
Fig. 20	BM71-250-175-342YL*	1000	B-342	Yellow	16-10	1.77 (44.83)	0.44 (11.15)		M71-R4300	\$573.84
Fig. 20	M71-250-175-342	100	B-342	White	16-10	1.77 (44.83)	0.44 (11.15)		M71-R4300	\$82.10
Fig. 20	M71-250-175-342YL	100	B-342	Yellow	16-10	1.77 (44.83)	0.44 (11.15)		M71-R4300	\$81.84
Fig. 8	BM71C-375-342*	1 Roll (cont.)	B-342	White	12-6	0.65 (16.38)	50 ft. (15.24 m)		M71-R4300	\$396.00
Fig. 20	BM71-375-1-342*	1000	B-342	White	12-6	1.02 (25.78)	0.65 (16.38)		M71-R4300	\$629.05
Fig. 20	M71-375-1-342	100	B-342	White	12-6	1.02 (25.78)	0.65 (16.38)		M71-R4300	\$89.81
Fig. 20	M71-375-1-342YL	100	B-342	Yellow	12-6	1.02 (25.78)	0.65 (16.38)		M71-R4300	\$89.81
Fig. 20	BM71-375-175-342*	1000	B-342	White	12-6	1.77 (44.83)	0.65 (16.38)		M71-R4300	\$845.30
Fig. 20	M71-375-175-342	100	B-342	White	12-6	1.77 (44.83)	0.65 (16.38)		M71-R4300	\$120.82
Fig. 20	M71-375-175-342YL	100	B-342	Yellow	12-6	1.77 (44.83)	0.65 (16.38)		M71-R4300	\$120.82
Fig. 8	BM71C-500-342*	1 Roll (cont.)	B-342	White	8-1	0.85 (21.61)	50 ft. (15.24 m)		M71-R4300	\$456.00
Fig. 20	BM71-500-1-342*	1000	B-342	White	8-1	1.02 (25.78)	0.85 (21.61)		M71-R4300	\$726.79
Fig. 20	BM71-500-1-342YL*	1000	B-342	Yellow	8-1	1.02 (25.78)	0.85 (21.61)		M71-R4300	\$726.79
Fig. 20	M71-500-1-342	100	B-342	White	8-1	1.02 (25.78)	0.85 (21.61)		M71-R4300	\$103.84
Fig. 20	M71-500-1-342YL	100	B-342	Yellow	8-1	1.02 (25.78)	0.85 (21.61)		M71-R4300	\$103.84
Fig. 20	BM71-500-175-342*	1000	B-342	White	8-1	1.77 (44.83)	0.85 (21.61)		M71-R4300	\$977.73
Fig. 20	BM71-500-175-342YL*	1000	B-342	Yellow	8-1	1.77 (44.83)	0.85 (21.61)		M71-R4300	\$977.73
Fig. 20	M71-500-175-342	100	B-342	White	8-1	1.77 (44.83)	0.85 (21.61)		M71-R4300	\$139.63
Fig. 20	M71-500-175-342YL	100	B-342	Yellow	8-1	1.77 (44.83)	0.85 (21.61)		M71-R4300	\$139.63
Fig. 20	M71-1000-1-342	50	B-342	White	1-500	1.02 (25.78)	1.66 (42.16)		M71-R4300	\$71.72
Fig. 20	M71-1000-1-342YL	50	B-342	Yellow	1-500	1.02 (25.78)	1.66 (42.16)		M71-R4300	\$71.72
Fig. 8	BM71C-1000-342*	1 Roll (cont.)	B-342	White	1-500	1.66 (42.16)	50 ft. (15.24 m)		M71-R4300	\$630.00
Fig. 20	BM71-1000-175-342*	500	B-342	White	1-500	1.77 (44.83)	1.66 (42.16)		M71-R4300	\$679.75
Fig. 20	M71-1000-175-342	50	B-342	White	1-500	1.77 (44.83)	1.66 (42.16)		M71-R4300	\$97.14
Fig. 20	M71-1000-175-342YL	50	B-342	Yellow	1-500	1.77 (44.83)	1.66 (42.16)		M71-R4300	\$97.14

* "B" indicates bulk roll.

* See all ribbon colors on page 14.

PermaSleeves™ Wire Markers (Continued)




Figure 26



Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 26	M71-111-145FR-GY	100	B-145FR	Grey	1.21	(30.63)	0.76	(19.25)	M71-R6000	\$33.60
Fig. 26	BM71-111-145-GY*	1000	B-145	Grey	1.21	(30.63)	0.76	(19.25)	M71-R6000	\$213.81
Fig. 26	M71-111-145-GY	100	B-145	Grey	1.21	(30.63)	0.76	(19.25)	M71-R6000	\$30.53
Fig. 26	M71-110-145FR-GY	100	B-145FR	Grey	1.75	(44.45)	1.00	(25.40)	M71-R6000	\$33.60
Fig. 26	BM71-110-145-GY*	1000	B-145	Grey	1.75	(44.45)	1.00	(25.40)	M71-R6000	\$213.81
Fig. 26	M71-110-145-GY	100	B-145	Grey	1.75	(44.45)	1.00	(25.40)	M71-R6000	\$30.53

Voice/Data Comm

Durable materials with permanent adhesive in a variety of sizes for marking racks, bays, frames, slots, and other voice/data equipment.




Figure 3




Figure 4




Figure 5




Figure 8




Figure 31



Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 4	M71-45-422	500	B-422	White	1.05	(38.10)	0.38	(9.53)	M71-R6000	\$48.75
Fig. 4	M71-30-422	250	B-422	White	1.50	(38.10)	0.75	(19.05)	M71-R6000	\$45.69
Fig. 4	BM71-20-422*	1000	B-422	White	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$178.85
Fig. 4	M71-37-422	100	B-422	White	3.00	(76.20)	1.90	(48.26)	M71-R6000	\$38.12

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 8	M71C-375-422	1 Roll (cont.)	B-422	White	0.38	(9.53)	50 ft.	(15.24 m)	M71-R6000	\$54.37
Fig. 5	M71C-475-422	1 Roll (cont.)	B-422	White	0.48	(12.10)	50 ft.	(15.24 m)	M71-R6000	\$62.53
Fig. 8	M71C-500-422	1 Roll (cont.)	B-422	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$54.37
Fig. 8	M71C-625-422	1 Roll (cont.)	B-422	White	0.63	(15.88)	50 ft.	(15.24 m)	M71-R6000	\$75.74
Fig. 8	M71C-1000-422	1 Roll (cont.)	B-422	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$75.15
Fig. 8	M71C-1900-422	1 Roll (cont.)	B-422	White	1.90	(48.26)	50 ft.	(15.24 m)	M71-R6000	\$112.65

Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 3	M71C-230-412	1 Roll (cont.)	B-412	White	0.23	(5.84)	50 ft.	(15.24 m)	M71-R6200	\$45.32
Fig. 3	M71C-375-412	1 Roll (cont.)	B-412	White	0.38	(9.53)	50 ft.	(15.24 m)	M71-R6200	\$47.77
Fig. 5	M71C-475-412	1 Roll (cont.)	B-412	White	0.48	(12.10)	50 ft.	(15.24 m)	M71-R6200	\$50.33
Fig. 3	M71C-500-412	1 Roll (cont.)	B-412	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6200	\$50.33
Fig. 5	M71C-625-412	1 Roll (cont.)	B-412	White	0.63	(15.90)	50 ft.	(15.24 m)	M71-R6200	\$60.96
Fig. 3	M71C-785-412	1 Roll (cont.)	B-412	White	0.79	(19.94)	50 ft.	(15.24 m)	M71-R6200	\$69.64
Fig. 31	BM71-40-412*	5000	B-412	White	1.94	(49.23)	0.38	(9.53)	M71-R6200	\$265.72
Fig. 31	M71-40-412	750	B-412	White	1.94	(49.23)	0.38	(9.53)	M71-R6200	\$57.06

Printable Tags

Polyethylene material that is tear and chemical/solvent resistance.




Figure 21




Figure 32



Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 21	M71-36-109	250	B-109	White	1.13	(28.57)	1.75	(44.45)	M71-R4300	\$45.94
Fig. 32	BM71-12-109*	1000	B-109	White	3.00	(76.20)	0.75	(19.05)	M71-R4300	\$240.19
Fig. 32	M71-12-109	100	B-109	White	3.00	(76.20)	0.75	(19.05)	M71-R4300	\$34.33

* "B" indicates bulk roll.

* See all ribbon colors on page 14.

Tamper Indicating

Tamper resistant tape destructs into tiny fragments when being removed. Making any attempts to remove the label very difficult and time consuming.




Figure 4




Figure 8



Tamper Resistant Labels

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 4	M71-17-352	500	B-352	Silver	1.00	(25.40)	0.50	(12.70)	M71-R6000	\$50.09
Fig. 4	M71-17-351	500	B-351	White	1.00	(25.40)	0.50	(12.70)	M71-R6200	\$49.73
Fig. 4	M71-31-352	250	B-352	Silver	1.50	(38.10)	1.00	(25.40)	M71-R6000	\$39.95
Fig. 4	M71-31-351	250	B-351	White	1.50	(38.10)	1.00	(25.40)	M71-R6200	\$39.95
Fig. 4	M71-20-352	100	B-352	Silver	2.00	(50.80)	1.00	(25.40)	M71-R6000	\$30.53
Fig. 4	M71-20-351	100	B-351	White	2.00	(50.80)	1.00	(25.40)	M71-R6200	\$30.53
Fig. 4	M71-37-352	100	B-352	Silver	3.00	(76.20)	1.90	(48.26)	M71-R6000	\$44.10
Fig. 4	M71-37-351	100	B-351	White	3.00	(76.20)	1.90	(48.26)	M71-R6200	\$44.22

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 8	M71C-500-530	1 Roll (cont.)	B-530	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$53.21
Fig. 8	M71C-1000-530	1 Roll (cont.)	B-530	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$70.53
Fig. 8	M71C-2000-530	1 Roll (cont.)	B-530	White	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$105.17

Static Dissipative

Low profile polyimide material that has a static dissipative liner. Primarily used for printed circuit boards and electronic component labeling.




Figure 4



Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 4	M71-4-478	500	B-478	White	0.40	(10.16)	0.40	(10.16)	M71-R6000	\$72.44
Fig. 4	M71-9-478	750	B-478	White	0.65	(16.51)	0.20	(5.08)	M71-R6000	\$108.72
Fig. 4	M71-14-477	750	B-477	White	1.00	(25.40)	0.19	(4.75)	M71-R6000	\$140.13
Fig. 4	M71-25-478	750	B-478	White	1.25	(31.75)	0.25	(6.35)	M71-R6000	\$137.08
Fig. 4	M71-2-477	100	B-477	White	2.00	(50.80)	0.25	(6.35)	M71-R6000	\$39.71

Laboratory Identification

Self Laminating labels are great for vials, tubes, straws and more. Good for high and low temperature applications.




Figure 1




Figure 15




Figure 18



Self Laminating Labels

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions				Recommended Ribbon	Price
					A Inch	(mm)	B Inch	(mm)		
Fig. 1	M71-82-499	500	B-499	White	0.37 dia.	(9.53 dia.)	—	—	M71-R4300	\$31.52
Fig. 1	M71-83-499	500	B-499	White	0.50 dia.	(12.70 dia.)	—	—	M71-R4300	\$31.52
Fig. 15	M71-98-499	500	B-499	White	1.00	(25.40)	0.38	(9.53)	M71-R4300	\$62.19
Fig. 18	BM71-75-461*	1000	B-461	White	1.00	(25.40)	2.63	(66.68)	M71-R4300	\$233.97

Temporary/Removable

These indoor labels are designed with special adhesive that makes it easy to remove and re-apply.




Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Reccommended Ribbon	Price
Fig. 8	M71C-500-581-WT	1 Roll (cont.)	B-581	White	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$46.56
Fig. 8	M71C-500-581-YL	1 Roll (cont.)	B-581	Yellow	0.50	(12.70)	50 ft.	(15.24 m)	M71-R6000	\$46.56
Fig. 8	M71C-1000-581-WT	1 Roll (cont.)	B-581	White	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$65.21
Fig. 8	M71C-1000-581-YL	1 Roll (cont.)	B-581	Yellow	1.00	(25.40)	50 ft.	(15.24 m)	M71-R6000	\$65.21
Fig. 8	M71C-2000-581-WT	1 Roll (cont.)	B-581	White	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$98.50
Fig. 8	M71C-2000-581-YL	1 Roll (cont.)	B-581	Yellow	2.00	(50.80)	50 ft.	(15.24 m)	M71-R6000	\$98.50

Low Light Applications

B-582 Bradyglo phosphorescent material is light absorbing and will glow for 10 hours. B-584 reflective material helps to illuminate the labels when light is shined on the surface.

These two materials are great for egress and other critical pieces of information.




Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	(mm)	Reccommended Ribbon	Price
Fig. 8	BM71C-1000-584-OR*	1 Roll (cont.)	B-584	Orange	1.00	(25.40)	75 ft.	(22.86 m)	M71-R6000	\$122.00
Fig. 8	BM71C-1000-584-WT*	1 Roll (cont.)	B-584	White	1.00	(25.40)	75 ft.	(22.86 m)	M71-R6000	\$122.00
Fig. 8	BM71C-1000-584-YL*	1 Roll (cont.)	B-584	Yellow	1.00	(25.40)	75 ft.	(22.86 m)	M71-R6000	\$122.00
Fig. 8	BM71C-1000-582*	1 Roll (cont.)	B-582	Phosphorescent	1.00	(25.40)	75 ft.	(22.86 m)	M71-R6000	\$122.00
Fig. 8	BM71C-2000-584-OR*	1 Roll (cont.)	B-584	Orange	2.00	(50.80)	75 ft.	(22.86 m)	M71-R6000	\$195.42
Fig. 8	BM71C-2000-584-WT*	1 Roll (cont.)	B-584	White	2.00	(50.80)	75 ft.	(22.86 m)	M71-R6000	\$195.42
Fig. 8	BM71C-2000-584-YL*	1 Roll (cont.)	B-584	Yellow	2.00	(50.80)	75 ft.	(22.86 m)	M71-R6000	\$195.42
Fig. 8	BM71C-2000-582*	1 Roll (cont.)	B-582	Phosphorescent	2.00	(50.80)	75 ft.	(22.86 m)	M71-R6000	\$195.42

* "B" indicates bulk roll.

* See all ribbon colors on page 14.

ToughStripe® Print-On-Demand Floor Labels

- Create custom-printed floor labels using your BMP®71 Label Printer!
- Same durability and performance as ToughStripe® floor marking tape
- Easy 3-step process: print label, position on floor, apply overlamine




Figure 8



Description	Catalog Number	
	1" x 100' (\$122.40)	2" x 100' (\$183.70)
White	M71-1000-483-WT-KT	M71-2000-483-WT-KT
Black	M71-1000-483-BK-KT	M71-2000-483-BK-KT
Yellow	M71-1000-483-YL-KT	M71-2000-483-YL-KT
Red	M71-1000-483-RD-KT	M71-2000-483-RD-KT
Blue	M71-1000-483-BL-KT	M71-2000-483-BL-KT
Green	M71-1000-483-GN-KT	M71-2000-483-GN-KT
Orange	M71-1000-483-OR-KT	M71-2000-483-OR-KT





BMP®71 Ribbons

Part Number	Description	Size	Price	Part Number	Description	Size	Price
M71-R4300	Black Ribbon	150' (45.72 m)	\$53.66	M71-R6800-WT	White Ribbon	150' (45.72 m)	\$69.85
M71-R6000	Black Ribbon	150' (45.72 m)	\$53.66	M71-R6900-RD	Red Ribbon	150' (45.72 m)	\$63.42
M71-R6200	Black Ribbon	150' (45.72 m)	\$53.66	M71-R6900-BL	Blue Ribbon	150' (45.72 m)	\$63.42
M71-R6400	Black Ribbon	150' (45.72 m)	\$59.02	M71-R6900-GR	Green Ribbon	150' (45.72 m)	\$63.42
M71-R6600	Black Ribbon	150' (45.72 m)	\$69.85	M71-R6900-MA	Magenta Ribbon	150' (45.72 m)	\$63.42
M71-R4400-WT	White Ribbon	150' (45.72 m)	\$63.42	M71-R6900-YL	Yellow Ribbon	150' (45.72 m)	\$51.16

B-Number	Material	M71-R4300 (Black)	M71-R6000 (Black)	M71-R6200 (Black)	M71-R6400 (Black)	M71-R6600 (Black)	M71-R4400-WT (White)	M71-R6800-WT (White)	M71-R6900 (Colors)
B-109	Tag	●	—	▲	—	—	—	—	—
B-145	Tag	—	●	—	—	—	▲	—	—
B-145FR	Tag	—	●	—	—	—	▲	—	▲
B-321*	Polyolefin	—	—	●	—	—	—	—	—
B-341	Polyolefin	●	—	—	—	—	—	—	—
B-342	Polyolefin	●	—	—	—	—	—	—	—
B-345*	High Temp Sleeve	—	—	—	—	●	—	▲	—
B-351	Vinyl	—	—	●	—	—	—	—	—
B-352	Vinyl	—	●	—	—	—	▲	—	▲
B-353*	Paper	●	—	—	—	—	—	—	—
B-390*	Polypropylene	—	●	—	—	—	▲	—	▲
B-412	Polypropylene	▲	—	●	—	—	—	—	—
B-422	Polyester	—	● UL	—	—	—	▲	—	▲
B-423	Polyester	—	● UL	▲	—	—	▲	—	▲
B-424	Paper	●	—	—	—	—	—	—	—
B-425	Polyimide	●	—	—	—	—	—	—	—
B-426	Polyimide	●	—	—	—	—	—	—	—
B-427	Vinyl	● UL	—	▲	—	—	—	—	—
B-428	Polyester	● UL	—	—	—	—	—	—	—
B-430	Polyester	—	● UL	▲	—	—	▲	—	▲
B-432*	Polyester	—	● UL	—	—	—	▲	—	▲
B-433*	Polyester	—	● UL	—	—	—	▲	—	▲
B-435*	Polyester	—	● UL	—	—	—	▲	—	▲
B-439*	Vinyl	—	●	▲	—	—	▲	—	▲
B-457	Polyimide	—	● UL	—	—	—	▲	—	▲
B-459	Polyester	—	● UL	—	—	—	▲	—	▲
B-461	Polyester	●	—	▲	—	—	—	—	—
B-473	Polyester	—	● UL	▲	—	—	▲	—	▲
B-477	Polyimide	—	● UL	▲	—	—	▲	—	▲
B-478	Polyimide	—	● UL	—	—	—	▲	—	▲
B-479*	Polyimide	—	● UL	—	—	—	▲	—	▲
B-481*	Polyester	—	—	—	●	—	—	—	—
B-483	Polyester	—	● UL	▲	—	—	▲	—	▲
B-486	Polyester	● UL	—	—	—	—	—	—	—
B-488	Polyester	● UL	—	▲	—	—	—	—	—
B-489	Polyester	● UL	—	—	—	—	—	—	—
B-490*	Polyester	●	—	—	—	—	—	—	—
B-495*	Polyethylene Napthalate	—	● UL	—	—	—	▲	—	▲
B-498	Vinyl Cloth	▲	—	●	—	—	—	—	—
B-499	Nylon Cloth	● UL	—	▲	—	—	—	—	—
B-529	Polypropylene	—	●	—	—	—	▲	—	▲
B-530	Tamper Resistant	—	●	—	—	—	▲	—	▲
B-595	Vinyl	—	●	—	—	—	▲	—	▲
B-581	Vinyl	—	●	—	—	—	▲	—	▲
B-582	Phosphorescent	—	●	—	—	—	▲	—	▲
B-584	Reflective	—	●	—	—	—	▲	—	▲
B-593	Polyester	—	●	—	—	—	▲	—	▲
B-7531*	Metalized Polyester	●	—	—	—	—	—	—	—
B-7536*	Polyester	—	—	●	—	—	—	—	—
B-7546*	Tamper-Evident Polyester	—	● UL	—	—	—	▲	—	▲
B-7551*	Polyester	—	—	●	—	—	—	—	—
B-7566*	Tamper-Evident Polyester	—	●	—	—	—	▲	—	▲
B-7576*	Tamper-Evident Metalized Polyester	—	● UL	—	—	—	—	—	—
B-7593*	Polyethelene	—	●	—	—	—	▲	—	▲
B-7596*	Vinyl	—	—	●	—	—	—	—	—
B-7597*	Polyethelene	●	—	—	—	—	—	—	—
B-7599*	Polyethelene Tag	●	—	—	—	—	—	—	—
B-7643*	Thermosplastic Polyether Polyurethane	—	●	—	—	—	▲	—	▲
B-7696*	Vinyl Tag	—	●	—	—	—	▲	—	▲
B-8425*	Polypropylene	—	● UL	—	—	—	▲	—	▲

*TLS@2200 materials that can be used in the BMP®71 Label Printer.

●	Recommended ribbon for use with respective material.
▲	Acceptable ribbon for use with respective material.
UL	These materials are UL recognized with its respective ribbon.



BMP®71 PRINTER APPLICATIONS

Visual Workplace



M71C-1000-580-WT M71-R6900BL

Multi-Line Labels



M71C-2000-580-RD M71-R6900WT

Vinyl Pipe Markers Up To 2" Wide



M71C-1000-580-BL
M71-R6900WT



Glow-In-The-Dark



M71C-1000-582 M71-R6900GN

Floor Labeling Solutions




M71C-2000-580-YL M71-R6000



SEE THE POSSIBILITIES WITH THE E

Work Station Labels



M71-40-412 M71-R6200

Die Cut Labels




M71-7-423 M71-R6000

Equipment Labels



M71-30-428-CALI M71-R4300

Patch Panel Labels




M71C-375-422 M71-R6000

Power and Ground Cable Tags



M71-111-145FR-GY M71-R6000

Flags/Fiber Optic Labels



M71FP-2-425 M71-R4300


M71FD-2-425 M71-R4300

Wire Bundle Labels




M71-12-109 M71-R4300

PermaSleeve™ Heat-Shrink Sleeves



BM71-187-1-342 M71-R4300

Self-Laminating Labels



M71-31-427-YL M71-R4300

3MP®71 LABEL PRINTER

Arc Flash Labels




M71-38-483-WARN M71-R6000

Labels Withstand High Temperatures



M71-38-483-DANG M71-R6000

Framed Labels



M71-24-423-BK M71-R6000

Control Panel Labels



M71EP-167-593-RD M71-R6000

Pre-Printed Labels




M71-25-478 M71-R6000

Create Tags With Bar Codes



M71-20-423 M71-R6000

Tamper Indicating Tape



M71-17-352 M71-R6000

* Most labels are actual size.

THE ALL-IN-ONE LABELER FOR YOUR WHOLE CREW

Catalog Number	Description	Catalog Number	Description
BMP71*	BMP®71 Label Printer	BMP71-SC-QC	BMP®71 Label Printer with Soft Case and Quick Charger
BMP71-LM	BMP®71 Label Printer with LabelMark Software	M71-AC-BC	BMP®71 AC/Battery Adaptor
BMP71-MW	BMP®71 Label Printer with Markware Lean Software	M71-ADAPT	TLS/Handimark Media Adaptor
BMP71-360-KIT	BMP®71 Label Printer with Brady 360 Replacement Printer Program	M71-BATT	BMP®71 Battery Pack
BMP71-QC	BMP®71 Label Printer with Quick Charger	M71-CABLE	BMP®71 USB Cable
BMP71-SC	BMP®71 Label Printer with Soft Case	M71-CLEAN	BMP®71 Cleaning Kit
		M71-HC	BMP®71 Hardcase
		M71-QC	BMP®71 Quick Charger
		M71-SC	BMP®71 Softcase
		BMP71-360	Brady 360 Replacement Printer Program



BMP®71 LABEL PRINTER
*Label printer ships with Hardcase, Charger/ AC Adapter, 1 Roll of M71-31-423 White Die Cut Labels, 1 R6000 Black Ribbon Cartridge, Roll Adapter, USB Cable, Quickstart Guide, a CD including the Printer Driver, Users Guide and Tutorial.

WATCH A DEMO VIDEO OR REQUEST A FREE SAMPLE PACK AT:
www.BradyID.com/bmp71
www.BradyCanada.ca/bmp71



Brady 360™ Replacement Printer Program

The Brady 360™ Printer Replacement Plan supplements the Limited Warranty already provided to you with the purchase of your Brady printer. With this plan, Brady Corporation, in its reasonable discretion, will send a replacement printer in the event that your covered printer requires service during the term of its Limited Warranty. Brady will replace your defective printer with a new printer that has the same or similar functionality and is of the same or greater value.

Limit two new replacement printers per covered printer in each warranty period. The plan must be purchased at the time of printer purchase to be valid.

** Limit of two printers in the first 12 months of initial purchase.

Terms of Brady Corporation's BMP®71 warranty can be found at:
www.BradyID.com/bmp71
www.BradyCanada.ca/bmp71

USA
1-888-272-3946
www.BradyID.com
Canada
1-800-263-6179
www.BradyCanada.ca
Mexico
1-800-262-7777
www.BradyLatinAmerica.com

