

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [98823-1010](#)
Status: **Active**
Overview: [NSCC - New Standard Casing Contact](#)
Description: NSCC Male Housing, Terminal Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits, White

Documents:
[3D Model](#) [Application Specification AS-98816-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Housings
Series [98823](#)
Application Power, Wire-to-Wire
Comments Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
Overview [NSCC - New Standard Casing Contact](#)
Product Name NSCC
UPC 822348817177

Physical
Circuits (maximum) 10
Circuits Detail 10x1.5mm pins
Color - Resin White
Gender Male
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 8.000/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.33mm, 6.00mm
Polarized to Mating Part Yes
Ports 1
Temperature Range - Operating -40°C to +100°C

Electrical
Current - Maximum per Contact 10A

Material Info
Old Part Number 08119EV10F9

Reference - Drawing Numbers
[Application Specification](#) AS-98816-001
[Sales Drawing](#) SD-98823-001



image - Reference only **Series**

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[98823Series](#)

Mates With
[98816-1010](#) , [98816-1110](#) (Female Receptacle Housing)

Use With
Use: Male FCI Terminals