


VH D 9500 CLG



Technical Reference

Specifications

Capacity	9500mAh
Chemistry	NiMH
Dimensions	58.2 x 32.15mm
Maximum Continuous Current	70A
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	-10°C
Nominal Voltage	1.2V
Operating Temperature Range	-10 → +40°C
Size	D
Terminal Type	Standard

VH Series Ni / MH rechargeable batteries with lugs

Ni/MH rechargeable batteries with lugs.

Higher capacity than Ni / Cd rechargeable batteries.

No memory effect.

Nominal voltage:	1.2 Vdc
Operating temperature under discharge:	-20 °C → +40 °C

Stock no.	Type	Format	Dim (mm) Ø x h	Capacity (mAh)
483-4403	VH AAA CLG	AAA	10.5 x 44.9	600
218-4554	VH 4 / 5 A CLG	4 / 5 A	16.9 x 43.2	1600
455-8749	VH AA 1700 CLG	AA	14.4 x 50.7	1700
419-9772	VH Cs 3000 CLG	Cs	22.2 x 42.2	3000
455-8777	VH D 9500 CLG	D	32.2 x 60.3	9500