

Distributed by:




www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Waterproof Tube Style Color Camera

ITEM NO: 15-CM25WN, 15-CM25WNB



Caution for Installation

1. Avoid places where there is direct sunlight.
2. Do not directly touch the CCD element. If necessary, use a soft cloth moistened with alcohol to wipe off the dust.
3. Avoid places where temperatures exceed 50°C or more.
4. Avoid places where there is frequent vibrations or shocks.
5. Please input power **regulator DC 12V**.
6. When any abnormalities occur, make sure to unplug the unit and contact your local dealer
7. Anti-corrosion, waterproof (IP65).

Packing

1 Camera	X1
2 Sunshade Cover	X1
2 User Manual	X1
3 Bracket Holder	X1
4 Screw	X3
5 Plastic-Conical-Anchor	X3

Specification

ITEMS	15-CM25WN	15-CM25WNB
TYPE	COLOR	
PICK UP DEVICE	1/4" CCD IMAGE SENSOR	
PICTURE ELEMENTS H * V	NTSC: 512 * 492 – PAL:512 * 582	
HORIZONTAL RESOLUTION	420 Lines	
VERTICAL FREQUENCY	NTSC:59.94Hz - PAL:50Hz	
SCANNING SYSTEM	2:1 INTERLACE	
MINI ILLUMINATION	0 Lux with IR LED 20 pieces	
SYNCHRONIZATION	Internal	
S/N RATIO	more than 48 dB	
ELECTRONIC SHUTTER	Up to 1/100,000 sec.	
WHITE BALANCE	Auto White Balance	
IR RAY (acceptable)	880 ~ 940 nM Infrerad Wave Length	
LENS	4.3mm F1.8	
GAMMA	0.45	
VIDEO OUTPUT	1 Vp-p,75 Ohms	
AUTO GAIN CONTROL	AUTO	
POWER SUPPLY	12VDC (+/-10%)	
POWER CONSUMPTION	160mA (+/-10%)	
COLOR	SILVER	BLACK
WEIGHT g	390	
STORAGE TEMPERATURE	-30 to + 60 Degree C	
OPERATING TEMPERATURE	-10 to + 50 Degree C	

Remark: The camera are only operated with regulative adaptor AC to DC 12V, AC non-regulative adaptor may cause camera damaged.