


AD6025 SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
 Impeller:Plastic(UL:94V-0)
 Bearing:Ball, Sleeve, 1B1S, Hypro bearing
 Lead wire:UL 1007AWG24
 VOLTAGE AVAILABLE:5V,12V,24V


Specifications(Nominal)

*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ⊗=Ball ⊘=Sleeve ○=1B1S ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	(CFM)	Maximum Pressure (InAq)	(mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x25	AD0605LB-A70GL	⊗ ⊘ ●	5	0.10	0.50	2500	0.374	13.20	0.063	1.60	18.1	58.0
	AD0605MB-A70GL	⊗ ⊘ ●	5	0.19	0.95	3500	0.510	18.00	0.118	3.00	28.0	
	AD0605HB-A70GL	⊗ ⊘ ●	5	0.35	1.75	4500	0.708	25.00	0.188	4.78	36.9	
	AD0612LB-A70GL	⊗ ⊘ ●	12	0.06	0.72	2500	0.374	13.20	0.063	1.60	18.1	
	AD0612MB-A70GL	⊗ ⊘ ●	12	0.10	1.20	3500	0.510	18.00	0.118	3.00	28.0	
	AD0612HB-A70GL	⊗ ⊘ ●	12	0.19	2.28	4600	0.701	24.78	0.200	4.78	35.2	
	AD0612UB-A70GL	⊗ ⊘ ●	12	0.25	3.00	5000	0.765	27.00	0.230	5.84	40.0	
	AD0612XB-A70GL	⊗	12	0.30	3.60	6100	0.889	31.40	0.320	8.13	42.9	
	AD0624MB-A70GL	⊗ ⊘ ●	24	0.06	1.44	3500	0.510	18.00	0.118	3.00	28.0	
	AD0624HB-A70GL	⊗ ⊘ ●	24	0.12	2.88	4500	0.708	25.00	0.188	4.78	36.9	
	AD0624UB-A70GL	⊗ ⊘ ●	24	0.14	3.36	5000	0.765	27.00	0.230	5.84	40.0	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	cUL	SP	ROHS	CE
✓	✓		✓	✓