

Wire Wrapping Bits - Data Sheet



BW-2224 - Wire Wrapping Bit, 22-24 AWG

3 in. Long Wire Wrapping Bit. These wire wrapping bits and sleeves conform to terminal height, width and wire size combinations. The wire wrapping sleeves are insulated to prevent shorting of adjacent connections. Wire Gauge 22-24. Hole Diameter 0.075 inches. Hole Depth 0.807 inches. Compatible Sleeve Part No. SW-2224.

BW-2600 - Wire Wrapping Bit, 26 AWG

3 in. Long Wire Wrapping Bit. These wire wrapping bits and sleeves conform to terminal height, width and wire size combinations. The wire wrapping sleeves are insulated to prevent shorting of adjacent connections. Wire Gauge 26. Hole Diameter 0.075 inches. Hole Depth 1 inch. Compatible Sleeve Part No. SW-2426.

SPECIFICATIONS

PART NO.	BW-2224	BW-2600
Wrap Function	Wrap	Wrap
Wrap Type	Regular	Regular
Wire Gauge	22-24 AWG (0.65-0.50 mm)	26 AWG (0.40 mm)
Min. Terminal Diagonal	0.054" (1.37 mm)	
Max. Terminal Diagonal	0.073" (1.85 mm)	
Terminal Hole Depth	0.807" (20.05 mm)	1" (25.4 mm)
Terminal Hole Dia.	0.075" (1.9 mm)	0.075" (1.9 mm)
Effective Radius	0.075" (1.9 mm)	
Wrap Post Size	0.045" (1.14 mm)	0.045" (1.14 mm)
Length	3" (76.2mm)	
Weight	0.057 lbs	0.057 lbs
UPC No	811490011632	811490015524