





REV.	DATE	DESCRIPTION
A	04/05/03	UPDATE DRAWING FORMAT
B	07/19/07	REVISE BARREL AND FERRULE DIMENSIONS



RECOMMENDED CABLE
STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.							07/19/07
7						CHECKED								
6						ISSUED			PART DESCRIPTION					
5	FERRULE	BRASS	NICKEL	1			SHEET	1 OF 1		BNC CRIMP PLUG (BELDEN 8218/VFM 809/1407B/1167B-75ohms)				
4	GASKET	RUBBER	RED	1					PART NO.					
3	INSULATOR	TEFLON	NATURAL	1					112955					
2	CONTACT PIN	BRASS	GOLD	1					DWG. NO.					
1	SHELL/BODY	BRASS	NICKEL	1					112955.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112955.DWG		REV.	B	SIZE	A	SCALE	NA