















716 6321

walthers

Amp	Volt	Hz	IP Ident. colour + h	Part No	Couplers	2 P +  IEC/EN 60 309	 g	EAN No. 4015609...																														
 IP44					mondo angled coupler, RAL 7035 light grey	  	10 138	016310 016303 016327																														
16	230 110 400	50/60 50/60 50/60	6 4 9	316 306 316 304 316 309	<table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>p</th></tr><tr><td>16 A</td><td>95</td><td>50,3</td><td>80</td><td>8/13</td></tr></table>				Ampère	d	e	f	p	16 A	95	50,3	80	8/13																				
Ampère	d	e	f	p																																		
16 A	95	50,3	80	8/13																																		
 IP44					angled coupler, with Schuko socket outlet on reverse side	  	10 152	016341																														
16	230	50/60	6	317 306	<table><tr><th>Ampère</th><th>a</th><th>d</th><th>e</th><th>f</th><th>Øp</th></tr><tr><td>16 A</td><td>54</td><td>87</td><td>49,5</td><td>140</td><td>7/13</td></tr></table>				Ampère	a	d	e	f	Øp	16 A	54	87	49,5	140	7/13																		
Ampère	a	d	e	f	Øp																																	
16 A	54	87	49,5	140	7/13																																	
 IP67					gland entry	  	10 172	016372 016365 016389																														
16	230 110 400	50/60 50/60 50/60	6 4 9	319 306 319 304 319 309																																		
32	230 110 400	50/60 50/60 50/60	6 4 9	339 306 339 304 339 309																																		
63	230 110 400	50/60 50/60 50/60	6 4 9	369 306 369 304 369 309																																		
125	230 110 400	50/60 50/60 50/60	6 4 9	379 306 379 304 379 309	<table><tr><th>Ampere</th><th>d</th><th>f</th><th>m</th><th>u</th><th>Pg</th></tr><tr><td>16 A</td><td>136</td><td>78</td><td>121</td><td>72</td><td>13,5</td></tr><tr><td>32 A</td><td>170</td><td>96</td><td>149</td><td>96</td><td>21</td></tr><tr><td>63 A</td><td>255</td><td>117</td><td>206</td><td>110</td><td>36</td></tr><tr><td>125 A</td><td>332</td><td>130</td><td>275</td><td>130</td><td>48</td></tr></table>				Ampere	d	f	m	u	Pg	16 A	136	78	121	72	13,5	32 A	170	96	149	96	21	63 A	255	117	206	110	36	125 A	332	130	275	130	48
Ampere	d	f	m	u	Pg																																	
16 A	136	78	121	72	13,5																																	
32 A	170	96	149	96	21																																	
63 A	255	117	206	110	36																																	
125 A	332	130	275	130	48																																	
with Multi Contact																																						

			IP		Wall socket outlets with switch		2 P + 		 9		EAN No. 4015609...
Amp	Volt	Hz	Ident. colour + h	Part No.			IEC/EN 60 309				
					with double interlocking, switch 2 poles						
IP44											
16	230	50/60	6	531 23 16					1		039562
	110	50/60	4	531 23 14					796		039555
	400	50/60	9	531 23 19							039579
32	230	50/60	6	531 23 36					1		039609
	110	50/60	4	531 23 34					1039		039593
	400	50/60	9	531 23 39							039616
					with double interlocking, switch 2 poles						
IP44											
63	230	50/60	6	531 23 66					1		039630
	110	50/60	4	531 23 64					2482		039623
	400	50/60	9	531 23 69							039647
					with double interlocking, switch 2 poles						
IP67											
16	230	50/60	6	531 33 16					1		039944
	110	50/60	4	531 33 14					845		133116
	400	50/60	9	531 33 19							166251
32	230	50/60	6	531 33 36					1		134267
	110	50/60	4	531 33 34					1066		166268
	400	50/60	9	531 33 39							166275
					with double interlocking, switch 2 poles						
IP67											
63	230	50/60	6	531 33 66					1		174034
	110	50/60	4	531 33 64					2533		039951
	400	50/60	9	531 33 69							166282