




CT-500CH / CT-520CH CT-550CH / CT-570CH

PA24442A01
Rev. 01 9-2007

CRIMPING HEAD PRODUCT INFORMATION CHARTS

© Panduit Corp. 2007



CT-500CH CRIMPING HEAD -- PRODUCT INFORMATION CHART

Crimp Pocket/ Color Code	Part No. Prefix	AWG Wire Range	Wire Strip Length +1/32, -0
22-18/ Red	JN	24-18	7/16
	BSN, PN-R, PN-F, PN-LF, PN-FF PNF-R, PNF-F, PNF-LF, PK-R	22-18	7/32
	BSV, PV-R, PV-F, PV-FF, PV-RX, PV-FX	22-18	5/16
	DNF, DNF-M, DV-M, DV-MB, PV-P	22-18	9/32
	BSN22, DV-P	22-18	1/4
16-14/ Blue	JN	18-16	7/16
	BSN, PN-R, PN-F, PN-LF, PN-FF PNF-R, PNF-F, PNF-LF, PK-R	16-14	7/32
	BSV, PV-R, -F, -FF, -RX, -FX	16-14	5/16
	DNF, DNF-M, DV-M, DV-MB, PV-P	16-14	9/32
	DV-P	16-14	1/4

CT-520CH CRIMPING HEAD -- PRODUCT INFORMATION CHART

Crimp Pocket/ Color Code	Part No. Prefix	AWG Wire Range	Wire Strip Length +1/32, -0
22-18/ Red	BSN	26-22	1/4
	PSN	22-18	5/16
	*DNF-FIB, *DNF-FIM, DNF-FIMB, DNF-LPB DPF-FIB, DPF-FIM, DPF-FIMB, DPF-LPB	22-18	9/32
	*DNF-FIB, DPF-FIB (.110/.111 Tab Size)	22-18	7/32
	DV-B	22-18	1/4
16-14/ Blue	PSN	20-16	5/16
	*DNF-FIB, *DNF-FIM, DNF-FIMB, DNF-LPB DPF-FIB, DPF-FIM, DPF-FIMB, DPF-LPB	16-14	9/32
	DV-B	16-14	1/4

* The Terminal Locator must be removed in order to install this Part Number.

Website: www.panduit.com
Email: cs@panduit.com



For Technical Support:
888-506-5400, ext. 3255
Fax: (630) 759-7532

CT-550CH CRIMPING HEAD – PRODUCT INFORMATION CHART			
Crimp Pocket/ Color Code	Part No. Prefix	AWG Wire Range	Wire Strip Length +1/32, -0
22-14/ Red/Blue	JN	24-18	7/16
	JN	18-16	7/16
	BSV, PV-R, PV-F, PV-FF, PV-RX, PV-FX, PV-SLF	22-18	5/16
	BSV, PV-R, PV-F, PV-FF, PV-RX, PV-FX, PV-SLF	16-14	5/16
	DNF-M, DV-M, DV-MB, PV-P	22-18	9/32
	DNF, DNF-M, DV-M, DV-MB, PV-P	16-14	9/32
	DNF-110, DNF-111, PN-R, PN-F, PN-LF, PN-FF, PNF-R, PNF-F, PNF-LF, PK-R, PN- SLF, PNF-SLF	22-18	7/32
	PN-R, PN-F, PN-LF, PN-FF, PNF-R, PNF-F, PNF-LF, PK-R, PN-RX, PN-SLF, PNF-SLF	16-14	7/32
	DV-P	22-18	1/4
	DV-P	16-14	1/4
12-10/ Yellow	JN	18-12	1/2
	PN-HDR, PN-HDRX	16-12	9/32
	PSN	14-12	7/16
	PN-RX	14-10	9/32
	PV-R, PV-F, PV-FF, PV-RX, PV-FX, PV-LF, PV-LFX	14-10	5/16
	BSN, D, DR DNF-M DV DV-M PN-R, PN-F, PN- LF, PN-FF, PNF-R, PNF-F, PNF-LF, PK-R, PN- RX, PN-SLF, PNF-SLF, PV-P	12-10	9/32
	BSV PV-LF, PV-LFX PV-SLF	12-10	5/16
	DNF-FI, DPF-FI	12-10	3/8

CT-570CH CRIMPING HEAD -- PRODUCT INFORMATION CHART			
Crimp Pocket/ Color Code	Part No. Prefix	AWG Wire Range	Wire Strip Length +1/32, -0
22-18/ Red	BS, D, DR, D-M, P-R, P-F, P-LF, P-SLF, P-FF, P-RHT6, P-P	22-18	9/32
16-14/ Blue	BS, D, DR, D-M, P-R, P-F, P-LF, P-SLF, P-FF, P-RHT6, P-P	16-14	9/32
12-10/ Yellow	P-HDR	16-12	9/32
	BS, D, DR, D-M, P-R, P-F, P-LF, P-SLF, P-FF, P-RHT6, P-P	12-10	9/32

NOTE: In the interest of higher quality and value, PANDUIT is constantly improving and updating our products. Consequently, pictures herein may vary from the actual product.