


1544322-4 Product Details

[Share](#) [Print](#) [Email](#)


1544322-4

TE Internal Number: 1544322-4

 **Active**

 [View 3D PDF](#)

FASTON Uninsulated Receptacles & Housings

 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.80 mm
- Board Mount = No
- Receptacle Style = Straight

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [CLIP DE 6.3 A ENFICHAGE DOUX](#) (PDF, English)

Catalog Pages/Data Sheets:

- [1654742 HOUSEHOLD APPLIANCES RASTS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version D2)
- [3D Model](#) (IGES, Version D2)
- [3D Model](#) (STEP, Version D2)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Terminal
- [Terminal Type](#) = Receptacle
- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 x 0.80 [.250 x .031]
- [Receptacle Style](#) = Straight
- [Insulation Support](#) = Insulation Support
- [Wire/Cable Type](#) = Stranded
- [Insulation Diameter \(mm \[in\]\)](#) = 3.80 [.149]
- [Insertion Force](#) = Low
- [Material](#) = Bronze
- [Finish](#) = Pre-Tin
- [Crimp Type](#) = F-Crimp

Mechanical Attachment:

- [Board Mount](#) = No

Body Features:

- [Weld Tab](#) = Without
- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.00² [20-17]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = IEC 760
- UL Rating = Listed
- CSA Certified = Yes

Packaging Features:

- [Packaging Method](#) = Strip
- Packaging Quantity = 6,000

Other:

- [For Hermetic Header Tab](#) = No
- Line = PRONER
- Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

