







OPERATING INSTRUCTIONS

© Panduit Corp. 2006



A 	 STD: .19" (4.8mm)	 HVY-STD: .25" (6.3mm)	 LHVV: .30" (7.6mm)	 HVV: .30 - .35" (7.6 - 9mm)
B 	STD 	HVV 	HVV 	HVV 
C 	0 - 4	4 - 6	5 - 6	5 - 8



CABLE TIE INSTALLATION TOOL

Part No.: GTH

FOR INSTALLING:

PAN-TY, DOME-TOP Barb Ty, STA-STRAP, DURA-TY, CONTOUR-TY, and IN-LINE Cable Ties of Standard, Heavy-Standard, Light-Heavy, and Heavy cross sections.

MADE IN USA

TOOL MAINTENANCE: GTH

This tool requires no special operator maintenance.

REPLACEMENT KITS: (SOLD SEPARATELY)

KGTHBLD: Blade Replacement Kit

KGTHTL: Tension Lockout Kit

KGTHSLV: Grip Sleeve Kit

REPLACEMENT PARTS: (SOLD SEPARATELY)

WH24287C01 – Blade Guard Housing

WH25092A01 – Extended Blade Guard



For Technical Support:

Panduit Corp., USA, Tinley Park, IL
888-506-5400, ext. 3255 • Fax: 630-759-7532

Panduit Europe, West World, Westgate, London
England Tel.: 0208 601 7200 • Fax.: 0208 601 7319

Website: www.panduit.com

Email: cs@panduit.com

EU Website: www.panduit.com/emea

Email: cs-emea@panduit.com