


[Back](#)

Selected Cable: 17519					Cord View
End View	Plug	Cord	Connector	End View	
NONE	3"STRIP	SJT	2"STRIP	C13	
Part Number	17519				Approvals
NSN	5935-01-150-3107				
Category	3 conductor plastic original equipment cords				
Shielding	unshielded				
Jacket Color	black				
Length Feet	9'10"				
Length Meters	3				
Temperature Rating	60 C°C				
Packaging Units Per Carton	H-100,H25				
Color Coding	International				
AWG Stranding	18 (41x34)				
Nominal OD Inch	0.315				
Nominal OD millimeter	8.00				
Rating	1250 Watts 10A-125V (*)				
Notes	See 17518 for 6'7" version. See 17521 for 16 gauge version. See 17619 for shielded version. 17519 is dual rated at 10A-250V.				

Qty: 1

[Add to Quote](#)
[Back](#)

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.