


RECOIL HOSE



- Durable Polyurethane Hose
- Excellent Recoil Memory
- Maximum Flexibility and Lightweight
- Transparent Hose Color (opaque available)
- Custom Colors Available
- High Chemical Resistance

SINGLE AIR HOSE ASSEMBLIES (COILED)

MODEL	WORKING PRESSURE 100PSI	DESCRIPTION (OD X ID X LENGTH)	RETRACTED LENGTH	NPT FITTINGS
ASH-250C-10MSZ		3/8" x 1/4" x 10'	7"	1/4"
ASH-250C-15MSZ		3/8" x 1/4" x 15'	9 1/2"	1/4"
ASH-250C-25MSZ		3/8" x 1/4" x 25'	15 1/2"	1/4"
ASH-375C-15MSZ		9/16" x 3/8" x 15'	10"	3/8"
ASH-375C-25MSZ		9/16" x 3/8" x 25'	14"	3/8"
ASH-500C-15MSZ		3/4" x 1/2" x 15'	13"	1/2"
ASH-500C-25MSZ		3/4" x 1/2" x 25'	23"	1/2"

SINGLE AIR HOSE (COILED)

Custom length coil assemblies and special colors are available in minimum order quantities.

STRAIGHT AIR HOSE (SOLD PER FOOT)

MODEL	DESCRIPTION
ASH-250Z	1/4" I.D.
ASH-375Z	3/8" I.D.
ASH-500Z	1/2" I.D.

- Assemblies include reusable swivel fitting
- Burst pressure 428 PSI @ 68° F
- Working temperature: -104° F to 175° F
- Straight hose is available by the foot with or without hose fittings
- Ask about full reel pricing

RECOIL HOSE

MODEL	CAPACITY
250-RZ	1/4" NPT Rigid Fitting
250-SZ	1/4" NPT Swivel Fitting
375-RZ	3/8" NPT Rigid Fitting
375-SZ	3/8" NPT Swivel Fitting
500-RZ	1/2" NPT Rigid Fitting
500-SZ	1/2" NPT Swivel Fitting

HELPFUL TIPS FOR PROPER USE:


- Use recommended ID air hose and fittings
- Replace air hose regularly to help maintain clean air
- Clear hose allows you to see water or dirt accumulation in hose
- Use correct length of hose to reduce air loss and pressure drop
- Use locking quick disconnect couplers for additional safety

ERGONOMIC TWIST PLUGS

These unique, ergonomically designed hose fittings provide 360° rotation and 35° angled rotation in any direction.



MODEL	DESCRIPTION
TS-20NP-3NPT	1/4" NPT Female x 3/8" NPT Male
TS-30NP-2NPT	3/8" NPT Female x 1/4" NPT Male
TS-20NP-2NPT	1/4" NPT Female x 1/4" NPT Male
TS-20US-2NPT	1/4" US Plug x 1/4" NPT Male
TS-20US-3NPT	1/4" US Plug x 3/8" NPT Male
TS-30US-2NPT	3/8" US Plug x 1/4" NPT Male
TS-30US-3NPT	3/8" US Plug x 3/8" NPT Male



- Two rotation points prevent kinking of air hose
- Design ensures full flow of air pressure
- Rotating joint is supplied with polyurethane dust cover
- Heavy-duty construction for maximum life

QUICK COUPLERS

Manual ball couplers designed for use with ergonomic twist plugs. Brass with nitrile seals, rated to 300 PSI, from -40° to +250° F.



MODEL	DESCRIPTION
B23	1/4" NPT F x 1/4" QC Brass Coupler
B23E	1/4" NPT F x 3/8" QC Brass Coupler
B25	3/8" NPT F x 3/8" QC Brass Coupler