MALLORY Mallory Sonalert Products Inc.	Part # PK-16N04WA-01Q
Sales Outline Drawing	Revision A

Specifications:

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	1.0 ~ 2.0
Rated Voltage (Vdc)	1.5
Current Consumption Max. (mA)	25 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Black)
Leading Wire	26 AWG
Weight (Grams)	8.0
Options	For other options contact factory

RoHS Compliant

Dimensions: (units: mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mallory Sonalert:
PK-16N04WA-01Q