


Dimensions: mm (in.)



Electrical Specifications:

- Rating: 16A / 125VAC 1 / 8HP
10A / 250VAC 1 / 3HP
- Contact Resistance: $50m\Omega$ max.
- Insulation Resistance: 500 VDC 100M Ω min.
- Dielectric Strength: 1500 VAC 1 minute

Materials:

- Frame: Nylon #66, Black
- Neon: $\phi 4$, NE-2G
- Resistor: 1/4S, 33k Ω

Mechanical Specifications:

- Operating temperature: $-25^\circ \sim 85^\circ$
- Circuit: 3P SPST On-Off
- Neon Lamps: 110VAC

Note:

- RoHS Compliant

Illuminated Rocker Switch

103-7048-EV

**Mountain
Switch**

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7048-EV](#)