





LOC	DIST	REVISONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FT	0	E		REVISED PER ECO-07-018769	8/14/07	SS SH




PART NO & DATE CODE MARKED IN AREA INDICATED, ON EITHER SIDE



VIEW B-B
SCALE 10:1
TYPICAL



REAR MOUNTED PANEL CUTOUT
SCALE 1:1



FRONT MOUNTED PANEL CUTOUT
SCALE 1:1

- ① CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
- ② NYLON, UL 94V-0 RATED, BLACK.
- ③ CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN-LEAD OVER 2.54um [.000100] MIN COPPER.
- ④ 5.08um [.000200] MIN NICKEL OVER 10.16um [.000400] MIN COPPER.
- ⑤ CONTACT BODY: 0.76um [.000030] MIN GOLD FOR A LENGTH OF 2.54 [.100] MIN FROM MATING END, GOLD FLASH ON REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL. CONTACT POST: 2.54um [.000100] MIN TIN OVER 2.54um [.000100] MIN COPPER.
- ⑥ SELECT LOAD CONTACTS 35 & 36 REMOVED.

	—	YES	①	41.40 [1.630]	213597-5
	②	NO	②	16.38 [.645]	213597-4
	—	NO	③	16.38 [.645]	213597-3
	—	NO	④	16.38 [.645]	213597-2
OBSOLETE	—	NO	⑤	14.15 [.557]	213597-1
	NOTES	ORGANIZER	CONTACT FINISH	Z	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. SIPE 4-23-90	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK R. STONE 4-25-90	NAME		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC		
		0 PLC ± —	108-10040		
		1 PLC ± —	APPLICATION SPEC		
		2 PLC ± 0.13 [.005]	SIZE		
		3 PLC ± —	CAGE CODE		
		4 PLC ± —	DRAWING NO		
		ANGLES ± —	RESTRICTED TO		
MATERIAL: RECEPTACLE: ① SHELL: ZINC CONTACT: BRASS		FINISH: SHELL: ②	A1 00779 ③=213597		
		WEIGHT —	CUSTOMER DRAWING		
		SCALE 2:1	SHEET 1 OF 1 REV E		