


REVISIONS					
					RER
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED & REDRAWN PER 0720-0037-93	5/20/93	DKS	RER
	D1	REVISED PER ECO-17-004099	29AUG2017	RS	DR



 WIRE RANGE	 E13288 Listed
3/0 AWG SOLID OR STRANDED	3/0 AWG SOLID OR STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
3/0 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 3/OW* APPROX AS SHOWN.
- 2 STAMP 150 APPROX AS SHOWN.
- 3 TONGUE MATERIAL THK: 2.31 ± 0.08 [.091 $\pm$.003]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		CIRCULAR MIL AREA: 76.3-96.3mm ² [150,000-190,000] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 5/27/93 CHK RD HEIM 1/27/94		 TE Connectivity		
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, RING TONGUE, SOLISTRAND™, 3/0 AWG			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD RE ROSER 1/27/94 PRODUCT SPEC — APPLICATION SPEC —		SIZE A2	
MATERIAL COPPER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727		WEIGHT —		CAGE CODE 00779	
				DRAWING NO C-36929		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 2:1	
						SHEET 1 of 1	
						REV D1	