



0.6mm Free Height Standard Bridge Plugs, 0.6 [.024] Pitch

4H (4mm), 6H (6mm) and
8H (8mm) Double Row
Stacking Heights

280 Positions

Material and Finish:

Housing — High temperature thermoplastic, 94V-0 rated

Contacts — Copper alloy; duplex plated 0.00020 [.000008] min. gold on contact area, 0.00100 [.000039] min. tin-lead on solder area, with entire contact underplated 0.00130 [.000051] min. nickel

Related Product Data:

Performance Characteristics — page 12








Stacking Height Combinations — page 13

Mating Receptacles — pages 15 & 19

PC Board Layout — page 25

Technical Documents (Page 70):

AMP Product Specification
108-5468



Section A - A

Stacking Height	Dimensions		Part Numbers (Tape Packaged)
	A	B	
4H	5.45 .215	3.45 .136	1-353284-0
6H	7.45 .293	5.45 .215	1-353134-0
8H	9.45 .372	7.45 .293	1-353135-0