

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0191930226

Status:

Active

Description:

VersaKrimp™ Ring Tongue Terminal for 6 AWG Wire



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19193
Comments	Type I Noninsulated; Class 2
Mil-Spec	AS20659-143, MS20659-143
Product Name	VersaKrimp™
Type	Ring
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min: Mating (µin)	100
Plating min: Mating (µm)	2.5
Plating min: Termination (µin)	100
Plating min: Termination (µm)	2.5
Stud Size	1/2" (M12)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	6
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	E-358-12
Reference - Drawing Numbers	
Sales Drawing	SD-19193-005

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19193Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Putt Pump Dieless Head System	0192860065
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640074300
Die Set (large) for the HHLS Hydraulic Crimper	0192900004
Hand Crimp Tool	0640013900
Manual Putt Pump Hydraulic System, Die set required	0192860117

Manual tool for 0192940008
Crimping non-
insulated 8AWG thru
4/0 Terminals

This document was generated on 02/03/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION