






	78.74 [3.100]	31	86.36 [3.400]	88.90 [3.500]	64	1-1761683-7
	73.66 [2.900]	29	81.28 [3.200]	83.82 [3.300]	60	1-1761683-6
OBSOLETE	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	1-1761683-5
	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	1-1761683-3
	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	1-1761683-1
	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	1761683-9
	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	1761683-7
	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	1761683-3
	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG B.CRISAMORE/DTI		05/JUN/05		 TE Connectivity	
		CPR S.BOLASH		05/JUN/05			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPRO M.WALMSLEY		NAME	
mm				PRODUCT SPEC		HEADER ASSEMBLY, HIGH TEMP, VERTICAL, LOW PROFILE, IDC	