



1. Select Connector Type and Stud Hole Size Desired			2. Determine Conductor Size and then Select <i>PANDUIT</i> Part Number																
	Mechanical Connector Type	Stud Hole Size In.	Copper Code Conductor Size																
			#14 AWG	#12 AWG	#10 AWG	#8 AWG	#6 AWG	#4 AWG	#2 AWG	#1 AWG	1/0 AWG	2/0 AWG	3/0 AWG	4/0 AWG	250 kcmil	300 kcmil	350 kcmil	500 kcmil	600 kcmil
			PANDUIT Part Number																
	One-Hole, Straight Tongue HL	1/4	HL1-25-X■*																
						HL4-1-X■*													
									HL8-1-X*										
		3/8								HL13-1-5									
	One-Hole, Straight Tongue HLB	1/4				HLB4-1-X■*													
		3/8																	
	One-Hole, Straight Tongue HLA-90	1/4				HLA4-1-90-X■*													
									HLA8-1-90-X*										
										HLA13-1-90-5									
		3/8									HLA21-1-90-5								
	Two-Hole, Straight Tongue HL-2	1/4	HL1-2-25-X■*																
						HL4-2-X■*													
									HL8-2-X*										
		5/16								HL13-2-5									
	Two-Hole, Straight Tongue HL-2N	1/4																	
		3/8																	
	Two-Hole, Straight Tongue H2L-2N	1/4																	
		3/8																	
	Two-Way, Connector HC	1/4																	
		3/8																	
	Two-Hole, Straight Tongue HHL-2N	1/4																	
		3/8																	
	One-Hole, Straight Tongue PNL	#10	PNL-8-C■*																
		1/4	PNL-4-C■*																
		5/16																	
		3/8																	
	One-Hole, Straight Tongue ML	1/4																	
		5/16																	
		3/8																	
	Two-Hole, Straight Tongue PNL-2	5/16																	
		3/8																	
		1/2																	
	Two-Way, Connector PNLC	1/4																	
		5/16																	
		3/8																	

†Type PNL is also CSA Certified, Type PNLC is not UL Listed or CSA Certified.

◆ NEMA hole sizes and spacing.

■ Uses slotted set screw.

*Denotes minimum conductor size is solid conductor.

PAN-LUG™ Copper Mechanical Connectors

Easy Selection Guide

1. Select Connector Type and Stud Hole Size Desired				2. Determine Conductor Size and then Select <i>PANDUIT</i> Part Number																			
 	Mechanical Connector Type	Current Rating AMPS	Stud Hole Size In.	Copper Code Conductor Size																			
				#14 AWG	#12 AWG	#10 AWG	#8 AWG	#6 AWG	#4 AWG	#2 AWG	#1 AWG	1/0 AWG	2/0 AWG	3/0 AWG	4/0 AWG	250 kcmil	350 kcmil	400 kcmil	500 kcmil	600 kcmil	750 kcmil	800 kcmil	1000 kcmil
				<i>PANDUIT</i> Part Number																			
	One-Hole, Offset Tongue CB	25	1/8	CB25-18CY■																			
		50	3/16	CB35-36-CY•■																			
		70	1/4	CBA70-14-CY■																			
		90		CB70-14-CY•■																			
		125								CB125-14-QY■													
		175	3/8							CB175-38-QY													
		225	5/16							CB225-56-QY													
		300	3/8									CB300-38-QY											
		400											CB400-38-3Y										
		650	1/2																			CB650-12-3Y	
	Two Barrel, One-Hole, Offset Tongue DC	450	3/8								DC450-38-3Y												
		600										DC600-38-3Y											
		800	1/2										DC800-12-3Y										
	Two-Hole, Offset Tongue CO	50	3/16	CO35-36-QY•■(1)																			
		90	1/4	CO70-14-QY•■(1)																			
		125									CO125-14-QY■(1)												
		225	5/16							CO225-56-QY(1)													
		300	3/8									CO300-38-3Y(3)											
		400											CO400-38-3Y(2)										
		650	1/2																			CO650-12-3Y◆(2)	
	One-Hole, Straight "Fixed" Tongue CX	35	3/16	CX35-36-CY■																			
		70	1/4	CX70-14-CY•■																			
		125									CX125-14-QY■												
		225	5/16								CX225-56-QY												
		400	3/8												CX400-38-3Y								
	One-Hole, Straight Tongue CS	25	1/8	CS25-18-CY■																			
		50	3/16	CS35-36-CY•■																			
		70	1/4	CSA70-14-CY■																			
		90		CS70-14-CY•■																			
		125									CS125-14-QY■												
		175	3/8								CS175-38-QY												
		225	5/16								CS225-56-QY												
		300	3/8									CS300-38-QY											
		400											CS400-38-3Y										
		650	1/2																			CS650-12-3Y	
	Two-Hole, Straight Tongue CD	50	3/16	CD35-36-QY•■(1)																			
		90	1/4	CD70-14-QY■(1)																			
		125									CD125-14-QY■(1)												
		225	5/16								CD225-56-QY(1)												
		300	3/8									CD300-38-3Y(1)											
		400											CD400-38-3Y(2)										
		650	1/2																			CD650-12-3Y◆(2)	

- Multiple conductor combinations.
- ◆NEMA hole sizes and spacing.
- Uses slotted set screw.
- (1) 1.00" stud hole spacing.
- (2) 1.75" stud hole spacing.
- (3) 1.87" stud hole spacing.



For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference PCSG08

For a copy of *PANDUIT* product warranties, log on to
www.panduit.com/warranty

©2006 *PANDUIT* Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.
SA-PCSG08
Replaces SA-PCSG03
8/2006