


SPECIAL ESD ELECTRONIC PLIERS

Lap joint 
Double leaf spring
Bright polished - **chrome**-plated
With **conductive** black handguard

CUTTING PLIERS

No.	Length		Finish	Cutting capacity mm Ø		Weight g
	mm	inches		Soft wire	Hard wire	

Side cutters

with slim, rounded head

3-901-13	125	5	with side face	1.0	0.4	75
----------	-----	---	----------------	-----	-----	----

Side cutters

with slim, pointed head and special flat cutting edge, for soft wire only

3-902-13	125	5	without side face	0.8	-	75
----------	-----	---	-------------------	-----	---	----

Top cutters

with 3 mm wide cutting edge, jaw length 20 mm, for flush cutting, for soft wire only

3-905-13	135	5 1/2	without side face	0.8	-	85
----------	-----	-------	-------------------	-----	---	----

End cutters

with angular tips and oblique cutting edge, for flush cutting, for soft wire only

3-906-13	135	5 1/2	without side face	0.8		85
----------	-----	-------	-------------------	-----	--	----

ROUND, FLAT AND SNIPE NOSE PLIERS

Round nose pliers

3-931-13	130	5 1/8	plain jaws			80
----------	-----	-------	------------	--	--	----

Flat nose pliers

3-932-13	130	5 1/8	plain jaws			70
----------	-----	-------	------------	--	--	----

Snipe nose pliers

3-933-13	130	5 1/8	plain jaws			70
----------	-----	-------	------------	--	--	----

SIDE CUTTERS, TELEPHONE AND COMBINATION PLIERS

Lap joint, bright polished – chrome-plated
With **conductive** black handguard

Side cutters

swedish design

3-133-13	145	5 3/4	spezial-steel	2.5	1.25	155
----------	-----	-------	---------------	-----	------	-----

Telephone pliers snipe nose, long straight jaws, with cutting edges for hard wire

3-245-13	200	8	serrated jaws			180
----------	-----	---	---------------	--	--	-----

Combination pliers

with wire cutter, for hard wire

3-732-13	165	6 1/2	serrated jaws			185
----------	-----	-------	---------------	--	--	-----



3-901-13



3-902-13



3-905-13



3-906-13



3-931-13



3-932-13



3-933-13



3-133-13



3-245-13



3-732-13