



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- DWG-Mini-Com Min ..
- PDFMini-Com Min ..
- DXF-Mini-Com Min ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDFMini-Com Min ..

Home > [Products Overview](#) > Search Results >

onlinecomponents.com

THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

Current refinements (click to remove) Search Tips

Text Search: 'CJ88IWY'

Your search criteria matched only one product, shown below

CJ88IWY



- Patented lead frame termination style ensures twists are maintained to within 1/2"
- No punchdown tool required, optional termination tool (CJT -X) ensures conductors are fully terminated
- Termination cap provides excellent strain relief; helps control cable bend radius and securely retains wires
- Clear, removable termination cap provides easy troubleshooting
- Terminate 4 -pair 24 and 22 AWG 100 ohm solid unshielded twisted pair cable
- Accept 6 and 8-position modular plugs without damage
- White colored module base designates Category 3 performance
- Can be clearly identified with optional labels and icons
- Compatible with *Mini-Com*® Modular Patch Panels, Faceplates, and Surface Mount Boxes

Part Number	CJ88IWY
RoHS Compliancy Status	Compliant
Note	CJ88IWY replaces CJ88IW
Part Description	Category 3, 8-position, 8-wire universal module.
Product Type	Copper Jack Module
Color	Off White
CE Compliant	No
CE Marking	No
Modular Jack Type	RJ45
No. of Module Spaces	1
Performance Level	Category 3
Pricing Description	Mini-Com MiniJack Module, Cat 3, UTP, 8 pos 8 wire, Universal, Off White
Wiring Scheme	T568A/T568B
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.