




**Product Number:** AN-1322

**AN Series**

NEMA 1, 2, 4, 4X, 12, 13 Boxes (Diecast Aluminum)



***Design Features***

- Designed to IP66 of IEC529 and NEMA 1, 2, 4, 4x, 12, and 13 specifications.
- Wall mounting holes (on Style A) and cover attaching screws are outside the sealing area thus preventing ingress of moisture and dust (Style B does not have wall mounting holes).
- Cover incorporates a recessed gasket.
- Internal bosses for mounting PCBs horizontally or for connecting terminals, ground, etc.
- Most models have internal guide slots for mounting PCB assemblies vertically.
- Cover mounting holes are roll threaded and screws are recessed.
- UL Listed to UL508-4 requirements (file# E194432)

***Bonus Features***

- Body & Cover: Aluminum Alloy #ADC-12
- Gasket: Silicon
- Cover Screws: M4 Stainless Steel, non-magnetic
- PCB Mounting Hardware: Requires kit #57-58, ordered separately

***Finishes***

- Natural Finish or Gray (add suffix -G)

***External Dimensions (Inches):***

|   |    |      |
|---|----|------|
| ○ | A: | 7.87 |
| ○ | B: | 4.72 |
| ○ | C: | 2.95 |
| ○ | D: | 2.17 |
| ○ | E: | 7.56 |
| ○ | F: | 4.43 |
| ○ | G: | 2.81 |
| ○ | H: | 2.10 |

***Internal Grounding PCB Holes:***

|                   |    |
|-------------------|----|
| <b>0.125 Dia.</b> | 12 |
| <b>0.136 Dia.</b> | 0  |

***Wall Thickness:***

0.07 inches

***Weight:***

27.2 Ozs