



Model # BU-65-*

- Compatible with all shrouded, unshrouded, or retractable 0.16" (4mm) banana plugs
- Jaw opens 0.75" (19 mm) max
- Material: nickel-plated steel clip, glass-filled nylon housing
- Length: 3.23" (82.04mm)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000 V, 30 Amps, IEC 1010 Compliant

Alligator Clip

Alligator Clip

Model # BU-70/BU-70C

- Solder or crimp connection
- Jaw opens 0.313" (7.9 mm) max
- Material: nickel-plated steel (BU-70) or solid copper (BU-70C)
- Length: 1.69" (42.86mm)