




DESCRIPTION: PLASTIC FLAT RIBBON CONNECTOR



	A	B	C
9	1.213 30.81	.984 25.00	.707 17.96
15	1.541 39.14	1.312 33.33	.707 17.96
25	2.088 53.04	1.852 47.04	.707 17.96
37	2.729 69.32	2.500 63.50	.707 17.96

186-XXX-292-XX1

SERIES _____
POSITIONS _____
009
015
025
037
050
GENDER _____
1 = MALE
2 = FEMALE
TERMINATION _____
9 = IDC
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
55 = 4-40 INSERTS
PLATING OPTIONS _____
01 = GOLD FLASH

SPECIFICATIONS:

MATERIALS:

INSULATOR: UL 94V-0 RATED PBT
+30% FIBER-GLASS OR NYLON-66

ELECTRICALS:

CURRENT RATING: 1 AMP
CONTACT RESISTANCE: 15 mOHMS MAX
INSULTOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

CHECKED:

DATE:
9-28-98

DATE:

SCALE:
1:1

SHEET
1 OF
1

REV
1

DWG NO.
186-XXX-292-XX1

NorComp