

NetRunner™ Vertical Cable Management

- Large finger openings accommodate up to 24 Category 6 cables
- Integral cable retainers on the end of each finger to help contain cables within each rack unit
- Bend radius fingers align with rack spaces to support cables as they transition to the vertical pathway
- Dual hinged covers can be opened 110° to the left or right to provide complete access to the cables inside the vertical pathway

- Snap-on cable retainers can be placed on to fingers to help retain cables in channel during installation and maintenance
- Vertical managers include hinged covers, cable retainers, mounting brackets and #12-24 screws



WMPV22E

WMPVF22E

Part Number	Part Description	No. of Rack Spaces^	Std. Pkg. Qty.	Std. Ctn. Qty.
Vertical Cable Managers – Front and Rear				
WMPV22E	Front and rear vertical manager. Dimensions: 41.5"H x 4.9"W x 12.0"D (1054mm x 125mm x 306mm)	22	1	—
WMPVHC45E	Front and rear vertical manager. Dimensions: 83.0"H x 6.7"W x 14.1"D (2108mm x 170mm x 357mm)	45	1	—
WMPV45E	Front and rear vertical manager. Dimensions: 83.0"H x 4.9"W x 12.0"D (2108mm x 125mm x 306mm)	45	1	—
Vertical Cable Managers – Front Only				
WMPVF22E	Front only vertical manager. Dimensions: 41.5"H x 4.9"W x 6.5"D (1054mm x 125mm x 165mm)	22	1	—
WMPVHCF45E	Front only vertical manager. Dimensions: 83.0"H x 6.7"W x 7.6"D (2108mm x 170mm x 192mm)	45	1	—
WMPVF45E	Front only vertical manager. Dimensions: 83.0"H x 4.9"W x 6.5"D (2108mm x 125mm x 165mm)	45	1	—
Accessories				
WMPVCBE	NetRunner™ Center Mount Bracket Kit allows mounting to adjacent racks. Four brackets per kit.	—	1	10
WMPVSMK	NetRunner™ Side Mount Hardware Kit for use with Panduit CMR19X84S racks and Panduit R4P 4 post rack series.	—	1	10
WMPVCMB	Rack adapter bracket kit. Front or back mounted on racks with dimensions up to 1 5/8" (41.1mm) from outside edge of rack to center of the mounting hole. Two kits are required for center mounting of NetRunner™ Managers. Four brackets per kit.	—	1	10
NREP	End panel for use with NRV series, WMPVHCF45E/WMPVHC45E. Includes two panel sections to cover 45 RU on one side.	—	1	—
WMPV45EP	End panel for use with WMPV45E. Includes two panel sections to cover 45 RU on one side.	—	1	—
WMPV45ERTW	Rack top trough with waterfall creates pathway above rack, for use with CMR19X84 and WMPV45E/WMPVHC45E and NRV series.	—	1	—
WR5E-X	Snap-on finger cable retainers.	—	10	100

[^]One rack space = 1.75" (44.45mm).

All product color is black.

Part Number	Cable Capacity Chart							
	Cat6A-SD (.240")		Cat 6A (.300")		Cat6 (.240")		Cat5e (.225")	
	Front	Rear	Front	Rear	Front	Rear	Front	Rear
WMPV22E	143	143	91	143	143	143	162	162
WMPVF22E	143	—	91	—	143	—	162	—
WMPV45E	143	143	91	143	143	143	162	162
WMPVF45E	143	—	91	—	143	—	162	—
WMPVHC45E	266	266	170	266	266	266	303	303
WMPVHCF45E	266	—	170	—	266	—	303	—

Note: Capacities are based upon a fill rate of 35% to accommodate proper cable routing techniques.

For comparison, multiply by 1.5 for a fill rate of 50%.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[WMPV22E](#) [WMPV45E](#)