

- +

About AUO
- +

Citizenship
- +

Product Applications

Product Introduction
- +

TFT-LCD

- LCD TV

- PID

- Monitor

- Notebook PC

- General Display

- Mobile Device

- DSC

- Printer

- Car

- PND

- DPF
- +

E-Paper

Solar
- +

Technology
- +

Investor Relations
- +

Career
- +

Support



General Display	
Model	G070VW01 V0
Size	7"
Resolution (pixel)	WVGA (800 x 480)
Active Area	152.4 x 91.4
Pixel Pitch (mm)	0.1905
Mode	TN
Number of Colors	262K / 16.2M
Color Saturation (%)	60
Viewing Angle (H/V)	160 / 160
Brightness (cd/m ²)	400
Contrast Ratio	1000 : 1
Response Time (ms)	30
Power Consumption (W)	3.7
Interface	LVDS
Supply Voltage (v)	3.3
Light Source	LED
Outline Dimension (mm)	170 x 111 x 7.5
Weight (g)	165
Production	Now
Remark	Reverse Scan Replaceable LED 6/8 bit Convertible Wide Temperature

Related Links

- Technology
- Awards

Reference

- Contact AUO