

**Models 7140, 7142, 7148, 7150, 7151, 7152, 7153
Cable Mounted ¼" Phone Plugs and Jack***Model 7140 ¼" Phone Plug 2 Conductor (Mono)**Model 7142 ¼" Phone Plug 3 Conductor (Stereo)**Model 7148 ¼" Phone Jack-Locking (Stereo or Mono)**Model 7151 ¼" Phone Plug 2 Conductor (Mono)-Right Angle**Model 7150 ¼" Phone Plug 2 Conductor (Mono)-Long Handle**Model 7152 ¼" Phone Plug 3 Conductor (Stereo)**Model 7153 ¼" Phone Plug 2 Conductor (Mono)-Large Diameter Cable*

Use for optimal audio signal transfer and secure connection.

Features

- Available in mono and stereo versions
- Two and three conductor versions
- Quick to assemble
- Rugged all metal housing

Materials

- Body for models, 7140, 7142, 7148, 7151 is diecast zinc alloy with tarnish resistant nickel-plating
- Sturdy strain relief clamp (7140, 7142, 7148): POM.
- Plugs are nickel-plated brass

Ordering Information

Model: 7140, 7142, 7148, 7150, 7151, 7152, 7153.

Specifications

MODEL	WIRE SIZE (AWG)	O.D.	POLES
7140	18 AWG / 1 mm ²	4-7 mm	2 (Mono)
7142	18 AWG / 1 mm ²	4-7 mm	3 (Stereo)
7148	18 AWG / 1 mm ²	4-7 mm	2 or 3 (Mono or Stereo)
7150	18 AWG / 1 mm ²	12 mm	2 (Mono)
7151	18 AWG / 1 mm ²	4-7 mm	2 (Mono)
7152	16 AWG / 1.5 mm ²	12 mm	3 (Stereo)
7153	16 AWG / 1.5 mm ²	17.5 mm	2 (Mono)

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

7152 7151 7150