





(2,54 mm) .100"

IPD1-10-D-K-M



IPD1-15-S_K



CC79L-2630-01-L

IPD1, CC79 SERIES

DISCRETE WIRE CABLE COMPONENTS


SPECIFICATIONS

For complete specifications see www.samtec.com?IPD1 or www.samtec.com?CC79

TOOLING

- Hand tool (20-30 AWG): CAT-HT-179-2030-13
- Mini Applicator (20-24 AWG): CAT-MA-179-2024-XX-01
- Mini Applicator (26-30 AWG): CAT-MA-179-2630-XX-01


TYPE	POSITIONS PER ROW	ROW OPTION	K	LATCH OPTION
IPD1 = Body, Loose	-02, -03, -04, -05, -06, -08, -10, -12, -15, -16, -20, -25 (Standard sizes)	-S = Single Row -D = Double Row	-K = Keyed Polarization -M = Metal Latch (Metal for more rugged environments) (-02, -05 & -10 positions only) (Leave blank for plastic latch)	



Insulator Material:
Nylon 66


TYPE	WIRE GAUGE	01	PLATING OPTION
CC79L = Contact, Loose	-2630 = 26 to 30 AWG -2024 = 20 to 24 AWG		-L = 10µ" (0,25 µm) Gold on contact, Tin on tail

CC79R
= Contact, Full Reel (12,000 Parts per Reel)



Contact Material:
Phosphor Bronze

MINI MATE® TERMINAL SOLUTIONS



THINK OUTSIDE THE CATALOG

- Easy discrete wire ("crimp & poke") solutions
- Build a standard or flexible custom online
- Calculate performance, current rating, voltage drop
- Live chat with engineers for custom options
- Assembly and field kits available



- .100" (2,54 mm) pitch
- 20 to 30 AWG wire in PVC or *Teflon® cable
- Polarized, guide pins or latching options
- Single or double row
- For detailed information on Mini Mate® cable components and assemblies see:
Single row: MMTS, MMTST
Double row: MMTD, MMTDT
Components: IPM1, T1M74