


Part Number: 5642210010F

General Description	
Series	564
Configuration	3 mm Lens
Description	3 mm Blank/Red/Blank Backlighting Tri - Level CBI Non - Diffused
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Tri - Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Non - Diffused
Viewing Angle	45
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1,3	LED Position: 2
Color	Blank	Red
LED Type		High Efficiency
Peak Wave Length		635
Luminous Intensity Min		8.7
Luminous Intensity Typical		29
Forward Voltage Typical		2
Forward Voltage Max		2.8
Power Dissipation Max		100mW



5642210010F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)