






- ① HOUSING: NYLON, UL 94V-0 RATED, BLACK.
- ② CONTACTS & RECEPTACLE SHIELD: 2.54 μ m [.000100] MIN TIN OVER 1.27 μ m [.000050] MIN NICKEL.
- ③ ACCEPTS #2 SELF-TAPPING SCREW,.250 LONG REF.
- ④ CONTACTS & RECEPTACLE SHIELD: BRASS.



5212032-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 11-11-04 CHK C. ROHDE 11-11-04 APVD M. WALMSLEY 11-11-04	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-10047 APPLICATION SPEC 114-40025	NAME HEADER, DIN INTERFACE, 90 DEGREE, 4 POSITION, WITH GROUNDING AND MOUNTING HOLES	
MATERIAL ① ④	FINISH ②	WEIGHT -	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1
			REV 01	RESTRICTED TO -