




MATERIALS AND FINISHES

BODY, CRIMP TUBE, PRESS RING BRASS
PLATED NICKEL






CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

INSULATOR TEFLON

CRIMP DIE 3.25 (.128) HEX



RECOMMENDED
MOUNTING HOLE



RECOMMENDED
STRIP DIMENSIONS

73171-2632	73171-2631, ONE PER BAG
73171-2631	WITH JAM NUT & LOCKWASHER/BULK
73171-2630	NO JAM NUT & LOCKWASHER/BULK
PART NO.	DESCRIPTION/PACKAGING

CHG: UPDATED BODY
AND STRIP DIMENSION
EC NO: URF2013-0319
2012/12/11
DRWN:SSHAH
CHKD:ROBERTSON
APPR:JWIENER
2012/12/12
2012/12/13

REV
A2

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0004
3 PLACES	± .005	± .0004
2 PLACES	± .005	± .0004
1 PLACE	± .005	± .0004

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
JM	2005/05/04
CHECKED BY	DATE
JM	2005/05/04
APPROVED BY	DATE
JDW	2005/05/04

MATERIAL NO.
SEE TABLE

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
MINI BNC JACK, BULKHEAD
RG179, 75 OHMS
EWR-2785, MINI BNC-JC

MOLEX INCORPORATED

DOCUMENT NO.
SD-73171-263

SHEET NO.
1 OF 1