

## MINIATURE LAMP (656) Details



| Part #              | 656                         |                       |       |                        |                 |
|---------------------|-----------------------------|-----------------------|-------|------------------------|-----------------|
| Description         | T3 1/4 WEDGE 28V .06A .62CP |                       |       |                        |                 |
| Bulb Shape          | T-3 1/4                     | Filament              | C-2F  | Base Style             | Wedge (T-3 1/4) |
| Glass Diameter (in) | 0.39                        | MOL <sup>†</sup> (in) | 1.06  | LCL <sup>††</sup> (in) | 0.56            |
| Glass Diameter (mm) | 10                          | MOL (mm)              | 26.80 | LCL (mm)               | 14.20           |
| Volts               | 28                          | MSCP <sup>‡</sup>     | 0.62  | Avg Life Hrs           | 2500            |
| Watts               | 1.68                        | Amps                  | 0.06  | RoHS Compliant         | Yes             |

### <sup>†</sup> MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

### <sup>‡</sup> MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

### <sup>††</sup> LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.