

VANSONIC ENTERPRISE CO., LTD.

8F.,No.7,Lane 16, Sec.2, Szechwan Road, Panchiao, Taipei Hsien, TAIWAN.

TEL: +886-2-29626335


FAX: +886-2-29625220

E-MAIL: VANSONIC@MS4.HINET.NET

1.	MODEL:	30KM08					
2.	Dimension	Outer Diameter 16 X 30mm.		Baffle Opening 15 X 27mm.			
		Height	Refer to Drawing.	Weight	2.6	Grams.	
3.	Magnet	Materials	Rare Earth .	Size	Ø 7.9X1.3	mm.	
4	Nominal Impedance	8 Ω ± 15 % At 1500 Hz.					
5.	Power Rating	Normal	500 mW.	Maximum	1000	mW.	
6.	Lowest Resonant Frequency	500 ± 20 % Hz.					
7.	Output Sound Pressure Lever (S.P.L.)	77 ± 3 db / 0.5 Watt . 0.5 Meter.					
		Average at	800,	1000,	1200,	1500 Hz.	
8.	Frequency Range	300 ~ 4000 Hz.		Average S P L - 10 db.			
9.	Distortion	5 %	Maximum At	1000 Hz.	500 mW.		
10.	Abnormal Sound Test	Must be Normal Tested By			2.0 Volts.	Sine Wave.	
11.	Load Test	White Noise with Weighted Filter			2.0 Volts.(RMS)	24Hrs.	
12.	Polarity	Diaphragm shall move Forward when Apply a Positive DC.					
		Current to the "+" or "Marked" Terminal.					

MOUNTING NOTICE


AT LEAST
0.8mm
FOR
DIAPHRAM
MOVING



Unit : mm

Housing Material : ABS

30KMO8 VOL:2.00(0.5W) DIS:0.5M VANSOONIC
X:1.0000kHz *Y:77.33dB ZA:Live Curve SSR Fund.



21-AUG-2000 10:20:21

Mode: SPEAKER