



STENCIL ROLLS

Material Designed Specifically for SMT Screen Printers

- Less down time, less change over time, and less inventory required
- Material adaptable for all vacuum and non-vacuum machines
- High strength, even when wet
- Exceptionally low lint levels
- Solvent resistant and highly absorbent
- Excellent in both wet and dry applications
- Custom stencil rolls available upon request

PART NO.	WIDTH/CORE LENGTH	MAKE	REPLACES OEM ROLL & MACHINE TYPE	CORE LENGTH	CORE ID	ROLL LENGTH
EB41M1855	445/457/41 mm	MPM	P1485 AP & UP Series 3000 18"	18"	.75"	55'
EB41M1818-1	2348/457/41 mm	MPM	P2348 AP Series	18"	1.0"	47'
EB41M1812	305/457/41 mm	MPM	P2112 AP Series	18"	.75"	55'
EB41M2424	600/609/41 mm	MPM	MPM AP36	24"	.75"	55'
EB41M1809	223/457/41 mm	MPM	AP17, 21, 25, 27 UP 2000	18"	.75"	55'
EB41M0909	223/457/41 mm	MPM	AP17, 21, 25, 27	9"	.75"	55'
EB41M2222	550/559/41 mm	MPM	UP 3000 22"	22"	.75"	55'
EB41D1818	265/455/41 mm	DEK	DEK 260A #128034	18"	.75"	39'
EB41D2112	265/305/41 mm	DEK	265 Series	12"	.75"	39'
EB41D2120	265/530/41 mm	DEK	265 Series GS #129051	21"	.75"	39'
EB41D2121	265/540/41 mm	DEK	DEK265 #112239	21.25"	.75"	39'
EB41D2116	265/400/41 mm	DEK	DEK 265 GS/GSX/288 Horizon Infinity	21"	.75"	39'
EB41E1212	300/41 mm	EKRA	E4, E5	12"	.5"	33'
EB41E1616	400/41 mm	EKRA	E4, E5	16"	.5"	33'
EB41E2020	500/41 mm	EKRA	E4, E5	20"	.5"	33'
EB41E2424	600/41 mm	EKRA	E4, E5	24"	.5"	33'
EB41S1616	410/410/41 mm	SMTECH	SMT Quad	16"	1.5"	39'
EB41S2120	520/520/41 mm	SMTECH	SMT Quad	20"	1.5"	39'
EB41P1414	PGI 360/41 mm	Panasonic	GI Series	14.18"	1.5"	40'
EB41P1414-118	PGI 360/41 mm	Panasonic	GI Series	14.18"	1.5"	118'
EB41P1616	PGI 410/41 mm	Panasonic	GI Series	16"	1.5"	40'
EB41P1616-108	PGI 410/41 mm	Panasonic	GI Series	16"	1.5"	108'
EB41P2121	PGI 540/41 mm	Panasonic	GI Series	21.25"	1.5"	40'
EB41P2821	MSS	Panasonic	MSS	28"	1.5"	45'
EB41F1919	495/495/41 mm	Fuji	Fuji GSP	19.5"	1.0"	33'