






OPERATING VOLTAGE	100-240V
VOLTAGE CLASS	II
FREE AIR POWER AT 100V	10W APPROX.
FREE AIR POWER AT 240V	10W APPROX.
CABLE SPECIFICATION	20AWG, BLACK SILICONE INSULATED, UL STYLE 3367 200°C 300V
APPROX. WEIGHT	20GRAMS

*HEATER POWER WILL VARY ACCORDING TO APPLICATION.



ISOMETRIC VIEW (1:1)

TYPICAL INRUSH GRAPH



REVISION HISTORY									
REV	DESCRIPTION						DATE	ENGINEER	APPROVED
01	INITIAL RELEASE						19/02/2013	MLR	ML
REPRODUCTIONS OF THIS DRAWING OR TRANSFER TO A THIRD PARTY ARE NOT TO BE MADE WITHOUT PERMISSION FROM DBK TECHNITHERM.				IF IN DOUBT - ASK	PROJECT:	ALL UNITS IN MILLIMETERS UNLESS STATED	THIRD ANGLE PROJECTION		TOLERANCES UNLESS STATED: 0.00 ±0.1 0.0 ±0.3 0 ±0.5 ANGULAR ±0.5°
				DO NOT SCALE	CUSTOMER:	CUST PT No:			
DRN	DATE	CHKD	APPR	DATE	MATERIAL:	FINISH:	GEN SCALE:	DRG SHT	
MLR	19/02/2013	JRJ	ML	19/02/2013	N/A	N/A	1:1	A3	
DBK Technitherm Ltd UNIT II, LLANTRISANT BUSINESS PARK LLANTRISANT CF72 8LF WALES, UK					TITLE: HP05 I-20 100-240V 100-30				
					PART No: FG14397.4			ISSUE 01	SHEET 1 / 1