

Hexagonal locknut


50.2xx ES

Configuration

Hexagonal locknut	Stainless steel 1.4305
Internal thread	metric, as per EN 60423

Properties

	for secure tightening of cable glands and accessories
Temperature range	bis +200°C



Features

Standard

A	SW1	H		Part No.
	mm	mm	Piece	
M12x1,5	14	2,8	50	50.212 ES
M16x1,5	19	2,8	50	50.216 ES
M20x1,5	24	3	50	50.220 ES
M25x1,5	30	3,5	50	50.225 ES
M32x1,5	36	4	25	50.232 ES
M40x1,5	46	5	10	50.240 ES
M50x1,5	60	5	5	50.250 ES
M63x1,5	70	6	5	50.263 ES