




8 7 6 5 4 3 2 1




ASSEMBLY - VIEW FROM FRONT




ASSEMBLY - VIEW FROM BOTTOM



8 7 6 5 4 3 2 1



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

1589H6F1BKRF
Finish - Front - Black Painted Steel
Back - Black Painted Steel
Rated - 125 VAC, 60 Hz, 20 Amps
Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Recognized Standard UL1363
Cord Length
1589H6F1BKRF - 6' Foot Power Cord (NEMA 5-20P)
1589H6G1BKRF - 15' Foot Power Cord (NEMA 5-20P)

