

6.00086.50 PowerMaxx Li

## 7.2 Volt Cordless Drill / Screwdriver PowerMaxx Li

- Lightweight for fatigue-free work
- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Motor with integrated air cooling
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Spindle stop for manual turning and loosening of screws
- Spindle with hexagon recess for screwdriver bits
- Pistol grip for optimum power transmission in direction of drilling
- Rubber-coated handle provides a comfortable non-slip grip for the user
- High service life due to 3-level planetary metal gears
- Sturdy die cast gearbox housing for long service life

### Comparative technical values

Type of battery pack	Li-Ion
Battery pack voltage	7,2 V
Capacity of battery pack	2,2 Ah
Max. torque, soft	9 Nm
Max. torque, hard	16 Nm
Drill diameter in	
No-load speeds	0 - 250 / 0 - 750 /min
Drill spindle thread	1/2" -20 UNF
Chuck capacity	0,8 - 6,5 mm
Weight (including battery pack)	0,73 kg

### Scope of delivery

quick-action keyless chuck Futuro Plus, Li-Ion battery packs (7.2 V/2.2 Ah), charger LC 60, tool bag