



## Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: Non-switching: 100mA/50V DC  
Switching: 25mA/24V DC
- Contact resistance: 100mΩ max. (initial)
- Insulation resistance: 100MΩ min.

**Note:**

- RoHS Compliant

**Mechanical Specifications:**

- Operating temperature: -40°C ~ +85°C
- Operation force: 500gf max.

| Mouser Stock No. | No. of Pos. | Dim A. mm (In.) | Top Tape |
|------------------|-------------|-----------------|----------|
| 106-NHD2-EV      | 2           | 3.77 (.148)     | without  |
| 106-NHD4-EV      | 4           | 6.31 (.248)     | without  |
| 106-NHD6T-EV     | 6           | 8.85 (.348)     | with     |
| 106-NHD8T-EV     | 8           | 11.39 (.448)    | with     |
| 106-NHD10T-EV    | 10          | 13.93 (.548)    | with     |

**Dip Switches**

106-NHD2-EV, 106-NHD4-EV, 106-NHD6T-EV,  
106-NHD8T-EV, 106-NHD10T-EV

**Mountain  
Switch**