




1

BLOCK: PHENOLIC, BLACK, PER MIL-M-14 TYPE CFG.
JACKSCREW BODY: BRASS.
FLAT WASHER, ROLL PIN & JACKSCREW TIP: STAINLESS STEEL.

2

JACKSCREW BODY:
.200 MIN ZINC WITH AN RoHS COMPLIANT CHROMATE COATING.
FLAT WASHER & JACKSCREW TIP: PASSIVATED STAINLESS STEEL.

3

ACCOMODATES 14 TYPE II OR III #16 PIN OR SOCKET CONTACTS,
2 COAXICON PIN CONTACTS & 12 MALE POWER CONN CONTACTS.

4

FOR MATING RECEPT & PANEL CUTOUT SEE DWG 202478.

5

TYPE I #12 PIN CONTACT USED FOR GROUND.

6

SWAGGED AT 60°. ON BOTH SIDES

2

202479-2

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH

1

DWN B. CARBO 02 AUG 96	NAME TE TE Connectivity PLUG BLOCK ASSEMBLY, 29 POSITION, WITH CENTER FASTENER, M SERIES				
CHK R. STONE 08 AUG 96					
APVD G. STEINHAUER 22 AUG 96					
PRODUCT SPEC — APPLICATION SPEC — WEIGHT —					
CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C=202479	RESTRICTED TO —
SCALE 2:1			SHEET 1 of 1	REV M	

1471-9 (1/15)