



DESCRIPTION: M12 MALE - PANEL MOUNT (REAR) - SOLDER CUP - 12 POS.



PANEL CUTOUT



NUT

NOTE:

MATERIAL

HOUSING:
CONTACT:
SHELL:
NUT:
O-RING:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
EDPM

FINISH
CONTACT:

GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED
NICKEL PLATED

ELECTRICAL

RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:



1A
30V
100 mOhms MIN.
10 MOhms MAX.
IP67

ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C
WIRE GAUGE: 24-28 AWG

859-012-103R00Y

1 = GOLD FLASH
4 = 10µ" GOLD



RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
CHECKED:

DATE:
03-08-16
DATE:

NorComp

SCALE:
N.T.S.

SHEET
1 OF
1

REV
1

DWG NO.

859-012-103R00Y