

Datasheet

Item No. 77.331.1035.0

Bottom BAS GUT GM 10 M20 69 A0

revos BASIC 690V size 10 closed-bottom base with cable gland
M20, left, single locking lever



Item No.	77.331.1035.0
EAN	4015573622661
order unit	1 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Nominal voltage	690
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	10
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	20
Hinged lid	No
EMC-version	No