

Identification



Identification Products

**HellermannTyton**



# Identification Products

## Table of Contents

|                                    |    |
|------------------------------------|----|
| TagPrint Pro 3.0 Software .....    | 4  |
| Printers .....                     | 6  |
| Thermal Transfer Labels .....      | 8  |
| Self Laminating Label .....        | 10 |
| ShrinkTrak Labels .....            | 12 |
| Foam Nameplates .....              | 14 |
| Tip Tags .....                     | 15 |
| Pre-Printed Warning Labels .....   | 16 |
| Continuous Roll Vinyl Labels ..... | 18 |
| Specifications .....               | 20 |

# TagPrint<sup>PRO</sup> 3.0



## **Increase Productivity, Reduce Errors and Decrease Time Spent Producing Labels with a Complete Labeling Management Solution from HellermannTyton**

HellermannTyton's labeling system is comprised of the feature-rich labeling design software – TagPrint Pro 3.0, the highest quality thermal transfer, laser and ink jet printable labels, and a complete line of desk top thermal transfer printers.

### ***Simplify Your Label Design and Printing Process with TagPrint Pro 3.0***

TagPrint<sup>®</sup> Pro 3.0 is the cost-effective, easy-to-use label design and printing software in the HellermannTyton labeling system for achieving improved efficiency in wire and component marking, asset tagging, and structured cabling identification. Compatible with Windows<sup>®</sup> 7, Vista and XP as well as future operating systems such as Windows<sup>®</sup> 8, TagPrint<sup>®</sup> Pro 3.0 delivers an individualized, task-based experience that enables a user to easily develop labels with bar codes, text and graphics to meet numerous applications.

Designed for the industry specific needs of a business producing products on a shop floor or labeling products at a remote job site, the

intuitive interface of TagPrint Pro 3.0 simplifies the process of creating labels. TagPrint<sup>®</sup> Pro 3.0 streamlines labeling production by offering a user full control over the importing or entering of data, advanced security features, the option to group label designs under a single file name or job number, and the ability to batch print to either one or more printers at the same time.

Increase efficiency and reduce labor. TagPrint Pro 3.0 allows for complete management of the labeling process with a label design software system that simplifies the label creation process used to identify cables, tubes, conduits, components and equipment.

### **Familiar Task-based Navigation**

TagPrint Pro 3.0 has a Ribbon interface that offers quick and easy access to the commands that are needed to complete a task. Commands are organized in logical groups, which are collected together under tabs. Each tab relates to a type of activity, such as “Label”, “Table”, “Print” and “Utility”.

### **Batch Printing**

3.0 has a “print-later” feature for the purpose of batching under one file name in a simple print utility. Using built-in Macros, design each label and then define print options for execution at time of printing. Access the project file and concurrently print labels to a single printer or multiple printers.

### **At-a-glance Interface**

Whether it is one label or a page of labels, the 3.0 interface was designed to allow ease of control over print jobs from a single screen. Information is viewable at a glance so a user can view object properties, data information, and actual label layout at the same time. When changes are made, information is updated.

### **Built-in Security**

TagPrint Pro 3.0 offers a built-in security system for the restriction of use or protection of data. This feature allows the user to lockout or password protect label designs and data tables from unauthorized label editing. Available for purchase as a single-user or network license.

### **Expanded Import Capabilities and “Live Sync”**

3.0 has the ability to import a database that has been exported from another program (i.e., CAD) or connect to existing database (i.e., Excel) files with the added ability to sync up to that database at timed intervals set by the user. If enabled, this feature allows variable information to be updated automatically so that print data is fully controlled from one location without a manual refresh at each computer terminal.

### **Editing Convenience**

Label designs can be edited in Portrait or Landscape mode, as well as show the direction of label feed next to the design.

### **“PIN” Favorites**

Tagprint Pro 3.0 allows the user to “pin” saved label designs and data tables making them immediately available in the file menu.

### **Single-user License or Network Version Available**

TagPrint Pro 3.0 is available as a single-user license, or as a network version which allows a user to share printers, label designs, and data tables from multiple workstations within a single location.

## TT230SM Printer

HellermannTyton's TT230SM thermal transfer printer is the next generation of printer available for small-to-medium volume users looking for an easy to use and functional thermal transfer printer. The TT230SM prints to a wide variety of materials including all of HellermannTyton labels and ShrinkTrak.

- Uses standard ribbons
- Print head 300 dpi
- Barcodes: standard and 2D
- Ethernet network ready



## SwiftMark Automatic Label Printer and Applicator

Designed specifically for the wire and cable industry, the SwiftMark sets a new standard in labeling efficiency. The SwiftMark automatic label printer and applicator prints self-laminating vinyl labels and applies them to various sizes of wire and cable, increasing labeling productivity up to 400%.





## TTM430 / TTM460 Thermal Transfer Printer

HellermannTyton's TTM430 and TTM460 thermal transfer printers are ideal for medium-to-large volume users looking for an easy to use and extremely functional thermal transfer printer. Both print to a wide variety of materials including all HellermannTyton's labels and ShrinkTrak. Used along with TagPrint Pro, these printers will offer error free printing and seamless operations.

- Printhead 300 (TTM430) and 600 dpi (TTM460) for small text and smooth graphics
- Print speed up to 7.87" per second
- Straight through design allows easy loading of ribbon and labels. (Labels are held in an interchangeable media hub).
- Lightweight/minimal foot print



# INDUSTRIAL CONTROL PANEL


**HellermannTyton**

|                               |                     |
|-------------------------------|---------------------|
| Serial Number:                | RC2356YUP77         |
| Current:                      | 125 Amperes         |
| Largest Motor H.P.            | 20 Horsepower       |
| Max OCP Device:               | 60 Amperes          |
| Voltage:                      | 460 - 480 Volts     |
| Phase and Frequency:          | 3ph, 60 Hz          |
| Short Circuit Current Rating: | 100,000 Amperes RMS |
| Diagram Number:               | HT-4322             |
| NEMA Rating:                  | TYPE 2              |

TAG80T1-795

**2 DISCONNECTS REQUIRED TO DE-ENERGIZE**

TAG80T1-795 | 3.0" x 5.0"



## UID MILITARY APPROVED LABEL MATERIAL - 7871

MIL-STD-810  
ASTM D3330  
ASTM D4060  
UL Recognized  
British Standard BS-5609

Unique Item Identifier (UID) military compliant labeling system. Tested by the Naval Surface Warfare Center (NSWC) for high and low temperature cycling, salt, fog, chemical and abrasion resistance and adhesive performance.

**HellermannTyton**

TAG33T1-DTH | 3.0" x 2.0"

(123) 456-7890

TAGPP3T4-822  
.688" x .25"

**TAG75T1-822**

**DATACOM WIRING INSIDE**

TAG75T1-822  
2.0" x .625"

PATCH

PANEL

WALL

PLATE

CLEAR

TAGPP1T6-822C

TAGPP1T6-822C  
.625" x .33"

TERMINAL MARKING  
BLOCK

01 02 03 04 05 06 07 08 09 10

TAG83T1-822

TAG83T1-822 | 4.0" x .312"



INCREMENT: 188  
SERIAL: 0000BS  
TAG15T3-795

INCREMENT: 189  
SERIAL: 0000BT  
TAG15T3-795

INCREMENT: 190  
SERIAL: 0000BU  
TAG15T3-795

INCREMENT: 191  
SERIAL: 0000BV  
TAG15T3-795

INCREMENT: 192  
SERIAL: 0000BW  
TAG15T3-795

INCREMENT: 193  
SERIAL: 0000BX  
TAG15T3-795

INCREMENT: 194  
SERIAL: 0000BY  
TAG15T3-795

INCREMENT: 195  
SERIAL: 0000BZ  
TAG15T3-795

INCREMENT: 197  
SERIAL: 0000C1  
TAG15T3-795

INCREMENT: 198  
SERIAL: 0000C2  
TAG15T3-795

TAG16T3-822  
01/27/12 9:00 AM

TAG16T3-822  
01/27/12 9:00 AM

TAG16T3-822  
01/27/12 9:00 AM

TAG16T3-822  
01/27/12 9:01 AM

TAG16T3-822  
01/27/12 9:01 AM

TAG16T3-822  
01/27/12 9:01 AM

TAG16T3-822  
01/27/12 9:02 AM

TAG16T3-822  
01/27/12 9:02 AM

TAG16T3-822  
01/27/12 9:02 AM

TAG16T3-822  
01/27/12 9:03 AM

TAG16T3-822  
01/27/12 9:03 AM

TAG16T3-822  
01/27/12 9:03 AM

TAG16T3-822  
01/27/12 9:04 AM

TAG16T3-822  
01/27/12 9:04 AM

TAG16T3-822  
01/27/12 9:04 AM

TAG15T3-795 1.0" x .5"



TAG16T3-822 .9" x .25"



TAG71T5-822  
.5" x .43"



TAG82T2-822

A2

A3

A4

TAG82T2-822 1.5" x .25"

TAG82T2-822 .25" x .25"



100V – 7.0 AMPS

TAG69T1-336 2.0" x .275"

**HellermannTyton**

7930 N. Faulkner Rd.  
Milwaukee, WI 53224  
1-800-537-1512



RATING: 678-9854  
VOLTS: 120  
TYPE: TAG76T1-795  
SERIAL: SN-000023

TAG76T1-795 2.5" x 2.0"

TAG73T1-795



Date and time stamp

01/25/12 2:34 PM

TAG73T1-795 2.0" x 1.0"

# Self-Laminating Labels

## TAG6T1-100B

Self laminating for cables  
Flat ribbon cables  
Fiber optic cables

TAG6T1-100B | 2.0" x 3.75"

## TAG24T1-100B

### WIRE & CABLE MARKING

TAG24T1-100B  
2.0" x 1.437"

## TAG7T1-100B



LARGE CABLES OR  
CABLE BUNDLES

Input: 120VAC 60 Hz 15W



TAG  
9T3-100B

TAG9T3-100B  
1.0" x 2.25"

General Copper  
or Fiber Marker  
**TAG53T2-100B**

TAG53T2-100B  
1.5" x 1.437"

Sequentially Numbered

## 0021

TAG22T2-100B

TAG22T2-100B  
1.0" x 1.43"

TAG7T1-100B | 2.0" x 7.347"



# Self-Laminating Labels

**TAG  
38T4  
100B**



**DANGER**

**HIGH VOLTAGE CABLE**



CABLE GiC/81D  
CABLE GiC/81D  
CABLE GiC/81D  
CABLE GiC/81D

**DATA LINE**



**TAG9T3-100B**

TAG1T1-100B  
.9" x 3.12"

**TAG51T3-100B**

TAG51T3-100B  
1.0" x .75"

TAG10T2-100B | 2.0" x 2.25"



**TAG26T6  
-100B**


TAG26T6-  
100B  
.5" x .75"



TAG9T3-100B  
1.0" x 2.25"



TAG38T4-100B  
1.0" x 7.347"

TAG22T2-100B  
1.0" x 1.43"





# Foam Nameplate Labels

**HellermannTyton**

## TRUE HEPA AIR CLEANER

**Model No. 13520**

**Made in U.S.A. of US and Foreign Components**  
120V A.C., 60 Hz, 1.5A

Thermally Protected  
Patent No. 4392

READ ALL INSTRUCTIONS BEFORE USING  
UNPLUG BEFORE SERVICING



**596-00503**  
BLACK FOAM  
NAMEPLATE LABEL

596-00503  
1.06" x .49"

**596-00500**  
WHITE FOAM  
NAMEPLATE LABEL

596-00500  
1.06" x .49"

For Consumer Relations call 1-800-537-1512

596-00417 | 3" x 4"

**START**

596-00412  
1.25" x 1.25"  
.88" hole dia.

**STOP**

White Foam  
Button Label  
1.2mm hole  
**596-00414**

596-00414 | 1.75" x 1.75"

**596-00415**

*Foam Button Label*

**ON**

**OFF**

Black Foam  
Button Label  
1.2mm hole  
**596-00415**

596-00415 | 1.75" x 1.75"

**UNLOCK**

596-00413  
1.25" x 1.25"  
.88" hole dia.

**596-00507**

BLACK FOAM NAMEPLATE LABEL

**TOGGLE SWITCH**

596-00507 | 2" x 1"

**POWER  
MODULE**

596-00504 | 2" x 1"

**STOP**





# Tips Tag Labels





556-26008 | 2.59" x .68"



556-26006 | 2.59" x .50"




556-26007 | 3.54" x .50"



556-26009 | 3.54" x .68"

**TIPTAG**  
**Durattach Ribbon**  
Yellow on Front/White on back



**DANGER**

**Contact may cause  
electric shock or burn.  
Turn off and lock out  
system power  
before servicing.**

HellermannTyton 596-00377



**DANGER**

596-00376 | 5.5" x 2.75"



**WARNING**

596-00377 | 5.5" x 2.75"



**WARNING**

**BURN HAZARD**

**Hot Surface Inside.  
Allow to cool before  
servicing.**

HellermannTyton 596-00376

# **DANGER**

**AREA IN FRONT OF THIS  
ELECTRICAL PANEL MUST BE  
KEPT CLEAR FOR 36 INCHES.  
OSHA-NEC REGULATIONS**

*Shown at 90%*

## **DANGER**



596-00203  
6" x 4"




# ⚠️ WARNING

## Arc Flash Hazard Appropriate PPE Required

|                                |              |
|--------------------------------|--------------|
| Establish Protection Boundary: | 18 inches    |
| Personal Protective Equipment: | Class 0      |
| Radiant Energy at 36 inches:   | 1.08/Cal/Cm2 |

|                               |           |
|-------------------------------|-----------|
| Limited Approach Boundary:    | 60 Inches |
| Restricted Approach Boundary: | 32 Inches |
| Prohibited Approach Boundary: | 12 Inches |

MTQS#:4620.1    Date Issued: January 2010    Study Rev: 0  
Refer to NFPA 70E for minimum PPE requirements.



# ⚠️ CAUTION




**ENGINEERED SERIES  
COMBINATION SYSTEM  
RATED 50K AMPERES  
IDENTIFIED REPLACEMENT  
COMPONENTS REQUIRED**

558-00330 | 3" wide roll



558-00328 | 2" wide roll

# Continuous Roll Vinyl Labels



## Thermal Transfer Labels

| Product Selection |                 |          |       |        |                 |       |                 |       |                   |       |                |        |                |           |
|-------------------|-----------------|----------|-------|--------|-----------------|-------|-----------------|-------|-------------------|-------|----------------|--------|----------------|-----------|
| Article No.       | Part No.        | Type     | Width |        | Height of Label |       | Vertical Repeat |       | Horizontal Repeat |       | Width of Liner |        | Labels per Row | Pkg. Qty. |
|                   |                 |          | In.   | mm.    | In.             | mm.   | In.             | mm.   | In.               | mm.   | In.            | mm.    |                |           |
| 250 Material      |                 |          |       |        |                 |       |                 |       |                   |       |                |        |                |           |
| 598-00277         | TYHCT-250       | TYHC     | .250  | 6.35   | 1.500           | 38.10 | 1.625           | 41.27 | .250              | 6.35  | 4.120          | 104.70 | 16             | 5000      |
| 596-21250         | TAG21T6-250     | TAG21T6  | .5    | 12.70  | .75             | 19.05 | .875            | 22.22 | .5                | 12.7  | 3.25           | 82.55  | 6              | 10000     |
| 596-11250         | TAG11T4-250     | TAG11T4  | .65   | 16.50  | .2              | 5.08  | .3              | 7.62  | .65               | 16.5  | 2.6            | 66.04  | 4              | 5000      |
| 596-28250         | TAG28T4-250     | TAG28T4  | .80   | 20.30  | 1.43            | 36.3  | 1.62            | 41.1  | .80               | 20.3  | 3.45           | 87.6   | 4              | 5000      |
| 596-15250         | TAG15T3-250     | TAG15T3  | 1.0   | 25.40  | .5              | 12.7  | .6              | 15.24 | 1.0               | 25.4  | 3.35           | 85.09  | 3              | 10000     |
| 596-00044         | TAG35T2-250     | TAG35T2  | 2.0   | 50.80  | .375            | 9.53  | .50             | 12.7  | 2.0               | 50.8  | 4.1            | 104.14 | 2              | 10000     |
| 336 Material      |                 |          |       |        |                 |       |                 |       |                   |       |                |        |                |           |
| 596-00026         | TAG96T1-336     | TAG96T1  | 1.875 | 47.60  | .25             | 6.35  | .375            | 9.35  | 1.875             | 47.6  | 2.0            | 50.8   | 1              | 5000      |
| 596-00041         | TAG69T1-336     | TAG69T1  | 2.0   | 50.80  | .275            | 6.98  | .5              | 12.7  | 2.0               | 50.8  | 2.125          | 53.97  | 1              | 10000     |
| 596-00040         | TAG68T1-336     | TAG68T1  | 3.8   | 96.50  | .275            | 6.98  | .5              | 12.7  | 3.8               | 96.5  | 4.0            | 101.6  | 1              | 10000     |
| 795 Material      |                 |          |       |        |                 |       |                 |       |                   |       |                |        |                |           |
| 596-15795         | TAG15T3-795     | TAG15T3  | 1.0   | 25.40  | .5              | 12.7  | .6              | 15.24 | 1.0               | 25.4  | 3.35           | 85.09  | 3              | 10000     |
| 596-27795         | TAG27T3-795     | TAG27T1  | 1.5   | 38.11  | .75             | 19.05 | .875            | 22.2  | 1.5               | 38.11 | 2.20           | 55.88  | 1              | 3000      |
| 596-75795         | TAG75T1-795     | TAG75T1  | 2.0   | 50.80  | .625            | 15.87 | .75             | 19.05 | 2.0               | 50.8  | 2.12           | 53.8   | 1              | 2000      |
| 596-73795         | TAG73T1-795     | TAG73T1  | 2.0   | 50.80  | 1.0             | 25.4  | 1.125           | 28.57 | 1.0               | 25.4  | 2.20           | 55.83  | 1              | 3000      |
| 596-76795         | TAG76T1-795     | TAG76T1  | 2.5   | 63.50  | 2.0             | 50.8  | 2.12            | 53.8  | 2.5               | 63.5  | 2.62           | 66.5   | 1              | 1000      |
| 596-72795         | TAG72T1-795     | TAG72T1  | 2.75  | 69.85  | 1.25            | 31.75 | 1.375           | 34.93 | 2.75              | 69.85 | 2.95           | 74.95  | 1              | 3000      |
| 596-78795         | TAG78T1-795     | TAG78T1  | 3.0   | 76.20  | 4.0             | 101.6 | 4.12            | 104.7 | 3.0               | 76.2  | 3.12           | 79.2   | 1              | 500       |
| 596-80795         | TAG80T1-795     | TAG80T1  | 3.0   | 76.20  | 5.0             | 127   | 3.0             | 76.2  | 3.0               | 76.2  | 3.125          | 79.37  | 1              | 500       |
| 596-79795         | TAG79T1-795     | TAG79T1  | 4.0   | 101.60 | 2.0             | 50.8  | 2.12            | 53.97 | 4.0               | 101.6 | 4.25           | 107.9  | 1              | 500       |
| 822 Material      |                 |          |       |        |                 |       |                 |       |                   |       |                |        |                |           |
| 596-27822         | TAG27T1-822     | TAG27T1  | 1.5   | 38.11  | .75             | 19.05 | .875            | 22.2  | 1.5               | 38.11 | 2.20           | 55.88  | 1              | 3000      |
| 596-00019         | TAG75T1-822     | TAG75T1  | 2.0   | 50.80  | .625            | 15.87 | .75             | 19.05 | 2.0               | 50.8  | 2.12           | 53.8   | 1              | 2000      |
| 596-70822         | TAG70T12-822    | TAG70T12 | .25   | 6.35   | .25             | 6.35  | .5              | 12.7  | .25               | 6.35  | 3.2            | 81.2   | 12             | 10000     |
| 596-00028         | TAGPP1T6-822    | TAGPP1T6 | .625  | 15.87  | .333            | 8.45  | .75             | 19.05 | .625              | 15.87 | 3.8            | 96.52  | 6              | 1000      |
| 596-00082         | TAGPP1T6-82210M | TAGPP1T6 | .625  | 15.87  | .333            | 8.45  | .75             | 19.05 | .625              | 15.87 | 3.8            | 96.52  | 6              | 10000     |
| 596-11822         | TAG11T4-822     | TAG11T4  | .65   | 16.50  | .2              | 5.08  | .3              | 7.62  | .65               | 16.5  | 2.6            | 66.04  | 4              | 5000      |
| 596-00046         | TAGPP2T6-822    | TAGPP2T6 | .66   | 16.70  | .33             | 8.38  | .75             | 19.05 | .66               | 16.7  | 4.125          | 104.7  | 6              | 1000      |
| 596-00083         | TAGPP3T4-822    | TAGPP3T4 | .688  | 17.40  | .25             | 6.35  | .688            | 17.4  | .375              | 9.52  | 2.9            | 73.66  | 4              | 1000      |
| 596-13822         | TAG13T4-822     | TAG13T4  | .75   | 19.05  | .25             | 6.35  | .35             | 8.89  | .75               | 19.05 | 3.35           | 85.09  | 4              | 10000     |
| 596-15822         | TAG15T3-822     | TAG15T3  | 1.0   | 25.40  | .5              | 12.7  | .6              | 15.24 | 1.0               | 25.4  | 3.35           | 85.09  | 3              | 10000     |
| 596-84822         | TAG84T3-822     | TAG84T3  | 1.25  | 31.75  | .375            | 9.53  | .50             | 12.7  | 1.25              | 31.75 | 4.0            | 101.6  | 3              | 10000     |
| 596-00023         | TAG83T1-822     | TAG83T1  | 4.0   | 101.60 | .312            | 7.52  | .438            | 11.13 | 4.0               | 101.6 | 4.1            | 104.14 | 1              | 5000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

\* TAG17T2-822 not recommended for TT105M, TT2105M, TT2305M, TT3005M, TT3105M, and TT3305M printers. Use TAG82T2 instead.



## Thermal Transfer Labels

| Product Selection            |                  |          |       |       |                    |       |                    |       |                      |       |                |       | Labels<br>per<br>Row | Pkg.<br>Qty. |
|------------------------------|------------------|----------|-------|-------|--------------------|-------|--------------------|-------|----------------------|-------|----------------|-------|----------------------|--------------|
| Article No.                  | Part No.         | Type     | Width |       | Height of<br>Label |       | Vertical<br>Repeat |       | Horizontal<br>Repeat |       | Width of Liner |       |                      |              |
|                              |                  |          | In.   | mm.   | In.                | mm.   | In.                | mm.   | In.                  | mm.   | In.            | mm.   |                      |              |
| 822 Material (cont.)         |                  |          |       |       |                    |       |                    |       |                      |       |                |       |                      |              |
| 596-00022                    | TAG81T8-822      | TAG81T8  | .325  | 8.25  | .20                | 5.08  | .30                | 7.62  | .325                 | 8.25  | 2.6            | 66.04 | 8                    | 5000         |
| 596-16822                    | TAG16T3-822      | TAG16T3  | .9    | 22.86 | .25                | 6.35  | .35                | 8.89  | .9                   | 22.86 | 3.35           | 85.09 | 3                    | 10000        |
| 596-17822                    | TAG17T2-822      | TAG17T2  | 1.5   | 38.11 | .25                | 6.35  | .35                | 8.89  | 1.65                 | 41.98 | 3.35           | 85.09 | 2                    | 10000        |
| 596-73822                    | TAG73T1-822      | TAG73T1  | 2.0   | 50.80 | 1.0                | 25.4  | 1.125              | 28.57 | 1.0                  | 25.4  | 2.20           | 55.83 | 1                    | 3000         |
| 596-42822                    | TAG72T1-822      | TAG72T1  | 2.75  | 69.85 | 1.25               | 31.75 | 1.375              | 34.93 | 2.75                 | 69.85 | 2.95           | 74.95 | 1                    | 3000         |
| 596-71822                    | TAG71T5-822      | TAG71T5  | .5    | 12.70 | .43                | 11.1  | .662               | 16.81 | .43                  | 11.1  | 3.35           | 85.09 | 5                    | 10000        |
| 596-82822                    | TAG82T2-822      | TAG82T2  | 1.5   | 38.10 | .25                | 6.35  | .30                | 7.62  | 1.5                  | 38.1  | 3.20           | 81.28 | 2                    | 10000        |
| 822 C Material*              |                  |          |       |       |                    |       |                    |       |                      |       |                |       |                      |              |
| 596-00029                    | TAGPP1T6-822C    | TAGPP1T6 | .625  | 15.87 | .333               | 8.45  | .75                | 19.05 | .625                 | 15.87 | 3.8            | 96.52 | 6                    | 1000         |
| 596-00030                    | TAGPP1T6-822C10M | TAGPP1T6 | .625  | 15.87 | .333               | 8.45  | .75                | 19.05 | .625                 | 15.87 | 3.8            | 96.52 | 6                    | 10000        |
| 596-00003                    | TAG11T4-822C     | TAG11T4  | .6    | 16.50 | .2                 | 5.08  | .3                 | 7.62  | .65                  | 16.5  | 2.6            | 66.04 | 4                    | 5000         |
| 596-00047                    | TAGPP2T6-822C    | TAGPP2T6 | .66   | 16.70 | .33                | 8.38  | .75                | 19.05 | .66                  | 16.7  | 4.125          | 104.7 | 6                    | 1000         |
| 596-00084                    | TAGPP3T4-822C    | TAGPP3T4 | .688  | 17.40 | .25                | 6.35  | .375               | 9.52  | .688                 | 17.4  | 2.9            | 73.66 | 4                    | 1000         |
| 596-00001                    | TAG15T3-822C10M  | TAG15T3  | 1.0   | 25.40 | .5                 | 12.7  | .6                 | 15.24 | 1.0                  | 25.4  | 3.35           | 85.09 | 3                    | 10000        |
| 596-00043                    | TAG27T1-822C     | TAG27T1  | 1.5   | 38.11 | .75                | 19.05 | .875               | 22.2  | 1.5                  | 38.11 | 2.20           | 55.88 | 1                    | 3000         |
| DTH Material***              |                  |          |       |       |                    |       |                    |       |                      |       |                |       |                      |              |
| 596-00033                    | TAG13T4-DTH      | TAG13T4  | .75   | 19.05 | .25                | 6.35  | .35                | 8.89  | .75                  | 19.05 | 3.35           | 85.09 | 4                    | 10000        |
| 596-00034                    | TAG16T3-DTH      | TAG16T3  | .9    | 22.86 | .25                | 6.35  | .35                | 8.89  | .9                   | 22.86 | 3.35           | 85.09 | 3                    | 10000        |
| 596-00035                    | TAG15T3-DTH      | TAG15T3  | 1.0   | 25.40 | .5                 | 12.7  | .6                 | 15.24 | 1.0                  | 25.4  | 3.35           | 85.09 | 3                    | 10000        |
| 596-00036                    | TAG27T2-DTH      | TAG27T2  | 1.5   | 38.11 | .75                | 19.05 | .875               | 22.2  | 1.5                  | 38.11 | 2.20           | 55.83 | 2                    | 10000        |
| 596-00037                    | TAG99T1-DTH      | TAG99T1  | 2.0   | 50.80 | .25                | 6.35  | .375               | 9.52  | 2.0                  | 50.8  | 2.2            | 55.8  | 1                    | 2500         |
| 596-00038                    | TAG73T1-DTH      | TAG73T1  | 2.0   | 50.80 | 1.0                | 25.4  | 1.125              | 28.57 | 1.0                  | 25.4  | 2.20           | 55.83 | 1                    | 3000         |
| 596-00039                    | TAG33T1-DTH      | TAG33T1  | 3.0   | 76.20 | 2.0                | 50.8  | 2.13               | 53.97 | 2.0                  | 50.8  | 3.1            | 78.74 | 1                    | 1000         |
| PAP - Non-Adhesive Cardstock |                  |          |       |       |                    |       |                    |       |                      |       |                |       |                      |              |
| 596-00017                    | TAG74T2-PAP      | TAG74T2  | 1.75  | 44.45 | .375               | 9.53  | .562               | 14.2  | 1.75                 | 44.45 | 3.5            | 88.9  | 2                    | 1000         |
| 596-00025                    | TAG82T2-PAP      | TAG82T2  | 2.0   | 50.8  | .396               | 10.05 | .562               | 14.2  | 2.0                  | 50.8  | 4.05           | 102.0 | 2                    | 1000         |
| 596-00024                    | TAG85T1-PAP      | TAG85T1  | 3.0   | 76.2  | .50                | 12.7  | .60                | 15.24 | 3.0                  | 76.2  | 3.2            | 8.28  | 1                    | 5000         |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

\* Clear    \*\* Not recommended for TT1210 printer    \*\*\* For use with DTH ribbons only!

## Self-Laminating Labels

## Thermal Transfer Self-Laminating Labels

| Product Selection |              | Type    | Width |       | Height of Printable Area |       | Height of Label |       | Vertical Repeat |        | Horizontal Repeat |       | Width of Liner |        | Labels per Row | Pkg. Qty. |
|-------------------|--------------|---------|-------|-------|--------------------------|-------|-----------------|-------|-----------------|--------|-------------------|-------|----------------|--------|----------------|-----------|
| Article No.       | Part No.     |         | In.   | mm.   | In.                      | mm.   | In.             | mm.   | In.             | mm.    | In.               | mm.   | In.            | mm.    |                |           |
| 100B Material     |              |         |       |       |                          |       |                 |       |                 |        |                   |       |                |        |                |           |
| 596-00009         | TAG26T6-100B | TAG26T6 | .5    | 12.70 | .375                     | 9.52  | .75             | 19.05 | 1.0             | 25.4   | .5                | 12.7  | 3.35           | 85.09  | 6              | 10000     |
| 596-00010         | TAG2T5-100B  | TAG2T5  | .5    | 12.70 | .5                       | 12.7  | 1.43            | 36.5  | 1.62            | 41.28  | .66               | 16.81 | 3.35           | 85.09  | 5              | 10000     |
| 596-00014         | TAG51T3-100B | TAG51T3 | 1.0   | 25.40 | .35                      | 8.8   | .75             | 19.05 | .937            | 23.7   | 1.075             | 27.3  | 3.35           | 85.09  | 3              | 10000     |
| 596-00006         | TAG22T2-100B | TAG22T2 | 1.0   | 25.40 | .5                       | 12.7  | 1.43            | 36.5  | 1.62            | 41.28  | 1.075             | 27.3  | 2.25           | 57.1   | 2              | 5000      |
| 596-00007         | TAG22T3-100B | TAG22T3 | 1.0   | 25.40 | .5                       | 12.7  | 1.43            | 36.5  | 1.62            | 41.28  | 1.075             | 27.3  | 3.35           | 85.09  | 3              | 5000      |
| 596-00027         | TAG9T3-100B  | TAG9T3  | 1.0   | 25.40 | .75                      | 19.05 | 2.25            | 57.1  | 2.5             | 63.5   | 1.0               | 25.4  | 3.35           | 85.09  | 3              | 5000      |
| 596-00013         | TAG3T3-100B  | TAG3T3  | 1.0   | 25.40 | 1.0                      | 25.4  | 3.75            | 95.25 | 4.0             | 101.6  | 1.075             | 27.3  | 3.35           | 85.09  | 3              | 3000      |
| 596-00011         | TAG38T4-100B | TAG38T4 | 1.0   | 25.40 | 1.5                      | 38.1  | 7.35            | 188.9 | 7.75            | 196.80 | 1.0               | 25.4  | 4.10           | 104.14 | 4              | 1000      |
| 596-00045         | TAG53T2-100B | TAG53T2 | 1.5   | 38.1  | .7                       | 17.78 | 1.44            | 36.49 | 1.62            | 41.28  | 1.5               | 38.1  | 3.35           | 89.05  | 2              | 2500      |
| 596-00005         | TAG1T1-100B  | TAG1T1  | 1.9   | 48.26 | .75                      | 19.05 | 3.12            | 79.2  | 3.42            | 86.8   | 1.9               | 48.2  | 3.875          | 98.42  | 2              | 2500      |
| 596-00008         | TAG24T1-100B | TAG24T1 | 2.0   | 50.80 | .5                       | 12.7  | 1.44            | 36.49 | 1.68            | 42.6   | 2.0               | 50.8  | 2.2            | 55.9   | 1              | 1000      |
| 596-00002         | TAG10T2-100B | TAG10T2 | 2.0   | 50.80 | .75                      | 19.05 | 2.25            | 57.1  | 2.5             | 63.5   | 2.0               | 50.8  | 3.875          | 98.42  | 2              | 2500      |
| 596-00021         | TAG7T1-100B  | TAG7T1  | 2.0   | 50.80 | 1.5                      | 38.1  | 7.35            | 188.9 | 7.75            | 196.80 | 2.0               | 50.8  | 4.10           | 104.14 | 2              | 1000      |
| 596-00016         | TAG6T1-100B  | TAG6T1  | 2.0   | 50.80 | 1.5                      | 38.1  | 3.75            | 95.25 | 4.0             | 101.6  | 2.0               | 50.8  | 2.20           | 55.88  | 1              | 1000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Self-Laminating Labels

## Self-Laminating Laser Tags

| Product Selection |            | Type   | Width |      | Height of Printable Area |       | Height of Label |       | Labels per Row | Labels per Column | Labels per Sheet | Pkg. Qty. |
|-------------------|------------|--------|-------|------|--------------------------|-------|-----------------|-------|----------------|-------------------|------------------|-----------|
| Article No.       | Part No.   |        | In.   | mm.  | In.                      | mm.   | In.             | mm.   |                |                   |                  |           |
| 105 Material      |            |        |       |      |                          |       |                 |       |                |                   |                  |           |
| 594-26105         | TAG26L-105 | TAG26L | .50   | 12.7 | .375                     | 9.5   | .75             | 19.0  | 16             | 16                | 156              | 5000      |
| 594-02105         | TAG2L-105  | TAG2L  | .50   | 12.7 | .50                      | 12.7  | 1.43            | 36.5  | 16             | 7                 | 112              | 5000      |
| 594-05105         | TAG5L-105  | TAG5L  | .80   | 20.3 | .50                      | 12.7  | 1.43            | 36.4  | 8              | 7                 | 56               | 5000      |
| 594-65105         | TAG65L-105 | TAG65L | .81   | 20.7 | .81                      | 20.7  | 2.13            | 53.9  | 9              | 4                 | 36               | 1000      |
| 594-51105         | TAG51L-105 | TAG51L | 1.00  | 25.4 | .35                      | 8.89  | .75             | 19.0  | 8              | 12                | 84               | 5000      |
| 594-49105         | TAG49L-105 | TAG49L | 1.00  | 25.4 | .35                      | 8.8   | 1.00            | 25.5  | 8              | 8                 | 80               | 2500      |
| 594-63105         | TAG63L-105 | TAG63L | 1.00  | 25.4 | .50                      | 12.7  | 1.33            | 33.78 | 8              | 7                 | 56               | 2500      |
| 594-09105         | TAG9L-105  | TAG9L  | 1.00  | 25.4 | .75                      | 19.0  | 2.25            | 57.1  | 7              | 4                 | 28               | 1000      |
| 594-50105         | TAG50L-105 | TAG50L | 1.00  | 25.4 | 1.00                     | 25.4  | 3.16            | 80.4  | 8              | 3                 | 21               | 1000      |
| 594-64105         | TAG64L-105 | TAG64L | 1.17  | 29.6 | .83                      | 21.08 | 3.33            | 84.6  | 6              | 3                 | 18               | 1000      |
| 594-01105         | TAG1L-105  | TAG1L  | 1.90  | 48.2 | .75                      | 19.0  | 3.25            | 82.5  | 4              | 3                 | 12               | 1000      |
| 594-52105         | TAG52L-105 | TAG52L | 2.00  | 50.8 | .47                      | 33.7  | 1.33            | 33.7  | 3              | 7                 | 21               | 1000      |
| 594-10105         | TAG10L-105 | TAG10L | 2.00  | 50.8 | .75                      | 19.1  | 2.25            | 57.2  | 4              | 4                 | 16               | 1000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Ink Jet Self-Laminating Labels

| Product Selection |            | Type   | Width |       | Height of Print-able Area |       | Height of Label |       | Labels per Row | Labels per Column | Labels per Sheet | Pkg. Qty. |
|-------------------|------------|--------|-------|-------|---------------------------|-------|-----------------|-------|----------------|-------------------|------------------|-----------|
| Article No.       | Part No.   |        | In.   | mm.   | In.                       | mm.   | In.             | mm.   |                |                   |                  |           |
| 100B Material     |            |        |       |       |                           |       |                 |       |                |                   |                  |           |
| 593-26994         | TAG26J-994 | TAG26J | .500  | 12.70 | .350                      | 8.89  | .750            | 19.05 | 16             | 8                 | 128              | 2500      |
| 593-05994         | TAG5J-994  | TAG5J  | .800  | 20.30 | .500                      | 12.70 | 1.430           | 36.32 | 10             | 4                 | 40               | 1000      |
| 593-51994         | TAG51J-994 | TAG51J | 1.000 | 25.40 | .350                      | 8.89  | .750            | 19.05 | 8              | 8                 | 64               | 1000      |
| 593-22994         | TAG22J-994 | TAG22J | 1.000 | 25.40 | .500                      | 12.70 | 1.430           | 36.32 | 8              | 4                 | 32               | 1000      |
| 593-09994         | TAG9J-994  | TAG9J  | 1.000 | 25.40 | .750                      | 19.05 | 2.250           | 57.15 | 8              | 3                 | 24               | 1000      |
| 593-64994         | TAG64J-994 | TAG64J | 1.160 | 29.60 | .860                      | 21.80 | 3.250           | 82.60 | 7              | 2                 | 14               | 1000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Laser Tags Labels

## Product Selection

Product Selection

| Article No.        | Part No.    | Type     | Width |       | Height |       | Labels per Row | Labels per Column | Labels per Sheet | Pkg. Qty. |
|--------------------|-------------|----------|-------|-------|--------|-------|----------------|-------------------|------------------|-----------|
|                    |             |          | In.   | mm.   | In.    | mm.   |                |                   |                  |           |
| 788 Material       |             |          |       |       |        |       |                |                   |                  |           |
| 594-01788          | TAGPP1-788  | TAGPP1   | 1.5   | 15.87 | .37    | 7.87  | 12             | 30                | 360              | 1000      |
| 594-00001          | TAGPP2-788  | TAGPP2   | .66   | 16.7  | .33    | 8.38  | 12             | 30                | 360              | 1000      |
| 594-62788          | TAG62L-788  | TAG62L   | 1.5   | 31.75 | .37    | 9.52  | 5              | 25                | 125              | 1000      |
| 594-61788          | TAG61L-788  | TAG61L   | 2.62  | 66.67 | 1.0    | 25.4  | 3              | 10                | 30               | 7500      |
| 594-60788          | TAG60L-788  | TAG60L   | 2.83  | 71.88 | 1.5    | 38.1  | 3              | 7                 | 21               | 5250      |
| 594-59788          | TAG59L-788  | TAG59L   | 4.0   | 101.6 | 1.5    | 38.1  | 2              | 7                 | 14               | 3500      |
| 594-58788          | TAG58L-788  | TAG58L   | 4.0   | 101.6 | 2.0    | 50.8  | 2              | 5                 | 10               | 2500      |
| 594-56788          | TAG57L-788  | TAG56L   | 4.0   | 101.6 | 3.33   | 84.5  | 2              | 3                 | 6                | 1500      |
| 594-57788          | TAG56L-788  | TAG57L   | 4.25  | 107.9 | 2.75   | 69.8  | 2              | 4                 | 8                | 2000      |
| 594-55788          | TAG55L-788  | TAG55L   | 4.25  | 107.9 | 5.5    | 139.7 | 2              | 2                 | 4                | 1000      |
| 594-54788          | TAG54L-788  | TAG54L   | 8.50  | 215.9 | 5.5    | 139.7 | 1              | 2                 | 2                | 500       |
| 594-53788          | TAG53L-788  | TAG53L   | 8.50  | 215.9 | 10.81  | 274.6 | 1              | 1                 | 1                | 250       |
| 788 C Material     |             |          |       |       |        |       |                |                   |                  |           |
| 594-02788          | TAGPP1-788C | TAGPP1   | .625  | 15.87 | .333   | 8.45  | 12             | 30                | 360              | 1000      |
| 594-00002          | TAGPP2-788C | TAGPP2   | .660  | 16.7  | .330   | 8.38  | 12             | 30                | 360              | 1000      |
| 789 Material       |             |          |       |       |        |       |                |                   |                  |           |
| 594-11789          | TAG11L-789  | TAG11L   | .65   | 16.5  | .2     | 5.08  | 10             | 48                | 480              | 5000      |
| 594-13789          | TAG13L-789  | TAG13L   | .75   | 19.0  | .25    | 6.35  | 8              | 39                | 312              | 5000      |
| 594-14789          | TAG14L-789  | TAG14L   | 1.0   | 25.4  | .375   | 9.52  | 7              | 25                | 175              | 5000      |
| 594-15789          | TAG15L-789  | TAG15L   | 1.0   | 25.4  | .5     | 12.7  | 7              | 19                | 133              | 5000      |
| 594-96789          | TAG96L-789  | TAG96L   | 1.875 | 47.62 | .25    | 6.3   | 4              | 36                | 144              | 1000      |
| 594-69789          | TAG69L-789  | TAG69L   | 2.0   | 50.8  | .275   | 6.98  | 4              | 35                | 140              | 1000      |
| 594-67789          | TAG67L-789  | TAG67L   | 2.87  | 73.0  | .375   | 9.52  | 2              | 25                | 50               | 1000      |
| 594-66789          | TAG66L-789  | TAG66L   | 3.59  | 91.4  | .375   | 9.52  | 2              | 25                | 50               | 1000      |
| 594-68789          | TAG68L-789  | TAG68L   | 3.8   | 96.5  | .275   | 6.98  | 2              | 35                | 70               | 2500      |
| 594-45789          | TAG45L-789  | TAG45L   | 4.0   | 101.6 | .8     | 20.32 | 2              | 12                | 24               | 5000      |
| Cardstock Material |             |          |       |       |        |       |                |                   |                  |           |
| 593-00001          | TAGPHONE    | TAGPHONE | 1.75  | 44.45 | .375   | 9.52  | 4              | 21                | 84               | 1000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Product Selection

Product Selection

| Article No.        | Part No.    | Type     | Width |       | Height |       | Labels per Row | Labels per Column | Labels per Sheet | Pkg. Qty. |
|--------------------|-------------|----------|-------|-------|--------|-------|----------------|-------------------|------------------|-----------|
|                    |             |          | In.   | mm.   | In.    | mm.   |                |                   |                  |           |
| 108 Material       |             |          |       |       |        |       |                |                   |                  |           |
| 593-01108          | TAGPP1J-108 | TAGPP1J  | .625  | 15.87 | .31    | 7.87  | 12             | 30                | 360              | 1000      |
| 593-65108          | TAG65J-108  | TAG65J   | 1.0   | 25.4  | 1.5    | 31.75 | 12             | 10                | 50               | 12500     |
| 593-59108          | TAG59J-108  | TAG59J   | 4.0   | 101.6 | 1.5    | 38.1  | 2              | 7                 | 14               | 3500      |
| 593-57108          | TAG57J-108  | TAG57J   | 4.25  | 107.9 | 2.75   | 69.8  | 2              | 4                 | 8                | 2000      |
| 593-56108          | TAG56J-108  | TAG56J   | 3.33  | 84.5  | 4.0    | 101.6 | 2              | 3                 | 6                | 1500      |
| 450 Material       |             |          |       |       |        |       |                |                   |                  |           |
| 593-11450          | TAG11J-450  | TAG11J   | .20   | 5.08  | .65    | 16.05 | 21             | 12                | 252              | 5000      |
| 593-13450          | TAG13J-450  | TAG13J   | .25   | 6.35  | .75    | 19.0  | 26             | 12                | 312              | 5000      |
| 593-14450          | TAG14J-450  | TAG14J   | .375  | 9.52  | 1.0    | 25.4  | 16             | 9                 | 144              | 2500      |
| 593-19450          | TAG19J-450  | TAG19J   | .375  | 9.52  | 2.0    | 50.8  | 15             | 4                 | 60               | 1200      |
| 593-15450          | TAG15J-450  | TAG15J   | .50   | 12.7  | 1.0    | 25.4  | 13             | 9                 | 117              | 5000      |
| 593-21450          | TAG21J-450  | TAG21J   | .50   | 12.7  | .75    | 19.0  | 13             | 12                | 156              | 5000      |
| 593-28450          | TAG28J-450  | TAG28J   | .80   | 20.3  | 1.437  | 36.49 | 8              | 6                 | 48               | 1000      |
| Cardstock Material |             |          |       |       |        |       |                |                   |                  |           |
| 593-00001          | TAGPHONE    | TAGPHONE | 1.75  | 44.45 | .375   | 9.52  | 4              | 21                | 84               | 1000      |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## ShrinkTrak Heat Shrinkable Markers

## Product Selection

| Product Selection                   |           |                 |             |             |       |      |        |      |           |  |
|-------------------------------------|-----------|-----------------|-------------|-------------|-------|------|--------|------|-----------|--|
| Article No.                         | Part No.  | Type            | Color       | Center Slit | Width |      | Height |      | Pkg. Qty. |  |
|                                     |           |                 |             |             | In.   | mm.  | In.    | mm.  |           |  |
| 0.125" (3.17mm) - Outside Diameter  |           |                 |             |             |       |      |        |      |           |  |
| 553-50003                           | 553-50003 | HST3-1WH        | White (WH)  | -           | 1.9   | 48   | 1.9    | 48   | 1000      |  |
| 553-50078                           | 553-50078 | HST3-1WH        | White (WH)  | -           | 1.9   | 48   | .235   | 5.97 | 2500      |  |
| 553-50004                           | 553-50004 | HST3-1WH-S      | White (WH)  | Single      | .95   | 24   | .235   | 5.97 | 500       |  |
| 553-50074                           | 553-50074 | HST3-1WH-S      | White (WH)  | Single      | .95   | 24   | .235   | 5.97 | 2000      |  |
| 553-50067                           | 553-50067 | HST3-1WH-S      | White (WH)  | Single      | .95   | 24   | .235   | 5.97 | 5000      |  |
| 553-50070                           | 553-50070 | HST3-1WH-2S     | White (WH)  | Double      | .63   | 16   | .235   | 5.97 | 750       |  |
| 553-50075                           | 553-50075 | HST3-1WH-2S     | White (WH)  | Double      | .63   | 16   | .235   | 5.97 | 3000      |  |
| 553-50063                           | 553-50063 | HST3-1WH-3S     | White (WH)  | Triple      | .475  | 12   | .235   | 5.97 | 1000      |  |
| 553-50088                           | 553-50088 | HST3-1WH-3S     | White (WH)  | Triple      | .475  | 12   | .475   | 12   | 4000      |  |
| 553-50006                           | 553-50006 | HST3-1YE        | Yellow (YE) | -           | 1.9   | 48   | .235   | 5.97 | 1000      |  |
| 553-50005                           | 553-50005 | HST3-1YE        | Yellow (YE) | -           | 1.9   | 48   | .235   | 5.97 | 250       |  |
| 553-50007                           | 553-50007 | HST3-1YE-S      | Yellow (YE) | Single      | .95   | 24   | .235   | 5.97 | 500       |  |
| 553-50076                           | 553-50076 | HST3-1YE-S      | Yellow (YE) | Single      | .95   | 24   | .235   | 5.97 | 2000      |  |
| 553-50071                           | 553-50071 | HST3-1YE-2S     | Yellow (YE) | Double      | .63   | 16   | .235   | 5.97 | 750       |  |
| 553-50077                           | 553-50077 | HST3-1YE-2S     | Yellow (YE) | Double      | .63   | 16   | .235   | 5.97 | 3000      |  |
| 0.187" (4.74 mm) - Outside Diameter |           |                 |             |             |       |      |        |      |           |  |
| 553-50008                           | 553-50008 | HST4.8-1.6BK    | Black (BK)  | -           | 1.9   | 48.2 | .312   | 7.92 | 250       |  |
| 553-50009                           | 553-50009 | HST4.8-1.6WH    | White (WH)  | -           | 1.9   | 48   | .312   | 7.92 | 250       |  |
| 553-50010                           | 553-50010 | HST4.8-1.6WH    | White (WH)  | -           | 1.9   | 48.2 | .312   | 7.92 | 1000      |  |
| 553-50177                           | 553-50177 | HST4.8-1.6WH    | White (WH)  | -           | 1.9   | 48   | .312   | 7.92 | 3000      |  |
| 553-50079                           | 553-50079 | HST4.8-1.6WH    | White (WH)  | -           | 1.9   | 48   | .312   | 7.92 | 5000      |  |
| 553-50011                           | 553-50011 | HST4.8-1.6WH-S  | White (WH)  | Single      | .95   | 24   | .312   | 7.92 | 500       |  |
| 553-50080                           | 553-50080 | HST4.8-1.6WH-S  | White (WH)  | Single      | .95   | 24   | .312   | 7.92 | 2000      |  |
| 553-50068                           | 553-50068 | HST4.8-1.6WH-2S | White (WH)  | Double      | .63   | 16   | .312   | 7.92 | 750       |  |
| 553-50072                           | 553-50072 | HST4.8-1.6WH-2S | White (WH)  | Double      | .633  | 16   | .312   | 7.92 | 3000      |  |
| 553-50064                           | 553-50064 | HST4.8-1.6WH-3S | White (WH)  | Triple      | .312  | 12   | .312   | 7.92 | 1000      |  |
| 553-50081                           | 553-50081 | HST4.8-1.6WH-3S | White (WH)  | Triple      | .475  | 12   | .312   | 7.92 | 4000      |  |
| 553-50013                           | 553-50013 | HST4.8-1.6YE    | Yellow (YE) | -           | 1.9   | 48   | .312   | 7.92 | 1000      |  |
| 553-50012                           | 553-50012 | HST4.8-1.6YE    | Yellow (YE) | -           | 1.9   | 48   | .312   | 7.92 | 250       |  |
| 553-50014                           | 553-50014 | HST4.8-1.6YE-S  | Yellow (YE) | Single      | .95   | 24   | .312   | 7.92 | 500       |  |
| 553-50069                           | 553-50069 | HST4.8-1.6YE-2S | Yellow (YE) | Double      | .633  | 16   | .312   | 7.92 | 750       |  |
| 553-50073                           | 553-50073 | HST4.8-1.6YE-2S | Yellow (YE) | Double      | .633  | 16   | .312   | 7.92 | 3000      |  |
| 553-50176                           | 553-50176 | HST4.8-1.6WH-S  | White (WH)  | Double      | .95   | 24   | .312   | 7.92 | 3000      |  |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## ShrinkTrak Heat Shrinkable Markers

## Product Selection

| Product Selection                  |           |              |             |             |       |     |        |       |           |  |  |
|------------------------------------|-----------|--------------|-------------|-------------|-------|-----|--------|-------|-----------|--|--|
| Article No.                        | Part No.  | Type         | Color       | Center Slit | Width |     | Height |       | Pkg. Qty. |  |  |
|                                    |           |              |             |             | In.   | mm. | In.    | mm.   |           |  |  |
| 0.25" (6.35mm) - Outside Diameter  |           |              |             |             |       |     |        |       |           |  |  |
| 553-50015                          | 553-50015 | HST6-2BK     | Black (BK)  | -           | 1.9   | 48  | .42    | 10.67 | 250       |  |  |
| 553-50016                          | 553-50016 | HST6-2WH     | White (WH)  | -           | 1.9   | 48  | .42    | 10.67 | 250       |  |  |
| 553-50017                          | 553-50017 | HST6-2WH     | White (WH)  | -           | 1.9   | 48  | .42    | 10.67 | 1000      |  |  |
| 553-50018                          | 553-50018 | HST6-2WH     | White (WH)  | -           | 1.9   | 48  | .42    | 10.67 | 5000      |  |  |
| 553-50019                          | 553-50019 | HST6-2WH-S   | White (WH)  | Single      | .95   | 24  | .42    | 10.67 | 500       |  |  |
| 553-50020                          | 553-50020 | HST6-2YE-S   | Yellow (YE) | -           | 1.9   | 48  | .42    | 10.67 | 2000      |  |  |
| 553-50021                          | 553-50021 | HTS6-2YE-2S  | Yellow (YE) | -           | 1.9   | 48  | .42    | 10.67 | 1000      |  |  |
| 553-50022                          | 553-50022 | HST6-2YE-S   | Yellow (YE) | Single      | .95   | 24  | .42    | 10.67 | 1000      |  |  |
| 553-50082                          | 553-50082 | HST6-2WH-2S  | White (WH)  | Double      | .633  | 16  | .42    | 10.67 | 750       |  |  |
| 553-50083                          | 553-50083 | HST6-2YE-2S  | Yellow (YE) | Double      | .633  | 16  | .42    | 10.67 | 750       |  |  |
| 553-50084                          | 553-50084 | HST6-2WH-S   | White (WH)  | Single      | .95   | 24  | .42    | 10.67 | 2000      |  |  |
| 553-50085                          | 553-50085 | HST6-2YE-S   | Yellow (YE) | Single      | .95   | 24  | .42    | 10.67 | 2000      |  |  |
| 553-50089                          | 553-50089 | HST6-2WH-3S  | White (WH)  | Single      | .475  | 12  | .42    | 10.67 | 4000      |  |  |
| 0.375" (9.52mm) - Outside Diameter |           |              |             |             |       |     |        |       |           |  |  |
| 553-50023                          | 553-50023 | HST9-3BK     | Black (BK)  | -           | 1.9   | 48  | .597   | 15.16 | 250       |  |  |
| 553-50024                          | 553-50024 | HST9-3WH     | White (WH)  | -           | 1.9   | 48  | .597   | 15.16 | 250       |  |  |
| 553-50025                          | 553-50025 | HST9-3WH-S   | White (WH)  | Single      | .95   | 24  | .597   | 15.16 | 500       |  |  |
| 553-50066                          | 553-50066 | HST9-3WH-3S  | White (WH)  | Triple      | .475  | 12  | .597   | 15.16 | 1000      |  |  |
| 553-50026                          | 553-50026 | HST9-3YE     | Yellow (YE) | -           | 1.9   | 48  | .597   | 15.16 | 250       |  |  |
| 553-50027                          | 553-50027 | HST9-3YE-S   | Yellow (YE) | Single      | .95   | 24  | .597   | 15.16 | 500       |  |  |
| 553-50192                          | 553-50192 | HST9-3WH     | White (WH)  | -           | 1.9   | 48  | .597   | 15.16 | 1000      |  |  |
| 0.5" (12.7mm) - Outside Diameter   |           |              |             |             |       |     |        |       |           |  |  |
| 553-50028                          | 553-50028 | HST12-4BK    | Black (BK)  | -           | 1.9   | 48  | .77    | 19.55 | 250       |  |  |
| 553-50029                          | 553-50029 | HST12-4WH    | White (WH)  | -           | 1.9   | 48  | .77    | 19.55 | 250       |  |  |
| 553-50030                          | 553-50030 | HST12-4WH-S  | White (WH)  | Single      | .95   | 24  | .77    | 19.55 | 500       |  |  |
| 553-50086                          | 553-50086 | HST12-4WH-3S | White (WH)  | Triple      | .475  | 12  | .77    | 19.55 | 1000      |  |  |
| 553-50031                          | 553-50031 | HST12-4YE    | Yellow (YE) | -           | 1.9   | 48  | .77    | 19.55 | 250       |  |  |
| 553-50032                          | 553-50032 | HST12-4YE-S  | Yellow (YE) | Single      | .95   | 24  | .77    | 19.55 | 500       |  |  |
| 553-50087                          | 553-50087 | HST12-4YE-3S | Yellow (YE) | Triple      | .475  | 12  | .77    | 19.55 | 1000      |  |  |
| 553-50231                          | 553-50231 | HST12-4WH    | White (WH)  | -           | .77   | 48  | .77    | 19.55 | 1000      |  |  |
| 553-50232                          | 553-50232 | HST12-4WH-S  | White (WH)  | Single      | .77   | 24  | .77    | 19.55 | 2000      |  |  |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.



## ShrinkTrak Heat Shrinkable Markers

## Product Selection

| Product Selection                  |           |               |             |             |       |       |        |       |           |
|------------------------------------|-----------|---------------|-------------|-------------|-------|-------|--------|-------|-----------|
| Article No.                        | Part No.  | Type          | Color       | Center Slit | Width |       | Height |       | Pkg. Qty. |
|                                    |           |               |             |             | In.   | mm.   | In.    | mm.   |           |
| 0.75" (19.05mm) - Outside Diameter |           |               |             |             |       |       |        |       |           |
| 553-50033                          | 553-50033 | HST18-6BK     | Black (BK)  | -           | 1.9   | 48    | 1.2    | 30.48 | 250       |
| 553-50034                          | 553-50034 | HST18-6WH     | White (WH)  | -           | 1.9   | 48    | 1.2    | 30.48 | 250       |
| 553-50035                          | 553-50035 | HST18-6WH-S   | White (WH)  | Single      | .95   | 24    | 1.2    | 30.48 | 500       |
| 553-50036                          | 553-50036 | HST18-6YE     | Yellow (YE) | -           | 1.9   | 48    | 1.2    | 30.48 | 250       |
| 553-50037                          | 553-50037 | HST18-6YE-S   | Yellow (YE) | Single      | .95   | 24    | 1.2    | 30.48 | 500       |
| 553-50233                          | 553-50233 | HST18-6WH     | White (WH)  | -           | 1.2   | 48    | 1.2    | 30.48 | 1000      |
| 553-50234                          | 553-50234 | HST18-6WH-S   | White (WH)  | Single      | 1.2   | 24    | 1.2    | 30.48 | 2000      |
| 1.0" (25.4mm) - Outside Diameter   |           |               |             |             |       |       |        |       |           |
| 553-50038                          | 553-50038 | HST24-8BK     | Black (BK)  | -           | 1.9   | 48    | 1.69   | 42.93 | 250       |
| 553-50039                          | 553-50039 | HST24-8WH     | White (WH)  | -           | 1.9   | 48    | 1.69   | 42.93 | 250       |
| 553-50040                          | 553-50040 | HST24-8WH-S   | White (WH)  | Single      | .95   | 24    | 1.69   | 42.93 | 500       |
| 553-50041                          | 553-50041 | HST24-8YE     | Yellow (YE) | -           | 1.9   | 48    | 1.69   | 42.93 | 250       |
| 553-50042                          | 553-50042 | HST24-8YE-S   | Yellow (YE) | Single      | .95   | 24    | 1.69   | 42.93 | 500       |
| 1.5" (38.1mm) - Outside Diameter   |           |               |             |             |       |       |        |       |           |
| 553-50226                          | 553-50226 | HFST39-13WH-S | White (WH)  | Single      | .95   | 24.13 | 2.26   | 57.40 | 300       |
| 553-50209                          | 553-50209 | HST39-13WH    | White (WH)  | -           | 1.9   | 48.2  | 2.26   | 57.40 | 150       |
| 553-50225                          | 553-50225 | HFST39-13YE   | Yellow (YE) | -           | 1.9   | 48.2  | 2.26   | 57.40 | 150       |
| 553-50227                          | 553-50227 | HFST39-13YE-S | Yellow (YE) | Single      | .95   | 24.13 | 2.26   | 57.40 | 300       |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Foam Nameplate Labels

## Product Selection

| Product Selection      |           |                 |       |      |        |       |      |       |           |  |
|------------------------|-----------|-----------------|-------|------|--------|-------|------|-------|-----------|--|
| Article No.            | Part No.  | Type            | Width |      | Height |       | Hole | Color | Pkg. Qty. |  |
|                        |           |                 | In.   | mm.  | In.    | mm.   |      |       |           |  |
| Foam Nameplates        |           |                 |       |      |        |       |      |       |           |  |
| 596-00500              | 596-00500 | NPL27X13WH      | 1.06  | 27   | .49    | 12.5  | N/A  | N/A   | 500       |  |
| 596-00503              | 596-00503 | NPL27X13BK      | 1.06  | 27   | .49    | 12.5  | N/A  | N/A   | 500       |  |
| 596-00504              | 596-00504 | NPL51X25WH      | 2     | 50.8 | 1      | 25.4  | N/A  | N/A   | 500       |  |
| 596-00507              | 596-00507 | NPL51X25BK      | 2     | 50.8 | 1      | 25.4  | N/A  | N/A   | 500       |  |
| 596-00417              | 596-00417 | NPLH76X101WH    | 3.0   | 76   | 4.0    | 101.6 | N/A  | N/A   | 150       |  |
| Foam Button Nameplates |           |                 |       |      |        |       |      |       |           |  |
| 596-00412              | 596-00412 | NPLH31X31WH22.5 | 1.25  | 31.7 | 1.25   | 31.7  | 0.88 | 22.3  | 250       |  |
| 596-00413              | 596-00413 | NPLH31X31BK22.5 | 1.25  | 31.7 | 1.25   | 31.7  | 0.88 | 22.3  | 250       |  |
| 596-00414              | 596-00414 | NPLH44X44WH30.5 | 1.75  | 44.4 | 1.75   | 44.4  | 1.2  | 30.4  | 250       |  |
| 596-00415              | 596-00415 | NPLH44X44BK30.5 | 1.75  | 44.4 | 1.75   | 44.4  | 1.2  | 30.4  | 250       |  |
| 596-00202              | 596-00202 | NPL60X60YE      | 2.375 | 60   | 2.375  | 60    | 1.2  | 30.4  | 100       |  |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

## Continuous Vinyl Labels

## Product Selection

| Product Selection                    |           | Type       | Description                         | Width |         | Length |      | Color  | Pkg. Qty. | Pkg. Type |
|--------------------------------------|-----------|------------|-------------------------------------|-------|---------|--------|------|--------|-----------|-----------|
| Article No.                          | Part No.  |            |                                     | In.   | (mm.)   | Ft.    | (M)  |        |           |           |
|                                      |           |            |                                     |       |         |        |      |        |           |           |
| Solid Colored Continuous Vinyl Rolls |           |            |                                     |       |         |        |      |        |           |           |
| 558-00309                            | 558-00309 | HT1WH250   | White vinyl on continuous roll      | 1     | (25.4)  | 250    | (76) | White  | 250       | RL        |
| 558-00313                            | 558-00313 | HT2WH250   | White vinyl on continuous roll      | 2     | (50.8)  | 250    | (76) | White  | 250       | RL        |
| 558-00345                            | 558-00345 | HT3WH250   | White vinyl on continuous roll      | 3     | (76.2)  | 250    | (76) | White  | 250       | RL        |
| 558-00350                            | 558-00350 | HT4WH250   | White vinyl on continuous roll      | 4     | (101.6) | 250    | (76) | White  | 250       | RL        |
| 558-00340                            | 558-00340 | HT1GN250   | Green vinyl on continuous roll      | 1     | (25.4)  | 250    | (76) | Green  | 250       | RL        |
| 558-00342                            | 558-00342 | HT2GN250   | Green vinyl on continuous roll      | 2     | (50.8)  | 250    | (76) | Green  | 250       | RL        |
| 558-00344                            | 558-00344 | HT3GN250   | Green vinyl on continuous roll      | 3     | (76.2)  | 250    | (76) | Green  | 250       | RL        |
| 558-00351                            | 558-00351 | HT4GN250   | Green vinyl on continuous roll      | 4     | (101.6) | 250    | (76) | Green  | 250       | RL        |
| 558-00336                            | 558-00336 | HT1OE250   | Orange vinyl on continuous roll     | 1     | (25.4)  | 250    | (76) | Orange | 250       | RL        |
| 558-00337                            | 558-00337 | HT2OE250   | Orange vinyl on continuous roll     | 2     | (50.8)  | 250    | (76) | Orange | 250       | RL        |
| 558-00338                            | 558-00338 | HT3OE250   | Orange vinyl on continuous roll     | 3     | (76.2)  | 250    | (76) | Orange | 250       | RL        |
| 558-00339                            | 558-00339 | HT1BU250   | Blue vinyl on continuous roll       | 1     | (25.4)  | 250    | (76) | Blue   | 250       | RL        |
| 558-00341                            | 558-00341 | HT2BU250   | Blue vinyl on continuous roll       | 2     | (50.8)  | 250    | (76) | Blue   | 250       | RL        |
| 558-00343                            | 558-00343 | HT3BU250   | Blue vinyl on continuous roll       | 3     | (76.2)  | 250    | (76) | Blue   | 250       | RL        |
| 558-00310                            | 558-00310 | HT1YE250   | Yellow vinyl on continuous roll     | 1     | (25.4)  | 250    | (76) | Yellow | 250       | RL        |
| 558-00314                            | 558-00314 | HT2YE250   | Yellow vinyl on continuous roll     | 2     | (50.8)  | 250    | (76) | Yellow | 250       | RL        |
| 558-00346                            | 558-00346 | HT3YE250   | Yellow vinyl on continuous roll     | 3     | (76.2)  | 250    | (76) | Yellow | 250       | RL        |
| 558-00308                            | 558-00308 | HT1RD250   | Red vinyl on continuous roll        | 1     | (25.4)  | 250    | (76) | Red    | 250       | RL        |
| 558-00312                            | 558-00312 | HT2RD250   | Red vinyl on continuous roll        | 2     | (50.8)  | 250    | (76) | Red    | 250       | RL        |
| 558-00006                            | 558-00006 | HT3RD250   | Red vinyl on continuous roll        | 3     | (76.2)  | 250    | (76) | Red    | 250       | RL        |
| 558-00370                            | 558-00370 | HT4RD250   | Red vinyl on continuous roll        | 4     | (101.6) | 250    | (76) | Red    | 250       | RL        |
| 558-00307                            | 558-00307 | HT1BK250   | Black vinyl on continuous roll      | 1     | (25.4)  | 250    | (76) | Black  | 250       | RL        |
| 558-00311                            | 558-00311 | HT2BK250   | Black vinyl on continuous roll      | 2     | (50.8)  | 250    | (76) | Black  | 250       | RL        |
| 558-00374                            | 558-00374 | HT3BK250   | Black vinyl on continuous roll      | 3     | (76.2)  | 250    | (76) | Black  | 250       | RL        |
| Reflective Continuous Labels         |           |            |                                     |       |         |        |      |        |           |           |
| 558-00371                            | 558-00371 | HT1RDRF250 | Reflective vinyl on continuous roll | 1     | (25.4)  | 250    | (76) | Red    | 250       | RL        |
| 558-00372                            | 558-00372 | HT2RDRF250 | Reflective vinyl on continuous roll | 2     | (50.8)  | 250    | (76) | Red    | 250       | RL        |
| 558-00373                            | 558-00373 | HT3RDRF250 | Reflective vinyl on continuous roll | 3     | (76.2)  | 250    | (76) | Red    | 250       | RL        |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes. Not all items in stock. Contact HellermannTyton for stock status before ordering.

## Continuous Vinyl Labels

## Product Selection

| Product Selection                                  |           |            |                                     | Width |         | Length |      | Color | Pkg. Qty. | Pkg. Type |
|----------------------------------------------------|-----------|------------|-------------------------------------|-------|---------|--------|------|-------|-----------|-----------|
| Article No.                                        | Part No.  | Type       | Description                         | In.   | (mm.)   | Ft.    | (M)  |       |           |           |
| Pre-printed Signal Panel Labels on Continuous Roll |           |            |                                     |       |         |        |      |       |           |           |
| 558-00327                                          | 558-00327 | HT20E50250 | White vinyl with .5" orange stripe  | 2     | (50.8)  | 250    | (76) | White | 250       | RL        |
| 558-00328                                          | 558-00328 | HT2YE50250 | White vinyl with .5" yellow stripe  | 2     | (50.8)  | 250    | (76) | White | 250       | RL        |
| 558-00330                                          | 558-00330 | HT30E75250 | White vinyl with .75" orange        | 3     | (76.2)  | 250    | (76) | White | 250       | RL        |
| 558-00331                                          | 558-00331 | HT3YE75250 | White vinyl with .75" yellow stripe | 3     | (76.2)  | 250    | (76) | White | 250       | RL        |
| 558-00333                                          | 558-00333 | HT40E10250 | White vinyl with 1" orange stripe   | 4     | (101.6) | 250    | (76) | White | 250       | RL        |
| 558-00334                                          | 558-00334 | HT4YE10250 | White vinyl with 1" yellow stripe   | 4     | (101.6) | 250    | (76) | White | 250       | RL        |

## Terminal Block Labels on Continuous Roll

|           |           |        |                            |      |        |     |        |       |     |    |
|-----------|-----------|--------|----------------------------|------|--------|-----|--------|-------|-----|----|
| 596-00380 | 596-00380 | TBL375 | White continuous polyester | .375 | (9.5)  | 100 | (30.5) | White | 100 | RL |
| 596-00381 | 596-00381 | TBL500 | White continuous polyester | .5   | (12.7) | 100 | (30.5) | White | 100 | RL |

## Pre-printed Signal Word Labels

|           |           |            |                                                     |     |         |      |         |       |     |    |
|-----------|-----------|------------|-----------------------------------------------------|-----|---------|------|---------|-------|-----|----|
| 596-00203 | 596-00203 | 4X6DANGER  | White with Red DANGER header                        | 4   | (101.6) | 6    | (152.4) | White | 250 | RL |
| 596-00427 | 596-00427 | 4X6CAUTION | White with Yellow CAUTION header                    | 4   | (101.6) | 6    | (152.4) | White | 250 | RL |
| 596-00371 | 596-00371 | 4X6SAFETY  | White with green SAFETY header.                     | 4   | (101.6) | 6    | (152.4) | White | 250 | RL |
| 596-00376 | 596-00376 | WV55X275   | Orange WARNING header, yellow voltage safety symbol | 5.5 | (139.7) | 2.75 | (69.9)  | White | 250 | RL |
| 596-00377 | 596-00377 | DV55X275   | Red DANGER header, yellow voltage safety symbol     | 5.5 | (139.7) | 2.75 | (69.9)  | White | 250 | RL |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes. Not all items in stock. Contact HellermannTyton for stock status before ordering.

## TagPrint Pro 3.0

## Product Selection

| Article No. | Part No.  | Description                             |
|-------------|-----------|-----------------------------------------|
| 556-00035   | 556-00035 | Single User TagPrint Pro 3.0            |
| 556-00042   | 556-00042 | Single User Upgrade to TagPrint Pro 3.0 |
| 556-00036   | 556-00036 | 3 User Network Version                  |
| 556-00037   | 556-00037 | 5 User Network Version                  |
| 556-00038   | 556-00038 | 10 User Network Version                 |
| 556-00039   | 556-00039 | 25 User Network Version                 |
| 556-00052   | 556-00052 | 50 User Network Version                 |

Use **Part No.** for ordering and **Type** for specification purposes.

# HellermannTyton

## **HellermannTyton North American Corporate Headquarters**

7930 N. Faulkner Rd, PO Box 245017, Milwaukee, WI 53224-9517  
Phone: (414) 355-1130, (800) 537-1512, Fax: (414) 355-7341, (800) 848-9866  
email: corp@htamericas.com, www.hellermann.tyton.com  
***TS16949, ISO 9001, and ISO14001 certified***

## **HellermannTyton Canada**

Unit #4, 205 Industrial Parkway North, Aurora, Ontario L4G 4C4 Canada  
Phone: (800) 661-2461, Fax: (800) 390-3904  
email: sales@hellermanntyton.ca

## **HellermannTyton Mexico**

Anillo Periferico Sur 7980 Edificio 2-D, Parque Industrial Tecnologico II  
Santa María Tequepexpan, Tlaquepaque, Jalisco, Mexico 45601  
Phone: 011-52-33-3-133-9880, Fax: 011-52-33-3-133-9861  
email: info@htamericas.com.mx

***ISO 9001 certified***

### **Warranty Policy**

HellermannTyton products are warranted to be free from defects in material and workmanship at the time sold by us; but our obligation under this warranty and that of the seller is limited to the replacement of the product, and neither we nor the seller are bound by any other warranty, expressed, implied or statutory. Under no circumstances are we or the seller liable for any loss, damage, expenses or consequential damages of any kind arising out of the use or inability to use these products. All are sold with the understanding that the user will test them in actual use and determine their adaptability for the intended uses.