

Header - PTSM 0,5/ 3-HH1-2,5-THR R32 - 1814786

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Header, Nominal current: 6 A, Number of positions: 3, Pitch: 2.5 mm, Color: black, Contact surface: Tin, Assembly: SMD/THT/THR

Key commercial data

Packing unit	1 pc
Minimum order quantity	500 pc
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Pitch	2.5 mm
Dimension a	5 mm

General

Range of articles	PTSM 0,5/..-HH-THR
Rated voltage (III/3)	50 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	6 A
Color	black
Number of positions	3

Classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101

Header - PTSM 0,5/ 3-HH1-2,5-THR R32 - 1814786

Classifications

eCl@ss

eCl@ss 7.0	27440401
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Approvals

Approvals

Approvals

GOST / UL Recognized / UL Recognized

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Header - PTSM 0,5/ 3-HH1-2,5-THR R32 - 1814786

Approvals

UL Recognized 	
	B
Nominal current I _N	5 A
Nominal voltage U _N	150 V

UL Recognized 	
	B
Nominal current I _N	5 A
Nominal voltage U _N	150 V