

Ratings:
 Current 16A
 Voltage 300 V
 Wire Size 22-15AWG
 Test Voltage 2.0 kV

Rated Cross Section:
 Single Wire (solid) 1.5mm²
 Stranded Wire (flexible) on request
 Stranded Wire with Ferrules on request

Dimensions:
 Spacing 5.08mm
 PCB Hole Diameter 1.3mm
 Stripped Length 10.0mm

Materials:
 Insulating Material PA
 Flammability UL94V-0
 Temperature -30°C/+105°C
 Tension Spring Stainless Steel
 Contact Cu
 Color Slade Gray

