


5360 Series T-1 Right Angle 4 Wide LED Assembly

Description and Features



Features

- Quad assembly with 4 T-1 LEDs permits easy installation, assures matched height and center to center spacing, reduces assembly time and costs.
- High Brite and Super Brite LEDs, high light output, diffused lens.
- Standoffs prevent flux entrapment.
- Low current-only 2mA needed.

Housing: Black Nylon, UL94V-O

Note: Alternate LEDs are also available in this package as a standard variation.

Refer to “Mounting Hole Pattern 5.pdf”

Electro-Optical Characteristics and Ratings

Part Number	Emitted Color	Typical Intensity (mcd)	Rated Current (mA)	Continuous Forward Current Max. (mA)	Forward Voltage		Reverse Breakdown Voltage Min. (V)	Peak Wavelength (nm)
					Typ. (V)	Max. (V)		
5360F1	Red	10	10	30	2.0	3.0	5	650
5360F3	Amber	7	10	30	2.2	3.0	5	603
5360F5	Green	16.3	10	30	2.2	3.0	5	562
5360F7	Yellow	6.3	10	30	2.1	3.0	5	585
5360F1LC	Red	2.5	2.0	7	1.8	5	5	635
5360F5LC	Green	2.1	2.0	7	1.8	2.2	5	565
5360F7LC	Yellow	1.8	2.0	7	1.9	2.7	5	585
5360F1-5V	Red	8	10	20	5	7.5	5	635
5360F3-5V	Amber	8	10	15	5	7.5	5	583
5360F5-5V	Green	8	12	15	5	7.5	5	565