




ARCONIC
Innovation, engineered.

HG166 series

Swage Gauge for Pull-Type Composite with Pin Protrusion

PIN: LGPL8S9S7S()V()B

COLLAR: SLFC-MV()



GAGE NO	REV	A	B	C	D	E	F	G	H	J
HG166-05	B	.070-.072	.168-.170	.112-.114	.252-.254	.088-.092	.114-.116	.123-.125	.233-.235	.365-.375
HG166-06	B	.067-.069	.177-.179	.099-.101	.259-.261	.112-.116	.038-.140	.147-.149	.261-.263	.405-.415
HG166-07	A	.115-.117	.243-.245	.145-.147	.322-.324	.128-.132	.159-.161	.169-.171	.297-.299	.444-.454
HG166-08	B	.081-.083	.237-.239	.133-.135	.321-.323	.155-.159	.186-.188	.195-.197	.343-.345	.500-.510

Alcoa Fastening Systems Kingston Operations

1 Corporate Drive
Kingston, NY 12401
845-331-7300
FAX: 845-334-7333
www.afshuck.net/us



March 15, 2018
DS HG166
sheet 1 of 2




ARCONIC
Innovation, engineered.

HG166 series

Swage Gauge for Pull-Type Composite with Pin Protrusion

PIN: LGPL8S9S7S()V()B

COLLAR: SLFC-MV()



GAGE NO	REV	A	B	C	D	E	F	G	H
HG166-10	D	.092-.094	.321-.323	.138-.140	.403-.405	.233-.243	.252-.254	.435-.437	.625-.635
HG166-12	B	.142-.144	.359-.361	.205-.207	.476-.478	.287-.297	.306-.308	.511-.513	.725-.735

Alcoa Fastening Systems Kingston Operations

1 Corporate Drive
Kingston, NY 12401
845-331-7300
FAX: 845-334-7333
www.afshuck.net/us



March 15, 2018
DS HG166
sheet 1 of 2