

LED PANEL MOUNT INDICATOR

STANDARD BEZEL, DC OPERATION

MOUNTING HOLE, Ø 14mm

PART NO.	COLOR	VOLTAGE V _{OP} [V] DC	CURRENT I _{OP typ.} [mA] DC	LUMI. INTENSITY LED I _{V typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
SATIN CHROME BEZEL					
WL-19210250	RED	12V	20	160	625
WL-19210251	GREEN	12V	20	80	568
WL-19210252	YELLOW	12V	20	80	588
WL-19210257	BLUE	12V	20	60	466
WL-1921025W	WHITE	12V	20	200	*
WL-19210350	RED	24V	20	160	625
WL-19210351	GREEN	24V	20	80	568
WL-19210352	YELLOW	24V	20	80	588
WL-19210357	BLUE	24V	20	60	466
WL-1921035W	WHITE	24V	20	200	*
WL-19210450	RED	28V	20	160	625
WL-19210451	GREEN	28V	20	80	568
WL-19210452	YELLOW	28V	20	80	588
WL-19210457	BLUE	28V	20	60	466
WL-1921045W	WHITE	28V	20	200	*
BLACK CHROME BEZEL					
WL-19211250	RED	12V	20	160	625
WL-19211251	GREEN	12V	20	80	568
WL-19211252	YELLOW	12V	20	80	588
WL-19211257	BLUE	12V	20	60	466
WL-1921125W	WHITE	12V	20	200	*
WL-19211350	RED	24V	20	160	625
WL-19211351	GREEN	24V	20	80	568
WL-19211352	YELLOW	24V	20	80	588
WL-19211357	BLUE	24V	20	60	466
WL-1921135W	WHITE	24V	20	200	*
WL-19211450	RED	28V	20	160	625
WL-19211451	GREEN	28V	20	80	568
WL-19211452	YELLOW	28V	20	80	588
WL-19211457	BLUE	28V	20	60	466
WL-1921145W	WHITE	28V	20	200	*

*Chromaticity coordinates X=0.31 Y=.031


NOTES

1. Maximum panel thickness 10mm
2. Storage temperature
T_{STG}: -25°C – +80°C
3. Ambient temperature
T_A: -20°C – +60°C
4. DC operation only
5. Voltage tolerance
V_{OP}: ±10%
6. Electro-optical ratings at
T_A=25°C
7. Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
8. Mounting hole
14 + 0.2mm
9. 2.8 x 0.8mm terminals are standard
10. Due to production tolerances, slight color variations may be detected within individual consignments
11. Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M14 nut
12. CAUTION: Do not solder directly to terminals

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm

OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.



wamco
LIGHTING

P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-1921XX5X Series Rev 2

LED PANEL MOUNT INDICATOR


SUNLIGHT VISIBILITY, STANDARD BEZEL, AC/DC OPERATION

MOUNTING HOLE, Ø 14mm

PART NO.	COLOR	VOLTAGE V _{OP} [V] AC/DC	CURRENT I _{OP typ.} [mA] AC/DC	LUMI. INTENSITY LED **I _{v typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
MATTE CHROME BEZEL					
WL-19212250	RED	12V	20	160	625
WL-19212251	GREEN	12V	20	80	568
WL-19212252	YELLOW	12V	20	80	588
WL-19212257	BLUE	12V	20	60	466
WL-1921225W	WHITE	12V	20	200	*
WL-19212350	RED	24V	20	160	625
WL-19212351	GREEN	24V	20	80	568
WL-19212352	YELLOW	24V	20	80	588
WL-19212357	BLUE	24V	20	60	466
WL-1921235W	WHITE	24V	20	200	*
WL-19212450	RED	28V	20	160	625
WL-19212451	GREEN	28V	20	80	568
WL-19212452	YELLOW	28V	20	80	588
WL-19212457	BLUE	28V	20	60	466
WL-1921245W	WHITE	28V	20	200	*

*Chromaticity coordinates X=0.31 Y=.031

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

